

Affected Catalog Part Numbers (CPN)

24AA08-I/MC

24AA08-I/MS

24AA08-I/P

24AA08-I/SN

24AA08-I/ST

24AA08T-I/MC

24AA08T-I/MNY

24AA08T-I/MS

24AA08T-I/OT

24AA08T-I/OT16KV06

24AA08T-I/SN

24AA08T-I/ST

24FC08-E/MS

24FC08-E/P

24FC08-E/SN

24FC08-E/SN36KVAO

24FC08-E/ST

24FC08-I/MS

24FC08-I/P

24FC08-I/SN

24FC08-I/ST

24FC08T-E/MS

24FC08T-E/OT

24FC08T-E/OT36KVAO

24FC08T-E/Q4B

24FC08T-E/Q6B36KVAO

24FC08T-E/SN

24FC08T-E/SN36KVAO

24FC08T-E/ST

24FC08T-E/ST36KVAO

24FC08T-I/MS

24FC08T-I/OT

24FC08T-I/Q4B

24FC08T-I/SN

24FC08T-I/ST

24LC08B-E/MC

24LC08B-E/MS

24LC08B-E/P

24LC08B-E/SN

24LC08B-E/SN16KVAO

24LC08B-E/ST

24LC08B-I/MC

24LC08B-I/MS

24LC08B-I/MS16KVAO

24LC08B-I/P

24LC08B-I/SN

24LC08B-I/ST

24LC08BT-E/MC

24LC08BT-E/MNY

24LC08BT-E/MS

24LC08BT-E/OT

24LC08BT-E/OT15KV04

24LC08BT-E/OT15KV05

24LC08BT-E/OT15KV06

24LC08BT-E/OT15KVAO

24LC08BT-E/OT16KV01

24LC08BT-E/OT16KV08

24LC08BT-E/OT16KV14

24LC08BT-E/OT16KV15

24LC08BT-E/OT16KV16

24LC08BT-E/OT16KV18

24LC08BT-E/OT16KVAO

24LC08BT-E/SN

24LC08BT-E/SN15KVAO

24LC08BT-E/SN16KV03

24LC08BT-E/SN16KV10

24LC08BT-E/SN16KV13

24LC08BT-E/SN16KV20

24LC08BT-E/SN16KVAO

24LC08BT-E/ST

24LC08BT-E/ST16KV12

24LC08BT-I/MC

24LC08BT-I/MNY

24LC08BT-I/MS

24LC08BT-I/MS16KVAO

24LC08BT-I/OT

24LC08BT-I/OT15KV02

24LC08BT-I/OT15KV02-GM

24LC08BT-I/OT16KV01

24LC08BT-I/OT16KV11

24LC08BT-I/OT16KV11-GM

24LC08BT-I/SN

24LC08BT-I/SN15KVAO

24LC08BT-I/SN16KV04

24LC08BT-I/SN16KVAO

24LC08BT-I/ST