

Affected Catalog Part Numbers (CPN)

PIC18F25K80-E/MM

PIC18F25K80-E/MMC01

PIC18F25K80-E/MMVAO

PIC18F25K80-E/MMVAO-MB

PIC18F25K80-E/SO

PIC18F25K80-E/SO033

PIC18F25K80-E/SOVAO

PIC18F25K80-E/SP

PIC18F25K80-E/SS

PIC18F25K80-E/SSV02

PIC18F25K80-E/SSVAO

PIC18F25K80-H/MM

PIC18F25K80-H/MMVAO

PIC18F25K80-H/SS

PIC18F25K80-H/SSV03

PIC18F25K80-H/SSVAO

PIC18F25K80-I/MM

PIC18F25K80-I/MM030

PIC18F25K80-I/MM032

PIC18F25K80-I/MMC04

PIC18F25K80-I/MMVAO

PIC18F25K80-I/SO

PIC18F25K80-I/SOC03

PIC18F25K80-I/SOVAO

PIC18F25K80-I/SP

PIC18F25K80-I/SS

PIC18F25K80-I/SSVAO

PIC18F25K80T-E/MM

PIC18F25K80T-E/MMC01

PIC18F25K80T-E/MMCUI

PIC18F25K80T-E/MMV04

PIC18F25K80T-E/MMV08

PIC18F25K80T-E/MMVAO

PIC18F25K80T-E/MMVAO-MB

PIC18F25K80T-E/SO

PIC18F25K80T-E/SO033

PIC18F25K80T-E/SOVAO

PIC18F25K80T-E/SS

PIC18F25K80T-E/SSV02

PIC18F25K80T-E/SSVAO

PIC18F25K80T-H/MM

PIC18F25K80T-H/MMVAO

PIC18F25K80T-H/SSV03

PIC18F25K80T-H/SSVAO

PIC18F25K80T-I/MM

PIC18F25K80T-I/MMC04

PIC18F25K80T-I/MMVAO

PIC18F25K80T-I/SO

PIC18F25K80T-I/SOC03

PIC18F25K80T-I/SS

PIC18F25K80T-I/SSVAO

PIC18F26K80-E/MM

PIC18F26K80-E/MMVAO

PIC18F26K80-E/SO

PIC18F26K80-E/SP

PIC18F26K80-E/SS

PIC18F26K80-E/SSV06

PIC18F26K80-E/SSVAO

PIC18F26K80-H/MM

PIC18F26K80-H/MMVAO

PIC18F26K80-H/SS

PIC18F26K80-H/SSV11

PIC18F26K80-I/MM

PIC18F26K80-I/SO

PIC18F26K80-I/SP

PIC18F26K80-I/SPREL

PIC18F26K80-I/SS

PIC18F26K80-I/SSV15

PIC18F26K80-I/SSV22

PIC18F26K80-I/SSVAO

PIC18F26K80T-E/MM

PIC18F26K80T-E/MMV05

PIC18F26K80T-E/MMV05-GM

PIC18F26K80T-E/MMV09

PIC18F26K80T-E/MMV23

PIC18F26K80T-E/MMV26

PIC18F26K80T-E/MMVAO

PIC18F26K80T-E/SO

PIC18F26K80T-E/SS

PIC18F26K80T-E/SSV06

PIC18F26K80T-E/SSVAO

PIC18F26K80T-H/MM

PIC18F26K80T-H/MMVAO

PIC18F26K80T-H/SSV11

PIC18F26K80T-H/SSV24

PIC18F26K80T-H/SSVAO

PIC18F26K80T-I/MM

PIC18F26K80T-I/MMVAO

PIC18F26K80T-I/SO

PIC18F26K80T-I/SS

PIC18F26K80T-I/SSV07

PIC18F26K80T-I/SSVAO

PIC18F45K80-E/ML

PIC18F45K80-E/P

PIC18F45K80-E/PT

PIC18F45K80-E/PTVAO

PIC18F45K80-H/ML

PIC18F45K80-H/PT

PIC18F45K80-H/PTVAO

PIC18F45K80-I/ML

PIC18F45K80-I/P

PIC18F45K80-I/PT

PIC18F45K80-I/PT021

PIC18F45K80-I/PTVAO

PIC18F45K80T-E/ML

PIC18F45K80T-E/PT

PIC18F45K80T-E/PTVAO

PIC18F45K80T-H/PTVAO

PIC18F45K80T-I/ML

PIC18F45K80T-I/PT

PIC18F45K80T-I/PT021

PIC18F45K80T-I/PTVAO

PIC18F46K80-E/ML

PIC18F46K80-E/P

PIC18F46K80-E/PT

PIC18F46K80-E/PTVAO

PIC18F46K80-H/ML

PIC18F46K80-H/PT

PIC18F46K80-I/ML

PIC18F46K80-I/P

PIC18F46K80-I/PT

PIC18F46K80-I/PTVAO

PIC18F46K80T-E/ML

PIC18F46K80T-E/PT

PIC18F46K80T-E/PTVAO

PIC18F46K80T-E/PTVAO-MB

PIC18F46K80T-I/ML

PIC18F46K80T-I/PT

PIC18F46K80T-I/PT035

PIC18F46K80T-I/PTV11

PIC18F46K80T-I/PTVAO

PIC18F65K80-E/MR

PIC18F65K80-E/PT

PIC18F65K80-I/MR

PIC18F65K80-I/PT

PIC18F65K80-I/PTVAO

PIC18F65K80T-E/PT

PIC18F65K80T-I/MR

PIC18F65K80T-I/PT

PIC18F65K80T-I/PTVAO

PIC18F66K80-E/MR

PIC18F66K80-E/PT

PIC18F66K80-E/PTVAO

PIC18F66K80-I/MR

PIC18F66K80-I/PT

PIC18F66K80-I/PTREL

PIC18F66K80-I/PTVAO

PIC18F66K80T-E/PT

PIC18F66K80T-I/MR

PIC18F66K80T-I/PT

PIC18F66K80T-I/PTVAO

PIC18LF25K80-I/MM

PIC18LF25K80-I/SO

PIC18LF25K80-I/SP

PIC18LF25K80-I/SS

PIC18LF26K80-I/MM

PIC18LF26K80-I/MMC01

PIC18LF26K80-I/SO

PIC18LF26K80-I/SP

PIC18LF26K80-I/SS

PIC18LF26K80T-I/MMC01

PIC18LF45K80-I/ML

PIC18LF45K80-I/P

PIC18LF45K80-I/PT

PIC18LF45K80T-I/ML

PIC18LF45K80T-I/PT

PIC18LF46K80-I/ML

PIC18LF46K80-I/P

PIC18LF46K80-I/PT

PIC18LF46K80T-I/PT

PIC18LF65K80-I/MR

PIC18LF65K80-I/PT

PIC18LF65K80T-I/PT

PIC18LF66K80-I/MR

PIC18LF66K80-I/PT

PIC18LF66K80T-I/PT