

	Actel Part#	PKG	Body size (mm)	Pitch (mm)	MFG	Manufactors Part #	Insulator Material	Insulation Resistance (Mohm)	Withstanding Voltage (VAC)	Contact Resistance (mOhm)	Inductance (nH)	Capacitance (pF)
1	SE-CS49	CS49	7x7	0.8	E-Tec	BPW049-0830-07BB01	Epoxy FR4	100	500 VAC	<50	<5	<1
2	SE-CS128	CS128	11x11	0.8	E-Tec	BPW128-0830-12BB01	Epoxy FR4	100	500 VAC	<50	<5	<1
3	SE-CS180	CS180	13x13	0.8	E-Tec	BPW180-0830-14BB01	Epoxy FR4	100	500 VAC	<50	<5	<1
4	SE-FG144	FG144	13x13	1	E-Tec	BPW144-1030-12AA01	Epoxy FR4	500	500 VAC	<50	<5	<1
5	SE-FG256	FG256	17x17	1	E-Tec	BPW256-1030-16AB01	Epoxy FR4	500	500 VAC	<50	<5	<1
6	SE-FG484	FG484	27x27	1	E-Tec	BPW484-1030-26AB01	Epoxy FR4	500	500 VAC	<50	<5	<1
7	SE-FG676	FG676	27x27	1	E-Tec	BPW676-1030-26AA01	Epoxy FR4	500	500 VAC	<50	<5	<1
8	SE-FG896	FG896	31x31	1	E-Tec	BPW896-1030-30AA01	Epoxy FR4	500	500 VAC	<50	<5	<1
9	SE-FG1152	FG1152	35x35	1	E-Tec	BPW1152-1030-34AB01	Epoxy FR4	500	500 VAC	<50	<5	<1
10	SE-BG272A	BG272	27x27	1.27	E-Tec	BPW272-1270-20AC11	Epoxy FR4	500	500 VAC	<50	<5	<1
11	SE-BG329A	BG329	31x31	1.27	E-Tec	BPW329-1270-23AB11	Epoxy FR4	500	500 VAC	<50	<5	<1
12	SE-BG456A	BG456	35x35	1.27	E-Tec	BPW456-1270-26AB11	Epoxy FR4	500	500 VAC	<50	<5	<1
13	SE-BG729	BG729	35x35	1.27	E-Tec	BPW729-1230-27AA01	Epoxy FR4	500	500 VAC	<50	<5	<1
14	SY-VQ80-2	VQ80	14x14	0.65	Yamaichi	IC149-080-151-S5	PPS(GF)	500	150	30	5.8	N/A
15	SY-VQ100-1	VQ100	14x14	0.50	Yamaichi	IC149-100-125-S5	PPS(GF)	500	150	30	5.8	N/A
16	SY-TQ64	TQ64	10x10	0.50	Yamaichi	IC149-064-175-S5	PPS(GF)	500	150	30	5.8	N/A
17	SY-VQ100-1	TQ100	14x14	0.50	Yamaichi	IC149-100-125-S5	PPS(GF)	500	150	30	5.8	N/A
18	SY-TQ144	TQ144	20x20	0.50	Yamaichi	IC149-144-145-S5	PPS(GF)	500	150	30	5.8	N/A
19	SY-TQ176	TQ176	24x24	0.50	Yamaichi	IC149-176-166-S5	PPS(GF)	500	150	30	5.8	N/A
20	SY-PQ100-1	PQ100	14x20	0.65	Yamaichi	IC149-100-114-S5	PPS(GF)	500	150	30	N/A	N/A
21	SY-PQ144-1	PQ144	28x28	0.65	Yamaichi	IC149-144K11453-1	PPS(GF)	500	150	30	N/A	N/A
22	SY-PQ160-1	PQ160	28x28	0.65	Yamaichi	IC149-160-123-S5	PPS(GF)	500	150	30	N/A	N/A
23	SY-PQ208-2	PQ208	28x28	0.50	Yamaichi	IC149-208-161-S5	PPS(GF)	1,000	150	30	5.8	N/A
24	SY-PQ240	PQ240	32x32	0.50	Yamaichi	IC149-240-167-S5	PPS(GF)	1,000	150	30	5.8	N/A