

PART NUMBERING SYSTEM

Tuning Fork Crystal Units

When ordering or inquiring, please specify Part Number according to the following.

(Example Part Number)

CM315

Model

CFS-206
CFS-145
CFV-206
CMR200T
CMJ206
CM200C
CM250C
CM519
CM415
CM315
CM212

32,768

Frequency

Please mention numeral of the frequency in Hz unit.

Frequency Tolerance (at 25°C)

A +/-30ppm (STD)
B +/-50ppm
C +/-100ppm
D +/-20ppm (STD) 32.768kHz
E +/-10ppm
F +/-15ppm
G +/-25ppm
H +/-5ppm
Z Others

* Standard shall differ subject to frequency.

D Z F T

TAPE & REEL SPECIFICATION

T Tape & Reel
B Bulk

Load capacitance (CL)

A Series	G 13.0pF
B 6.0pF	Q 10.0pF
C 9.0pF (STD)	S 11.0pF
D 9.5pF	V 8.0pF
E 12.0pF	Y 7.0pF
F 12.5pF (STD)	Z Others

Frequency Tolerance over Operating Temperature Range

Z Standard Spec.