

| |
|---------------------|
| PCN_IIRA-31UJIT895 |
| CATALOG_PART_NBR |
| H0109700T-I/SN026 |
| HA1047-I/SO |
| HA1047T-I/SO |
| HA1599-E/SN |
| HA1599T-E/SN |
| HA2068-I/SO |
| HA2068T-I/SO |
| HA3078-I/SO |
| HA3078T-I/SO |
| MTCH112-I/SN |
| MTCH112T-I/SN |
| PIC12F1501-E/SN |
| PIC12F1501-I/SN |
| PIC12F1501T-E/SN |
| PIC12F1501T-E/SN022 |
| PIC12F1501T-I/SN |
| PIC12F1501T-I/SN027 |
| PIC12F1571-E/SN |
| PIC12F1571-I/SN |
| PIC12F1571T-I/SN |
| PIC12F1572-E/SN |
| PIC12F1572-I/SN |
| PIC12F1572T-E/SN |
| PIC12F1572T-I/SN |
| PIC12F1612-E/SN |
| PIC12F1612-I/SN |
| PIC12F1612T-I/SN |
| PIC12F1822-E/SN |
| PIC12F1822-E/SN027 |
| PIC12F1822-E/SN029 |
| PIC12F1822-E/SN030 |
| PIC12F1822-E/SN031 |
| PIC12F1822-E/SN032 |
| PIC12F1822-E/SN033 |
| PIC12F1822-E/SN041 |
| PIC12F1822-E/SNC07 |
| PIC12F1822-I/SN |
| PIC12F1822-I/SN028 |
| PIC12F1822-I/SN035 |
| PIC12F1822-I/SNC04 |
| PIC12F1822-I/SNC08 |
| PIC12F1822-I/SNC09 |
| PIC12F1822T-E/SN |
| PIC12F1822T-E/SNC07 |
| PIC12F1822T-I/SN |

| |
|----------------------|
| PIC12F1822T-I/SN020 |
| PIC12F1822T-I/SN025 |
| PIC12F1822T-I/SN026 |
| PIC12F1822T-I/SN039 |
| PIC12F1822T-I/SN044 |
| PIC12F1822T-I/SNC04 |
| PIC12F1822T-I/SNC08 |
| PIC12F1822T-I/SNC09 |
| PIC12F1840-E/SN |
| PIC12F1840-I/SN |
| PIC12F1840T-E/SN |
| PIC12F1840T-I/SN |
| PIC12LF1501-E/SN |
| PIC12LF1501-I/SN |
| PIC12LF1501T-E/SN |
| PIC12LF1501T-I/SN |
| PIC12LF1552-E/SN |
| PIC12LF1552-I/SN |
| PIC12LF1552T-I/SN |
| PIC12LF1571-E/SN |
| PIC12LF1571-I/SN |
| PIC12LF1571T-I/SN |
| PIC12LF1572-E/SN |
| PIC12LF1572-I/SN |
| PIC12LF1572T-I/SN |
| PIC12LF1612-E/SN |
| PIC12LF1612-I/SN |
| PIC12LF1612T-I/SN |
| PIC12LF1822-E/SN |
| PIC12LF1822-E/SNC01 |
| PIC12LF1822-I/SN |
| PIC12LF1822T-E/SN |
| PIC12LF1822T-E/SN024 |
| PIC12LF1822T-E/SN027 |
| PIC12LF1822T-E/SNC01 |
| PIC12LF1822T-I/SN |
| PIC12LF1840-E/SN |
| PIC12LF1840-I/SN |
| PIC12LF1840T-E/SN |
| PIC12LF1840T-I/SN |
| PIC16F1459-ICE/SO |
| PIC16F1512-E/SO |
| PIC16F1512-I/SO |
| PIC16F1512T-I/SO |
| PIC16F1513-E/SO |
| PIC16F1513-I/SO |
| PIC16F1513T-I/SO |

| |
|---------------------|
| PIC16F1516-E/SO |
| PIC16F1516-I/SO |
| PIC16F1516T-I/SO |
| PIC16F1518-E/SO |
| PIC16F1518-I/SO |
| PIC16F1518T-I/SO |
| PIC16F1713-E/SO |
| PIC16F1713-I/SO |
| PIC16F1713T-I/SO |
| PIC16F1716-E/SO |
| PIC16F1716-I/SO |
| PIC16F1716T-I/SO |
| PIC16F1782-E/SO |
| PIC16F1782-I/SO |
| PIC16F1782T-I/SO |
| PIC16F1783-E/SO |
| PIC16F1783-I/SO |
| PIC16F1783-I/SOC02 |
| PIC16F1783-I/SOC04 |
| PIC16F1783T-I/SO |
| PIC16F1783T-I/SOC02 |
| PIC16F1783T-I/SOC04 |
| PIC16F1786-E/SO |
| PIC16F1786-I/SO |
| PIC16F1786T-I/SO |
| PIC16F1788-E/SO |
| PIC16F1788-I/SO |
| PIC16F1788T-I/SO |
| PIC16F1933-E/SO |
| PIC16F1933-I/SO |
| PIC16F1933T-E/SO021 |
| PIC16F1933T-E/SO022 |
| PIC16F1933T-E/SO023 |
| PIC16F1933T-I/SO |
| PIC16F1936-E/SO |
| PIC16F1936-E/SOC06 |
| PIC16F1936-I/SO |
| PIC16F1936-I/SOC04 |
| PIC16F1936T-I/SO |
| PIC16F1936T-I/SO021 |
| PIC16F1936T-I/SO022 |
| PIC16F1936T-I/SO023 |
| PIC16F1936T-I/SO031 |
| PIC16F1936T-I/SO032 |
| PIC16F1936T-I/SOC04 |
| PIC16F1938-E/SO |
| PIC16F1938-I/SO |

| |
|---------------------|
| PIC16F1938T-I/SO |
| PIC16F722A-E/SO |
| PIC16F722A-I/SO |
| PIC16F722AT-I/SO |
| PIC16F722-E/SO |
| PIC16F722-I/SO |
| PIC16F722T-I/SO |
| PIC16F723A-E/SO |
| PIC16F723A-I/SO |
| PIC16F723A-I/SOC02 |
| PIC16F723AT-E/SO |
| PIC16F723AT-I/SO |
| PIC16F723AT-I/SOC02 |
| PIC16F723-E/SO |
| PIC16F723-I/SO |
| PIC16F723T-I/SO |
| PIC16F726-E/SO |
| PIC16F726-I/SO |
| PIC16F726T-E/SO |
| PIC16F726T-I/SO |
| PIC16LF1459-ICE/SO |
| PIC16LF1512-E/SO |
| PIC16LF1512-I/SO |
| PIC16LF1512T-I/SO |
| PIC16LF1513-E/SO |
| PIC16LF1513-I/SO |
| PIC16LF1513T-I/SO |
| PIC16LF1516-E/SO |
| PIC16LF1516-I/SO |
| PIC16LF1516T-I/SO |
| PIC16LF1518-E/SO |
| PIC16LF1518-I/SO |
| PIC16LF1518T-I/SO |
| PIC16LF1713-E/SO |
| PIC16LF1713-I/SO |
| PIC16LF1713T-I/SO |
| PIC16LF1716-E/SO |
| PIC16LF1716-I/SO |
| PIC16LF1716T-I/SO |
| PIC16LF1782-E/SO |
| PIC16LF1782-I/SO |
| PIC16LF1782T-I/SO |
| PIC16LF1783-E/SO |
| PIC16LF1783-I/SO |
| PIC16LF1783T-I/SO |
| PIC16LF1786-E/SO |
| PIC16LF1786-I/SO |

| |
|---------------------|
| PIC16LF1786T-I/SO |
| PIC16LF1788-E/SO |
| PIC16LF1788-I/SO |
| PIC16LF1788T-I/SO |
| PIC16LF1902-E/SO |
| PIC16LF1902-I/SO |
| PIC16LF1902T-I/SO |
| PIC16LF1903-E/SO |
| PIC16LF1903-I/SO |
| PIC16LF1903T-I/SO |
| PIC16LF1906-E/SO |
| PIC16LF1906-I/SO |
| PIC16LF1906T-I/SO |
| PIC16LF1933-E/SO |
| PIC16LF1933-I/SO |
| PIC16LF1933T-I/SO |
| PIC16LF1936-E/SO |
| PIC16LF1936-I/SO |
| PIC16LF1936T-I/SO |
| PIC16LF1938-E/SO |
| PIC16LF1938-I/SO |
| PIC16LF1938T-I/SO |
| PIC16LF722A-E/SO |
| PIC16LF722A-I/SO |
| PIC16LF722AT-I/SO |
| PIC16LF722-E/SO |
| PIC16LF722-I/SO |
| PIC16LF722T-I/SO |
| PIC16LF722T-I/SO024 |
| PIC16LF723A-E/SO |
| PIC16LF723A-I/SO |
| PIC16LF723AT-I/SO |
| PIC16LF723-E/SO |
| PIC16LF723-I/SO |
| PIC16LF723T-I/SO |
| PIC16LF726-E/SO |
| PIC16LF726-I/SO |
| PIC16LF726T-I/SO |
| PIC18F14K22-ICE/SO |
| PIC18F14K50-ICE/SO |
| PIC18F23K20-E/SO |
| PIC18F23K20-I/SO |
| PIC18F23K20T-I/SO |
| PIC18F23K22-E/SO |
| PIC18F23K22-I/SO |
| PIC18F23K22T-I/SO |
| PIC18F24K20-E/SO |

| |
|----------------------|
| PIC18F24K20-I/SO |
| PIC18F24K20-I/SO024 |
| PIC18F24K20-I/SO029 |
| PIC18F24K20-I/SO032 |
| PIC18F24K20T-I/SO |
| PIC18F24K20T-I/SO024 |
| PIC18F24K20T-I/SO029 |
| PIC18F24K20T-I/SO032 |
| PIC18F24K20T-I/SO033 |
| PIC18F24K22-E/SO |
| PIC18F24K22-I/SO |
| PIC18F24K22T-I/SO |
| PIC18F24K50-E/SO |
| PIC18F24K50-I/SO |
| PIC18F24K50T-I/SO |
| PIC18F25K20-E/SO |
| PIC18F25K20-E/SOC11 |
| PIC18F25K20-E/SOC12 |
| PIC18F25K20-I/SO |
| PIC18F25K20-I/SOLPR |
| PIC18F25K20T-E/SO |
| PIC18F25K20T-E/SOC11 |
| PIC18F25K20T-E/SOC12 |
| PIC18F25K20T-I/SO |
| PIC18F25K22-E/SO |
| PIC18F25K22-I/SO |
| PIC18F25K22-I/SOC02 |
| PIC18F25K22T-I/SO |
| PIC18F25K22T-I/SO020 |
| PIC18F25K22T-I/SOC02 |
| PIC18F25K50-E/SO |
| PIC18F25K50-I/SO |
| PIC18F25K50T-I/SO |
| PIC18F25K80-E/SO |
| PIC18F25K80-I/SO |
| PIC18F25K80-I/SOC01 |
| PIC18F25K80T-E/SO |
| PIC18F25K80T-I/SO |
| PIC18F25K80T-I/SOC01 |
| PIC18F26K20-E/SO |
| PIC18F26K20-I/SO |
| PIC18F26K20-I/SO024 |
| PIC18F26K20-I/SOC01 |
| PIC18F26K20-I/SOLPR |
| PIC18F26K20T-I/SO |
| PIC18F26K20T-I/SO024 |
| PIC18F26K20T-I/SOC01 |

| |
|-----------------------|
| PIC18F26K20T-I/SOLPR |
| PIC18F26K22-E/SO |
| PIC18F26K22-I/SO |
| PIC18F26K22-I/SOC02 |
| PIC18F26K22T-I/SO |
| PIC18F26K22T-I/SO021 |
| PIC18F26K22T-I/SO022 |
| PIC18F26K22T-I/SOC02 |
| PIC18F26K80-E/SO |
| PIC18F26K80-I/SO |
| PIC18F26K80T-E/SO |
| PIC18F26K80T-I/SO |
| PIC18LF14K22-ICE/SO |
| PIC18LF14K50-ICE/SO |
| PIC18LF23K22-E/SO |
| PIC18LF23K22-I/SO |
| PIC18LF23K22T-I/SO |
| PIC18LF24K22-E/SO |
| PIC18LF24K22-I/SO |
| PIC18LF24K22T-I/SO |
| PIC18LF24K50-E/SO |
| PIC18LF24K50-I/SO |
| PIC18LF24K50T-I/SO |
| PIC18LF25K22-E/SO |
| PIC18LF25K22-I/SO |
| PIC18LF25K22-I/SOC01 |
| PIC18LF25K22T-E/SO |
| PIC18LF25K22T-I/SO |
| PIC18LF25K22T-I/SOC01 |
| PIC18LF25K50-E/SO |
| PIC18LF25K50-I/SO |
| PIC18LF25K50T-I/SO |
| PIC18LF25K80-I/SO |
| PIC18LF25K80T-I/SO |
| PIC18LF26K22-E/SO |
| PIC18LF26K22-I/SO |
| PIC18LF26K22-I/SOC01 |
| PIC18LF26K22T-E/SO |
| PIC18LF26K22T-I/SO |
| PIC18LF26K22T-I/SOC01 |
| PIC18LF26K80-I/SO |
| PIC18LF26K80T-I/SO |
| PIC24F08KA102-E/SO |
| PIC24F08KA102-I/SO |
| PIC24F08KA102-I/SOC01 |
| PIC24F08KA102T-I/SO |
| PIC24F08KL302-E/SO |

| |
|----------------------|
| PIC24F08KL302-I/SO |
| PIC24F08KL302T-I/SO |
| PIC24F08KL402-E/SO |
| PIC24F08KL402-I/SO |
| PIC24F08KL402T-I/SO |
| PIC24F08KM102-E/SO |
| PIC24F08KM102-I/SO |
| PIC24F08KM102T-I/SO |
| PIC24F08KM202-E/SO |
| PIC24F08KM202-I/SO |
| PIC24F08KM202T-I/SO |
| PIC24F16KA102-E/SO |
| PIC24F16KA102-I/SO |
| PIC24F16KA102T-I/SO |
| PIC24F16KA302-E/SO |
| PIC24F16KA302-I/SO |
| PIC24F16KA302T-I/SO |
| PIC24F16KL402-E/SO |
| PIC24F16KL402-I/SO |
| PIC24F16KL402T-I/SO |
| PIC24F16KM102-E/SO |
| PIC24F16KM102-I/SO |
| PIC24F16KM102T-I/SO |
| PIC24F16KM202-E/SO |
| PIC24F16KM202-I/SO |
| PIC24F16KM202T-I/SO |
| PIC24F32KA302-E/SO |
| PIC24F32KA302-I/SO |
| PIC24F32KA302T-I/SO |
| PIC24FV08KM102-E/SO |
| PIC24FV08KM102-I/SO |
| PIC24FV08KM102T-I/SO |
| PIC24FV08KM202-E/SO |
| PIC24FV08KM202-I/SO |
| PIC24FV08KM202T-I/SO |
| PIC24FV16KA302-E/SO |
| PIC24FV16KA302-I/SO |
| PIC24FV16KA302T-I/SO |
| PIC24FV16KM102-E/SO |
| PIC24FV16KM102-I/SO |
| PIC24FV16KM102T-I/SO |
| PIC24FV16KM202-E/SO |
| PIC24FV16KM202-I/SO |
| PIC24FV16KM202T-I/SO |
| PIC24FV32KA302-E/SO |
| PIC24FV32KA302-I/SO |
| PIC24FV32KA302T-I/SO |