

PCN_JAON-01XOEE717
CATALOG_PART_NBR
11AA010-I/SN
11AA010T-I/SN
11AA020-I/SN
11AA020T-I/SN
11AA02E48-I/SN
11AA02E48T-I/SN
11AA02E64-I/SN
11AA02E64T-I/SN
11AA02UID-I/SN
11AA02UIDT-I/SN
11AA040-I/SN
11AA040T-I/SN
11AA080-I/SN
11AA080T-I/SN
11AA160-I/SN
11AA160T-I/SN
11AA161-I/SN
11AA161T-I/SN
11LC010-E/SN
11LC010-I/SN
11LC010T-E/SN
11LC010T-I/SN
11LC020-E/SN
11LC020-I/SN
11LC020T-E/SN
11LC020T-I/SN
11LC040-E/SN
11LC040-I/SN
11LC040T-E/SN
11LC040T-I/SN
11LC080-E/SN
11LC080-I/SN
11LC080T-E/SN
11LC080T-I/SN
11LC160-E/SN
11LC160-I/SN
11LC160T-E/SN
11LC160T-I/SN
11LC161-E/SN
11LC161-I/SN
11LC161T-E/SN
11LC161T-I/SN
24AA01/SN
24AA014H-I/SN
24AA014HT-I/SN

24AA014-I/SN
24AA014T-I/SN
24AA01H-I/SN
24AA01HT-I/SN
24AA01-I/SN
24AA01T/SN
24AA01T-I/SN
24AA02/SN
24AA02/SNB79
24AA024H-I/SN
24AA024HT-I/SN
24AA024-I/SN
24AA024T-I/SN
24AA025E48-E/SN
24AA025E48-I/SN
24AA025E48T-E/SN
24AA025E48T-I/SN
24AA025E64-E/SN
24AA025E64-I/SN
24AA025E64T-E/SN
24AA025E64T-I/SN
24AA025-I/SN
24AA025T-I/SN
24AA025UID-I/SN
24AA025UIDT-I/SN
24AA02E48-E/SN
24AA02E48-I/SN
24AA02E48T-E/SN
24AA02E48T-I/SN
24AA02E64-E/SN
24AA02E64-I/SN
24AA02E64T-E/SN
24AA02E64T-I/SN
24AA02H-I/SN
24AA02HT-I/SN
24AA02-I/SN
24AA02T/SN
24AA02T-I/SN
24AA02UID-I/SN
24AA02UIDT-I/SN
24AA52-I/SN
24AA52T-I/SN
24C01C/SN
24C01C-E/SN
24C01C-I/SN
24C01CT/SN
24C01CT-E/SN

24C01CT-I/SN
24C02C/SN
24C02C-E/SN
24C02C-I/SN
24C02CT/SN
24C02CT-E/SN
24C02CT-I/SN
24LC014-E/SN
24LC014H-E/SN
24LC014H-I/SN
24LC014HT-E/SN
24LC014HT-I/SN
24LC014-I/SN
24LC014T-E/SN
24LC014T-I/SN
24LC01B/SN
24LC01B-E/SN
24LC01BH-E/SN
24LC01BH-I/SN
24LC01BHT-E/SN
24LC01BHT-I/SN
24LC01B-I/SN
24LC01BT/SN
24LC01BT-E/SN
24LC01BT-I/SN
24LC024/SN
24LC024-E/SN
24LC024H-E/SN
24LC024H-I/SN
24LC024HT-E/SN
24LC024HT-I/SN
24LC024-I/SN
24LC024T/SN
24LC024T-E/SN
24LC024T-I/SN
24LC025/SN
24LC025-E/SN
24LC025-I/SN
24LC025T/SN
24LC025T-E/SN
24LC025T-I/SN
24LC02B/SN
24LC02B-E/SN
24LC02BH-E/SN
24LC02BH-I/SN
24LC02BH-I/SN100
24LC02BHT-E/SN

24LC02BHT-I/SN
24LC02B-I/SN
24LC02B-I/SNA32
24LC02BT/SN
24LC02BT/SNA31
24LC02BT-E/SN
24LC02BT-I/SN
24LC02BT-I/SN104
24LC02BT-I/SNA32
24LCS52/SN
24LCS52-I/SN
24LCS52T/SN
24LCS52T-I/SN
24VL014/SN
24VL014H/SN
24VL014HT/SN
24VL014T/SN
24VL024/SN
24VL024H/SN
24VL024HT/SN
24VL024T/SN
24VL025/SN
24VL025T/SN
34AA02-E/SN
34AA02-I/SN
34AA02T-E/SN
34AA02T-I/SN
34LC02-E/SN
34LC02-I/SN
34LC02T-E/SN
34LC02T-I/SN
34VL02/SN
34VL02T/SN
MCP79400-I/SN
MCP79400T-I/SN
MCP79401-I/SN
MCP79401T-I/SN
MCP79402-I/SN
MCP79402T-I/SN
MCP7940M-I/SN
MCP7940MT-I/SN
MCP7940N-E/SN
MCP7940N-I/SN
MCP7940NT-E/SN
MCP7940NT-I/SN
MCP79410-I/SN
MCP79410T-I/SN

MCP79411-I/SN

MCP79411T-I/SN

MCP79412-I/SN

MCP79412T-I/SN
