

Affected Catalog Part Numbers (CPN)

DSPIC33EP256GM706-I/PT
DSPIC33EP256GM706-I/MR
DSPIC33EP256GM706-H/PT
DSPIC33EP256GM706-H/MR
DSPIC33EP256GM706-E/PT
DSPIC33EP256GM706-E/MR
DSPIC33EP256GM304-I/PT
DSPIC33EP256GM304-I/ML
DSPIC33EP256GM304-H/PT
DSPIC33EP256GM304-H/ML
DSPIC33EP256GM304-E/PT
DSPIC33EP256GM304-E/ML
DSPIC33EP512GM706T-I/PT
DSPIC33EP512GM706T-I/MR
DSPIC33EP512GM706-I/PT
DSPIC33EP512GM706-I/MR
DSPIC33EP512GM706-H/PT
DSPIC33EP512GM706-H/MR
DSPIC33EP512GM706-E/PT
DSPIC33EP512GM706-E/MR
DSPIC33EP128GM604-I/PT
DSPIC33EP128GM604-I/ML
DSPIC33EP128GM604-H/PT
DSPIC33EP128GM604-H/ML
DSPIC33EP128GM604-E/PT
DSPIC33EP128GM604-E/ML
DSPIC33EP128GM310-I/PT
DSPIC33EP128GM310-I/PF
DSPIC33EP128GM310-I/BG
DSPIC33EP128GM310-H/PT
DSPIC33EP128GM310-H/PF
DSPIC33EP128GM310-H/BG
DSPIC33EP128GM310-E/PT
DSPIC33EP128GM310-E/PF
DSPIC33EP128GM310-E/BG
DSPIC33EP512GM604T-I/PT
DSPIC33EP512GM604T-I/ML
DSPIC33EP512GM604-I/PT
DSPIC33EP512GM604-I/ML
DSPIC33EP512GM604-H/PT
DSPIC33EP512GM604-H/ML
DSPIC33EP512GM604-E/PT
DSPIC33EP512GM604-E/ML
DSPIC33EP128GM304-I/PT
DSPIC33EP128GM304-I/ML
DSPIC33EP128GM304-H/PT
DSPIC33EP128GM304-H/ML

DSPIC33EP128GM304-E/PT
DSPIC33EP128GM304-E/ML
DSPIC33EP512GM306T-I/PT
DSPIC33EP512GM306T-I/MR
DSPIC33EP512GM306-I/PT
DSPIC33EP512GM306-I/MR
DSPIC33EP512GM306-H/PT
DSPIC33EP512GM306-H/MR
DSPIC33EP512GM306-E/PT
DSPIC33EP512GM306-E/MR
DSPIC33EP512GM304T-I/PT
DSPIC33EP512GM304T-I/ML
DSPIC33EP512GM304-I/PT
DSPIC33EP512GM304-I/ML
DSPIC33EP512GM304-H/PT
DSPIC33EP512GM304-H/ML
DSPIC33EP512GM304-E/PT
DSPIC33EP512GM304-E/ML
DSPIC33EP256GM306-I/PT
DSPIC33EP256GM306-I/MR
DSPIC33EP256GM306-H/PT
DSPIC33EP256GM306-H/MR
DSPIC33EP256GM306-E/PT
DSPIC33EP256GM306-E/MR
DSPIC33EP256GM604-I/PT
DSPIC33EP256GM604-I/ML
DSPIC33EP256GM604-H/PT
DSPIC33EP256GM604-H/ML
DSPIC33EP256GM604-E/PT
DSPIC33EP256GM604-E/ML
DSPIC33EP512GM310T-I/PT
DSPIC33EP512GM310T-I/PF
DSPIC33EP512GM310T-I/BG
DSPIC33EP512GM310-I/PT
DSPIC33EP512GM310-I/PF
DSPIC33EP512GM310-I/BG
DSPIC33EP512GM310-H/PT
DSPIC33EP512GM310-H/PF
DSPIC33EP512GM310-H/BG
DSPIC33EP512GM310-E/PT
DSPIC33EP512GM310-E/PF
DSPIC33EP512GM310-E/BG
DSPIC33EP256GM710-I/PT
DSPIC33EP256GM710-I/PF
DSPIC33EP256GM710-I/BG
DSPIC33EP256GM710-H/PT
DSPIC33EP256GM710-H/PF
DSPIC33EP256GM710-H/BG
DSPIC33EP256GM710-E/PT
DSPIC33EP256GM710-E/PF

DSPIC33EP256GM710-E/BG
DSPIC33EP128GM306-I/PT
DSPIC33EP128GM306-I/MR
DSPIC33EP128GM306-H/PT
DSPIC33EP128GM306-H/MR
DSPIC33EP128GM306-E/PT
DSPIC33EP128GM306-E/MR
DSPIC33EP256GM310-I/PT
DSPIC33EP256GM310-I/PF
DSPIC33EP256GM310-I/BG
DSPIC33EP256GM310-H/PT
DSPIC33EP256GM310-H/PF
DSPIC33EP256GM310-H/BG
DSPIC33EP256GM310-E/PT
DSPIC33EP256GM310-E/PF
DSPIC33EP256GM310-E/BG
DSPIC33EP128GM706-I/PT
DSPIC33EP128GM706-I/MR
DSPIC33EP128GM706-H/PT
DSPIC33EP128GM706-H/MR
DSPIC33EP128GM706-E/PT
DSPIC33EP128GM706-E/MR
DSPIC33EP512GM710T-I/PT
DSPIC33EP512GM710T-I/PF
DSPIC33EP512GM710T-I/BG
DSPIC33EP512GM710-I/PT
DSPIC33EP512GM710-I/PF
DSPIC33EP512GM710-I/BG
DSPIC33EP512GM710-H/PT
DSPIC33EP512GM710-H/PF
DSPIC33EP512GM710-H/BG
DSPIC33EP512GM710-E/PT
DSPIC33EP512GM710-E/PF
DSPIC33EP512GM710-E/BG
DSPIC33EP128GM710-I/PT
DSPIC33EP128GM710-I/PF
DSPIC33EP128GM710-I/BG
DSPIC33EP128GM710-H/PT
DSPIC33EP128GM710-H/PF
DSPIC33EP128GM710-H/BG
DSPIC33EP128GM710-E/PT
DSPIC33EP128GM710-E/PF
DSPIC33EP128GM710-E/BG