Simulator Peripheral Support by Device

Information taken from MPLAB X IDE device database files.

Table Headings: See a list of heading descriptions below the table.
Table Cells: To sort the data, use the CSV file in SimPeripheralSupport.zip.

Color Legend: *Green cells:* supported; *Gray cells:* no support.
Text Legend: *Peripheral Name(s):* supported; *Blank:* no support.

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
AT90CAN128	AC	ADC																	ExternalInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG									TC0, TC1, TC2, TC3	UART0, UART1			WDT
AT90CAN32	AC	ADC																	ExternalInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG									TC0, TC1, TC2, TC3	UART0, UART1			WDT
AT90CAN64	AC	ADC																	ExternalInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG									TC0, TC1, TC2, TC3	UART0, UART1			WDT
AT90PWM1																			ExternalInterrupt																			TC0, TC1				WDT
AT90PWM161																			ExternalInterrupt																			TC1				WDT
AT90PWM216																			ExternalInterrupt																			TC0, TC1		USART		WDT
AT90PWM2B																			ExternalInterrupt																			TC0, TC1		USART		WDT
AT90PWM316																			ExternalInterrupt																			TC0, TC1		USART		WDT
AT90PWM3B																			ExternalInterrupt																			TC0, TC1		USART		WDT
AT90PWM81																			ExternalInterrupt																			TC1				WDT
AT90USB1286																			ExternalInterrupt																			TC0, TC1, TC2, TC3	UART1			WDT
AT90USB1287																			ExternalInterrupt																			TC0, TC1, TC2, TC3	UART1			WDT
AT90USB162																			ExternalInterrupt																			TC0, TC1	UART1			WDT
AT90USB646																			ExternalInterrupt																			TC0, TC1, TC2, TC3	UART1			WDT
AT90USB647																			ExternalInterrupt																			TC0, TC1, TC2, TC3	UART1			WDT
AT90USB82																			ExternalInterrupt																			TC0, TC1	UART1			WDT
ATA5700M322																																										
ATA5702M322																																										
ATA5781																																										
ATA5782																																										
ATA5783																																										
ATA5787																																										
ATA5831																																										
ATA5832																																										
ATA5833																																										
ATA5835																																										
ATA8210																																										
ATA8215																																										
ATA8510																																										
ATA8515																																										
ATSAMA5D21																																										
ATSAMA5D22																																										
ATSAMA5D23																																										
ATSAMA5D24																																										
ATSAMA5D26																																										
ATSAMA5D27																																										
ATSAMA5D28																																										
ATSAMC20E15A	ACC																EIC	EVSYS									MPU			PORT_GROUP0							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC20E16A	ACC																EIC	EVSYS									MPU			PORT_GROUP0							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC20E17A	ACC																EIC	EVSYS									MPU			PORT_GROUP0							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC20E18A	ACC																EIC	EVSYS									MPU			PORT_GROUP0							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC20G15A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC20G16A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4				

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
ATSAMC20G17A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC20G18A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC20J15A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC20J16A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC20J17A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC20J18A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC20N17A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1, PORT_GROUP2							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAMC20N18A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1, PORT_GROUP2							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAMC21E15A	ACC																EIC	EVSYS									MPU			PORT_GROUP0							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC21E16A	ACC																EIC	EVSYS									MPU			PORT_GROUP0							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC21E17A	ACC																EIC	EVSYS									MPU			PORT_GROUP0							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC21E18A	ACC																EIC	EVSYS									MPU			PORT_GROUP0							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC21G15A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC21G16A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC21G17A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC21G18A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC21J15A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC21J16A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC21J17A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAMC21J18A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4				

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
ATSAMC21N17A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1, PORT_GROUP2							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAMC21N18A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1, PORT_GROUP2							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAMD09C13A																	EIC	EVSYS												PORT_GROUP0							SYSTICK	TC1, TC2				
ATSAMD09D14A																	EIC	EVSYS												PORT_GROUP0							SYSTICK	TC1, TC2				
ATSAMD10C13A	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC1, TC2				
ATSAMD10C14A	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC1, TC2				
ATSAMD11C14A	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC1, TC2				
ATSAMD20E14	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAMD20E14B	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAMD20E15	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAMD20E15B	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAMD20E16	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAMD20E16B	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAMD20E17	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAMD20E18	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAMD20G14	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAMD20G14B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAMD20G15	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAMD20G15B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAMD20G16	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
ATSAMD20G16B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAMD20G17	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAMD20G18	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAMD20J14	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAMD20J14B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAMD20J15	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAMD20J15B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAMD20J16	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAMD20J16B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAMD20J17	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAMD20J18	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAMD21E15B	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC3, TC4, TC5				
ATSAMD21E15CU	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC3, TC4, TC5				
ATSAMD21E15L	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC3, TC4, TC5				
ATSAMD21E16B	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC3, TC4, TC5				
ATSAMD21E16CU	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC3, TC4, TC5				
ATSAMD21E16L	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC3, TC4, TC5				
ATSAMD21E17A	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC3, TC4, TC5				
ATSAMD21E17D	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC3, TC4, TC5				

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
ATSAMD21E17L	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC3, TC4, TC5				
ATSAMD21E18A	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC3, TC4, TC5				
ATSAMD21G15B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC3, TC4, TC5				
ATSAMD21G16B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC3, TC4, TC5				
ATSAMD21G16L	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMD21G17A	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC3, TC4, TC5				
ATSAMD21G17D	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC3, TC4, TC5				
ATSAMD21G17L	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMD21G18A	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC3, TC4, TC5				
ATSAMD21J15B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMD21J16B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMD21J17A	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMD21J17D	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMD21J18A	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMD51G18A	ACC																EIC	EVSYS								MPU				PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3				
ATSAMD51G19A	ACC																EIC	EVSYS								MPU				PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3				
ATSAMD51J18A	ACC																EIC	EVSYS								MPU				PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAMD51J19A	ACC																EIC	EVSYS								MPU				PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAMD51J20A	ACC																EIC	EVSYS								MPU				PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAMD51N19A	ACC																EIC	EVSYS								MPU				PORT_GROUP0, PORT_GROUP1, PORT_GROUP2							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAMD51N20A	ACC																EIC	EVSYS								MPU				PORT_GROUP0, PORT_GROUP1, PORT_GROUP2							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAMD51P19A	ACC																EIC	EVSYS								MPU				PORT_GROUP0, PORT_GROUP1, PORT_GROUP2							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
ATSAMD51P20A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1, PORT_GROUP2							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAMDA1E14B	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMDA1E15B	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMDA1E16B	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMDA1G14B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMDA1G15B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMDA1G16B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMDA1J14B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMDA1J15B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMDA1J16B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAME51G18A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1, PORT_GROUP2							SYSTICK	TC0, TC1, TC2, TC3				
ATSAME51G19A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1, PORT_GROUP2							SYSTICK	TC0, TC1, TC2, TC3				
ATSAME51J18A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAME51J19A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAME51J20A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAME51N19A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1, PORT_GROUP2							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAME51N20A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1, PORT_GROUP2							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAME53J18A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAME53J19A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
ATSAME53J20A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5				
ATSAME53N19A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1, PORT_GROUP2							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAME53N20A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1, PORT_GROUP2							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAME54N19A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1, PORT_GROUP2							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAME54N20A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1, PORT_GROUP2							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAME54P19A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1, PORT_GROUP2							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAME54P20A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1, PORT_GROUP2							SYSTICK	TC0, TC1, TC2, TC3, TC4, TC5, TC6, TC7				
ATSAME70J19	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2			WDT
ATSAME70J19B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2			WDT
ATSAME70J20	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2			WDT
ATSAME70J20B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2			WDT
ATSAME70J21	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2			WDT
ATSAME70J21B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2			WDT
ATSAME70N19	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAME70N19B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAME70N20	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAME70N20B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAME70N21	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAME70N21B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
ATSAME70Q19	ACC														EEFC												MPU		PIOA, PIOB, PIOC, PIOD, PIOE						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAME70Q19B	ACC														EEFC												MPU		PIOA, PIOB, PIOC, PIOD, PIOE						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAME70Q20	ACC														EEFC												MPU		PIOA, PIOB, PIOC, PIOD, PIOE						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAME70Q20B	ACC														EEFC												MPU		PIOA, PIOB, PIOC, PIOD, PIOE						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAME70Q21	ACC														EEFC												MPU		PIOA, PIOB, PIOC, PIOD, PIOE						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAME70Q21B	ACC														EEFC												MPU		PIOA, PIOB, PIOC, PIOD, PIOE						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMG51G18															EEFC												MPU		PIOA, PIOB						RTT		SYSTICK		UART0, UART1			WDT
ATSAMG51N18															EEFC												MPU		PIOA, PIOB						RTT		SYSTICK		UART0, UART1			WDT
ATSAMG53G19															EEFC												MPU		PIOA, PIOB						RTT		SYSTICK		UART0, UART1			WDT
ATSAMG53N19															EEFC												MPU		PIOA, PIOB						RTT		SYSTICK		UART0, UART1			WDT
ATSAMG54G19															EEFC												MPU		PIOA, PIOB						RTT		SYSTICK		UART0, UART1			WDT
ATSAMG54J19															EEFC												MPU		PIOA, PIOB						RTT		SYSTICK		UART0, UART1			WDT
ATSAMG54N19															EEFC												MPU		PIOA, PIOB						RTT		SYSTICK		UART0, UART1			WDT
ATSAMG55G19															EEFC												MPU		PIOA, PIOB						RTT		SYSTICK					WDT
ATSAMG55J19															EEFC												MPU		PIOA, PIOB						RTT		SYSTICK					WDT
ATSAMHA1E14AB	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1								SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMHA1E15AB	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1								SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMHA1E16AB	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1								SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMHA1G14A	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1								SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMHA1G14AB	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1								SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMHA1G15A	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1								SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMHA1G15AB	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1								SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMHA1G16A	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1								SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAMHA1G16AB	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1								SYSTICK	TC3, TC4, TC5, TC6, TC7				
ATSAML10D14A	ACC																EIC	EVSYS									MPU			PORT_GROUP0								SYSTICK	TC0, TC1, TC2				

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
ATSAML10D15A	ACC																EIC	EVSYS									MPU			PORT_GROUP0							SYSTICK	TC0, TC1, TC2				
ATSAML10D16A	ACC																EIC	EVSYS									MPU			PORT_GROUP0							SYSTICK	TC0, TC1, TC2				
ATSAML10E14A	ACC																EIC	EVSYS									MPU			PORT_GROUP0							SYSTICK	TC0, TC1, TC2				
ATSAML10E15A	ACC																EIC	EVSYS									MPU			PORT_GROUP0							SYSTICK	TC0, TC1, TC2				
ATSAML10E16A	ACC																EIC	EVSYS									MPU			PORT_GROUP0							SYSTICK	TC0, TC1, TC2				
ATSAML11D14A	ACC																EIC	EVSYS						IDAU			MPU, MPU_NS			PORT_GROUP0							SYSTICK, SYSTICK_NS	TC0, TC1, TC2				
ATSAML11D15A	ACC																EIC	EVSYS						IDAU			MPU, MPU_NS			PORT_GROUP0							SYSTICK, SYSTICK_NS	TC0, TC1, TC2				
ATSAML11D16A	ACC																EIC	EVSYS						IDAU			MPU, MPU_NS			PORT_GROUP0							SYSTICK, SYSTICK_NS	TC0, TC1, TC2				
ATSAML11E14A	ACC																EIC	EVSYS						IDAU			MPU, MPU_NS			PORT_GROUP0							SYSTICK, SYSTICK_NS	TC0, TC1, TC2				
ATSAML11E15A	ACC																EIC	EVSYS						IDAU			MPU, MPU_NS			PORT_GROUP0							SYSTICK, SYSTICK_NS	TC0, TC1, TC2				
ATSAML11E16A	ACC																EIC	EVSYS						IDAU			MPU, MPU_NS			PORT_GROUP0							SYSTICK, SYSTICK_NS	TC0, TC1, TC2				
ATSAML21E15B	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC0, TC1, TC4				
ATSAML21E16B	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC0, TC1, TC4				
ATSAML21E17B	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC0, TC1, TC4				
ATSAML21E18B	ACC																EIC	EVSYS												PORT_GROUP0							SYSTICK	TC0, TC1, TC4				
ATSAML21G16B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC4				
ATSAML21G17B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC4				
ATSAML21G18B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC4				
ATSAML21J16B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAML21J17B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAML21J18B	ACC																EIC	EVSYS												PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3, TC4				
ATSAML22G16A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3				
ATSAML22G17A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3				
ATSAML22G18A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3				
ATSAML22J16A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3				
ATSAML22J17A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3				
ATSAML22J18A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1							SYSTICK	TC0, TC1, TC2, TC3				
ATSAML22N16A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1, PORT_GROUP2							SYSTICK	TC0, TC1, TC2, TC3				
ATSAML22N17A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1, PORT_GROUP2							SYSTICK	TC0, TC1, TC2, TC3				
ATSAML22N18A	ACC																EIC	EVSYS									MPU			PORT_GROUP0, PORT_GROUP1, PORT_GROUP2							SYSTICK	TC0, TC1, TC2, TC3				

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
ATSAMS70J19	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2			WDT
ATSAMS70J19B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2			WDT
ATSAMS70J20	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2			WDT
ATSAMS70J20B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2			WDT
ATSAMS70J21	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2			WDT
ATSAMS70J21B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2			WDT
ATSAMS70N19	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMS70N19B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMS70N20	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMS70N20B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMS70N21	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMS70N21B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMS70Q19	ACC														EEFC												MPU		PIOA, PIOB, PIOC, PIOD, PIOE						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMS70Q19B	ACC														EEFC												MPU		PIOA, PIOB, PIOC, PIOD, PIOE						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMS70Q20	ACC														EEFC												MPU		PIOA, PIOB, PIOC, PIOD, PIOE						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMS70Q20B	ACC														EEFC												MPU		PIOA, PIOB, PIOC, PIOD, PIOE						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMS70Q21	ACC														EEFC												MPU		PIOA, PIOB, PIOC, PIOD, PIOE						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMS70Q21B	ACC														EEFC												MPU		PIOA, PIOB, PIOC, PIOD, PIOE						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMV70J19B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2			WDT
ATSAMV70J20B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2			WDT
ATSAMV70N19B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMV70N20B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
ATSAMV70Q19B	ACC														EEFC												MPU		PIOA, PIOB, PIOC, PIOD, PIOE						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMV70Q20B	ACC														EEFC												MPU		PIOA, PIOB, PIOC, PIOD, PIOE						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMV71J19B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2			WDT
ATSAMV71J20B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2			WDT
ATSAMV71J21B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2			WDT
ATSAMV71N19B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMV71N20B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMV71N21B	ACC														EEFC												MPU		PIOA, PIOB, PIOD						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMV71Q19B	ACC														EEFC												MPU		PIOA, PIOB, PIOC, PIOD, PIOE						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMV71Q20B	ACC														EEFC												MPU		PIOA, PIOB, PIOC, PIOD, PIOE						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMV71Q21	ACC														EEFC												MPU		PIOA, PIOB, PIOC, PIOD, PIOE						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATSAMV71Q21B	ACC														EEFC												MPU		PIOA, PIOB, PIOC, PIOD, PIOE						RTT		SYSTICK		UART0, UART1, UART2, UART3, UART4			WDT
ATmega128																			ExternalInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG									TC0, TC1, TC2, TC3	UART0, UART1			WDT
ATmega1280	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK, PORTL									TC0, TC1, TC2, TC3, TC4, TC5	UART0, UART1, UART2, UART3			WDT
ATmega1281	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG									TC0, TC1, TC2, TC3, TC4, TC5	UART0, UART1			WDT
ATmega1284	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD									TC0, TC1, TC2, TC3	UART0, UART1			WDT
ATmega1284P	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD									TC0, TC1, TC2, TC3	UART0, UART1			WDT
ATmega1284RFR2																			ExternalInterrupt																			TC0, TC1, TC2, TC3, TC4, TC5	UART0, UART1			WDT
ATmega128A																			ExternalInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG									TC0, TC1, TC2, TC3	UART0, UART1			WDT
ATmega128RFA1																			ExternalInterrupt																			TC0, TC1, TC2, TC3, TC4, TC5	UART0, UART1			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
ATmega128RFR2																			ExternalInterrupt																			TC0, TC1, TC2, TC3, TC4, TC5	UART0, UART1			WDT
ATmega16																			ExternalInterrupt											PORTA, PORTB, PORTC, PORTD									TC0, TC1, TC2		USART		WDT
ATmega1608	AC	ADC																EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF									TCA0, TCB0, TCB1, TCB2		USART0, USART1, USART2	VREF	
ATmega1609	AC	ADC																EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF									TCA0, TCB0, TCB1, TCB2, TCB3		USART0, USART1, USART2, USART3	VREF	
ATmega162																																						TC0, TC1, TC2, TC3				WDT
ATmega164A	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD									TC0, TC1, TC2	UART0, UART1			WDT
ATmega164P	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD									TC0, TC1, TC2	UART0, UART1			WDT
ATmega164PA	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD									TC0, TC1, TC2	UART0, UART1			WDT
ATmega165A																																						TC0, TC1, TC2	UART0			WDT
ATmega165P																																						TC0, TC1, TC2	UART0			WDT
ATmega165PA																																						TC0, TC1, TC2	UART0			WDT
ATmega168	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD									TC0, TC1, TC2	UART0			WDT
ATmega168A	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD									TC0, TC1, TC2	UART0			WDT
ATmega168P	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD									TC0, TC1, TC2	UART0			WDT
ATmega168PA	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD									TC0, TC1, TC2	UART0			WDT
ATmega168PB	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD, PORTE									TC0, TC1, TC2	UART0			WDT
ATmega169A	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG									TC0, TC1, TC2	UART0			WDT
ATmega169P	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG									TC0, TC1, TC2	UART0			WDT
ATmega169PA	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG									TC0, TC1, TC2	UART0			WDT
ATmega16A																			ExternalInterrupt											PORTA, PORTB, PORTC, PORTD									TC0, TC1, TC2		USART		WDT
ATmega16M1																			ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD, PORTE									TC0, TC1				WDT
ATmega16U2																			ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD									TC0, TC1	UART1			WDT
ATmega16U4																			ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD, PORTE, PORTF									TC0, TC1, TC3, TC4	UART1			WDT
ATmega2560	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK, PORTL									TC0, TC1, TC2, TC3, TC4, TC5	UART0, UART1, UART2, UART3			WDT
ATmega2561	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG									TC0, TC1, TC2, TC3, TC4, TC5	UART0, UART1			WDT
ATmega2564RFR2																			ExternalInterrupt																			TC0, TC1, TC2, TC3, TC4, TC5	UART0, UART1			WDT
ATmega256RFR2																			ExternalInterrupt																			TC0, TC1, TC2, TC3, TC4, TC5	UART0, UART1			WDT
ATmega32																			ExternalInterrupt											PORTA, PORTB, PORTC, PORTD									TC0, TC1, TC2		USART		WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
ATmega3208	AC	ADC																EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF								TCA0, TCB0, TCB1, TCB2		USART0, USART1, USART2	VREF	
ATmega3209	AC	ADC																EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF								TCA0, TCB0, TCB1, TCB2, TCB3		USART0, USART1, USART2, USART3	VREF	
ATmega324A	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD								TC0, TC1, TC2	UART0, UART1			WDT
ATmega324P	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD								TC0, TC1, TC2	UART0, UART1			WDT
ATmega324PA	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD								TC0, TC1, TC2	UART0, UART1			WDT
ATmega324PB	AC																		ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE								TC0, TC1, TC2, TC3, TC4	UART0, UART1, UART2			WDT
ATmega325																																						TC0, TC1, TC2	UART0			WDT
ATmega3250																																						TC0, TC1, TC2	UART0			WDT
ATmega3250A																																						TC0, TC1, TC2	UART0			WDT
ATmega3250P																																						TC0, TC1, TC2	UART0			WDT
ATmega3250PA																																						TC0, TC1, TC2	UART0			WDT
ATmega325A																																						TC0, TC1, TC2	UART0			WDT
ATmega325P																																						TC0, TC1, TC2	UART0			WDT
ATmega325PA																																						TC0, TC1, TC2	UART0			WDT
ATmega328	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD								TC0, TC1, TC2	UART0			WDT
ATmega328P	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD								TC0, TC1, TC2	UART0			WDT
ATmega328PB	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD, PORTE								TC0, TC1, TC2, TC3, TC4	UART0, UART1			WDT
ATmega329	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG								TC0, TC1, TC2	UART0			WDT
ATmega3290																																						TC0, TC1, TC2	UART0			WDT
ATmega3290A																																						TC0, TC1, TC2	UART0			WDT
ATmega3290P																																						TC0, TC1, TC2	UART0			WDT
ATmega3290PA																																						TC0, TC1, TC2	UART0			WDT
ATmega329A	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG								TC0, TC1, TC2	UART0			WDT
ATmega329P	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG								TC0, TC1, TC2	UART0			WDT
ATmega329PA	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG								TC0, TC1, TC2	UART0			WDT
ATmega32A																			ExternalInterrupt											PORTA, PORTB, PORTC, PORTD								TC0, TC1, TC2		USART		WDT
ATmega32C1																			ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD, PORTE								TC0, TC1				WDT
ATmega32M1																			ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD, PORTE								TC0, TC1				WDT
ATmega32U2																			ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD								TC0, TC1	UART1			WDT
ATmega32U4																			ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD, PORTE, PORTF								TC0, TC1, TC3, TC4	UART1			WDT
ATmega406																			ExternalInterrupt																			TC0				WDT
ATmega48	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD								TC0, TC1, TC2	UART0			WDT
ATmega4808	AC	ADC																EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF								TCA0, TCB0, TCB1, TCB2		USART0, USART1, USART2	VREF	

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
ATmega4809	AC	ADC																EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF								TCA0, TCB0, TCB1, TCB2, TCB3		USART0, USART1, USART2, USART3	VREF	
ATmega48A	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD								TC0, TC1, TC2	UART0			WDT
ATmega48P	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD								TC0, TC1, TC2	UART0			WDT
ATmega48PA	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD								TC0, TC1, TC2	UART0			WDT
ATmega48PB	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD, PORTE								TC0, TC1, TC2	UART0			WDT
ATmega64																			ExternalInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG								TC0, TC1, TC2, TC3	UART0, UART1			WDT
ATmega640	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK, PORTL								TC0, TC1, TC2, TC3, TC4, TC5	UART0, UART1, UART2, UART3			WDT
ATmega644	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD								TC0, TC1, TC2	UART0			WDT
ATmega644A	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD								TC0, TC1, TC2	UART0, UART1			WDT
ATmega644P	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD								TC0, TC1, TC2	UART0, UART1			WDT
ATmega644PA	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD								TC0, TC1, TC2	UART0, UART1			WDT
ATmega644RFR2																			ExternalInterrupt																			TC0, TC1, TC2, TC3, TC4, TC5	UART0, UART1			WDT
ATmega645																																						TC0, TC1, TC2	UART0			WDT
ATmega6450																																						TC0, TC1, TC2	UART0			WDT
ATmega6450A																																						TC0, TC1, TC2	UART0			WDT
ATmega6450P																																						TC0, TC1, TC2	UART0			WDT
ATmega645A																																						TC0, TC1, TC2	UART0			WDT
ATmega645P																																						TC0, TC1, TC2	UART0			WDT
ATmega649	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG								TC0, TC1, TC2	UART0			WDT
ATmega6490																																						TC0, TC1, TC2	UART0			WDT
ATmega6490A																																						TC0, TC1, TC2	UART0			WDT
ATmega6490P																																						TC0, TC1, TC2	UART0			WDT
ATmega649A	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG								TC0, TC1, TC2	UART0			WDT
ATmega649P	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG								TC0, TC1, TC2	UART0			WDT
ATmega64A																			ExternalInterrupt											PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG								TC0, TC1, TC2, TC3	UART0, UART1			WDT
ATmega64C1																			ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD, PORTE								TC0, TC1				WDT
ATmega64M1																			ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD, PORTE								TC0, TC1				WDT
ATmega64RFR2																			ExternalInterrupt																			TC0, TC1, TC2, TC3, TC4, TC5	UART0, UART1			WDT
ATmega8																			ExternalInterrupt											PORTB, PORTC, PORTD								TC0, TC1, TC2		USART		WDT
ATmega808	AC	ADC																EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF								TCA0, TCB0, TCB1, TCB2		USART0, USART1, USART2	VREF	

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
ATmega809	AC	ADC																EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF								TCA0, TCB0, TCB1, TCB2, TCB3		USART0, USART1, USART2, USART3	VREF	
ATmega8515																																						TC0, TC1		USART		WDT
ATmega8535																																						TC0, TC1, TC2		USART		WDT
ATmega88	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD								TC0, TC1, TC2	UART0			WDT
ATmega88A	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD								TC0, TC1, TC2	UART0			WDT
ATmega88P	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD								TC0, TC1, TC2	UART0			WDT
ATmega88PA	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD								TC0, TC1, TC2	UART0			WDT
ATmega88PB	AC	ADC																	ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD, PORTE								TC0, TC1, TC2	UART0			WDT
ATmega8A																			ExternalInterrupt											PORTB, PORTC, PORTD								TC0, TC1, TC2		USART		WDT
ATmega8U2																			ExternalInterrupt, PinChangeInterrupt											PORTB, PORTC, PORTD								TC0, TC1	UART1			WDT
ATtiny10																			ExternalInterrupt											PORTB								TC0				WDT
ATtiny102																			ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB								TC0		USART		WDT
ATtiny104																			ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB								TC0		USART		WDT
ATtiny11																																						TC0				
ATtiny12																																						TC0				WDT
ATtiny13																														PORTB								TC0				WDT
ATtiny13A																														PORTB								TC0				WDT
ATtiny15																																						TC0				WDT
ATtiny1604		ADC																EVSYS												PORTA, PORTB, PORTC, PORTMUX								TCA0, TCB0		USART0	VREF	
ATtiny1606		ADC																EVSYS												PORTA, PORTB, PORTC, PORTMUX								TCA0, TCB0		USART0	VREF	
ATtiny1607		ADC																EVSYS												PORTA, PORTB, PORTC, PORTMUX								TCA0, TCB0		USART0	VREF	
ATtiny1614	AC	ADC																EVSYS												PORTA, PORTB, PORTMUX								TCA0, TCB0, TCB1, TCD		USART0	VREF	
ATtiny1616	AC	ADC																EVSYS												PORTA, PORTB, PORTC, PORTMUX								TCA0, TCB0, TCB1, TCD		USART0	VREF	
ATtiny1617	AC	ADC																EVSYS												PORTA, PORTB, PORTC, PORTMUX								TCA0, TCB0, TCB1, TCD		USART0	VREF	
ATtiny1624	AC																	EVSYS												PORTA, PORTB, PORTC								TCA0, TCB0, TCB1		USART0, USART1	VREF	
ATtiny1626	AC																	EVSYS												PORTA, PORTB, PORTC								TCA0, TCB0, TCB1		USART0, USART1	VREF	
ATtiny1627	AC																	EVSYS												PORTA, PORTB, PORTC								TCA0, TCB0, TCB1		USART0, USART1	VREF	
ATtiny1634																																						TC0, TC1	UART0, UART1			WDT
ATtiny167																			ExternalInterrupt																			TC0, TC1				WDT
ATtiny20																			ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB								TC0, TC1				WDT
ATtiny202		ADC																EVSYS												PORTA, PORTMUX								TCA0, TCB0		USART0	VREF	
ATtiny204		ADC																EVSYS												PORTA, PORTB, PORTMUX								TCA0, TCB0		USART0	VREF	
ATtiny212	AC	ADC																EVSYS												PORTA, PORTMUX								TCA0, TCB0, TCD		USART0	VREF	
ATtiny214	AC	ADC																EVSYS												PORTA, PORTB, PORTMUX								TCA0, TCB0, TCD		USART0	VREF	
ATtiny2313																																						TC0, TC1		USART		WDT
ATtiny2313A																																						TC0, TC1		USART		WDT
ATtiny24																																						TC0, TC1				WDT
ATtiny24A																			ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB								TC0, TC1				WDT
ATtiny25																			ExternalInterrupt											PORTB								TC0				WDT
ATtiny26																																										WDT
ATtiny261																			ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB								TC0, TC1				WDT
ATtiny261A																																						TC0				WDT
ATtiny3216	AC	ADC																EVSYS												PORTA, PORTB, PORTC, PORTMUX								TCA0, TCB0, TCB1, TCD		USART0	VREF	
ATtiny3217	AC	ADC																EVSYS												PORTA, PORTB, PORTC, PORTMUX								TCA0, TCB0, TCB1, TCD		USART0	VREF	

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
ATtiny4																			ExternalInterrupt											PORTB								TC0				WDT
ATtiny40																			ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC								TC0				WDT
ATtiny402		ADC																EVSYS												PORTA, PORTMUX								TCA0, TCB0		USART0	VREF	
ATtiny404		ADC																EVSYS												PORTA, PORTB, PORTMUX								TCA0, TCB0		USART0	VREF	
ATtiny406		ADC																EVSYS												PORTA, PORTB, PORTC, PORTMUX								TCA0, TCB0		USART0	VREF	
ATtiny412	AC	ADC																EVSYS												PORTA, PORTMUX								TCA0, TCB0, TCD		USART0	VREF	
ATtiny414	AC	ADC																EVSYS												PORTA, PORTB, PORTMUX								TCA0, TCB0, TCD		USART0	VREF	
ATtiny416	AC	ADC																EVSYS												PORTA, PORTB, PORTC, PORTMUX								TCA0, TCB0, TCD		USART0	VREF	
ATtiny416auto	AC	ADC																EVSYS												PORTA, PORTB, PORTC, PORTMUX								TCA0, TCB0, TCD		USART0	VREF	
ATtiny417	AC	ADC																EVSYS												PORTA, PORTB, PORTC, PORTMUX								TCA0, TCB0, TCD		USART0	VREF	
ATtiny4313																																						TC0, TC1		USART		WDT
ATtiny43U																																						TC0				WDT
ATtiny44																																						TC0, TC1				WDT
ATtiny441																			ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB								TC0, TC1, TC2	UART0, UART1			WDT
ATtiny44A																			ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB								TC0, TC1				WDT
ATtiny45																			ExternalInterrupt											PORTB								TC0				WDT
ATtiny461																			ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB								TC0, TC1				WDT
ATtiny461A																																						TC0				WDT
ATtiny48	AC																		ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD								TC0, TC1				WDT
ATtiny5																			ExternalInterrupt											PORTB								TC0				WDT
ATtiny804		ADC																EVSYS												PORTA, PORTB, PORTC, PORTMUX								TCA0, TCB0		USART0	VREF	
ATtiny806		ADC																EVSYS												PORTA, PORTB, PORTC, PORTMUX								TCA0, TCB0		USART0	VREF	
ATtiny807		ADC																EVSYS												PORTA, PORTB, PORTC, PORTMUX								TCA0, TCB0		USART0	VREF	
ATtiny814	AC	ADC																EVSYS												PORTA, PORTB, PORTMUX								TCA0, TCB0, TCD		USART0	VREF	
ATtiny816	AC	ADC																EVSYS												PORTA, PORTB, PORTC, PORTMUX								TCA0, TCB0, TCD		USART0	VREF	
ATtiny817	AC	ADC																EVSYS												PORTA, PORTB, PORTC, PORTMUX								TCA0, TCB0, TCD		USART0	VREF	
ATtiny828																			ExternalInterrupt																			TC0, TC1		USART		WDT
ATtiny84																																						TC0, TC1				WDT
ATtiny841																			ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB								TC0, TC1, TC2	UART0, UART1			WDT
ATtiny84A																			ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB								TC0, TC1				WDT
ATtiny85																			ExternalInterrupt											PORTB								TC0				WDT
ATtiny861																			ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB								TC0, TC1				WDT
ATtiny861A																																						TC0				WDT
ATtiny87																			ExternalInterrupt																			TC0, TC1				WDT
ATtiny88	AC																		ExternalInterrupt, PinChangeInterrupt											PORTA, PORTB, PORTC, PORTD								TC0, TC1				WDT
ATtiny9																			ExternalInterrupt											PORTB								TC0				WDT
ATxmega128A1																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTH, PORTJ, PORTK, PORTQ, PORTR										USARTC0, USARTC1, USARTD0, USARTD1, USARTE0, USARTE1, USARTF0, USARTF1			

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
ATxmega128A1U		ADC																EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTH, PORTJ, PORTK, PORTMUX, PORTQ, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCD1, TCE0_TCE2, TCE1, TCF0_TCF2, TCF1		USARTC0, USARTC1, USARTD0, USARTD1, USARTE0, USARTE1, USARTF0, USARTF1		
ATxmega128A3																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTR										USARTC0, USARTC1, USARTD0, USARTD1, USARTE0, USARTE1, USARTF0, USARTF1		
ATxmega128A3U		ADC																EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCD1, TCE0_TCE2, TCE1, TCF0_TCF2		USARTC0, USARTC1, USARTD0, USARTD1, USARTE0, USARTE1, USARTF0		
ATxmega128A4U		ADC																EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCD1, TCE0_TCE2		USARTC0, USARTC1, USARTD0, USARTD1, USARTE0		
ATxmega128B1																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTG, PORTM, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCE0_TCE2		USARTC0, USARTE0		
ATxmega128B3																		EVSYS												PORTB, PORTC, PORTD, PORTG, PORTM, PORTMUX, PORTR								TCC0_TCC2, TCC1		USARTC0		
ATxmega128C3																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCE0_TCE2, TCF0_TCF2		USARTC0, USARTD0, USARTE0		
ATxmega128D3																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCE0_TCE2, TCF0_TCF2		USARTC0, USARTD0, USARTE0		
ATxmega128D4																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCE0_TCE2		USARTC0, USARTD0		
ATxmega16A4																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTR										USARTC0, USARTC1, USARTD0, USARTD1, USARTE0		

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
ATxmega16A4U		ADC																EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCD1, TCE0_TCE2		USARTC0, USARTC1, USARTD0, USARTD1, USARTE0		
ATxmega16C4																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCE0_TCE2		USARTC0, USARTC1, USARTD0		
ATxmega16D4																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCE0_TCE2		USARTC0, USARTD0		
ATxmega16E5		ADC												EDMA				EVSYS												PORTA, PORTC, PORTD, PORTMUX, PORTR								TCC4, TCC5, TCD5		USARTC0, USARTD0		
ATxmega192A3																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTR										USARTC0, USARTC1, USARTD0, USARTD1, USARTE0, USARTE1, USARTF0, USARTF1		
ATxmega192A3U		ADC																EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCD1, TCE0_TCE2, TCE1, TCF0_TCF2		USARTC0, USARTC1, USARTD0, USARTD1, USARTE0, USARTE1, USARTF0		
ATxmega192C3																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTMUX, PORTR										USARTC0, USARTD0, USARTE0		
ATxmega192D3																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCE0_TCE2, TCF0_TCF2		USARTC0, USARTD0, USARTE0		
ATxmega256A3																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTR										USARTC0, USARTC1, USARTD0, USARTD1, USARTE0, USARTE1, USARTF0, USARTF1		
ATxmega256A3B																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTR										USARTC0, USARTC1, USARTD0, USARTD1, USARTE0, USARTF0		

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
ATxmega256A3BU		ADC																EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCD1, TCE0_TCE2, TCE1, TCF0_TCF2		USARTC0, USARTC1, USARTD0, USARTD1, USARTE0, USARTF0		
ATxmega256A3U		ADC																EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCD1, TCE0_TCE2, TCE1, TCF0_TCF2		USARTC0, USARTC1, USARTD0, USARTD1, USARTE0, USARTE1, USARTF0		
ATxmega256C3																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCE0_TCE2, TCF0_TCF2		USARTC0, USARTD0, USARTE0		
ATxmega256D3																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCE0_TCE2, TCF0_TCF2		USARTC0, USARTD0, USARTE0		
ATxmega32A4																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTR										USARTC0, USARTC1, USARTD0, USARTD1, USARTE0		
ATxmega32A4U		ADC																EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCD1, TCE0_TCE2		USARTC0, USARTC1, USARTD0, USARTD1, USARTE0		
ATxmega32C3																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCE0_TCE2, TCF0_TCF2		USARTC0, USARTD0, USARTE0		
ATxmega32C4																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCE0_TCE2		USARTC0, USARTC1, USARTD0		
ATxmega32D3																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCE0_TCE2, TCF0_TCF2		USARTC0, USARTD0, USARTE0		
ATxmega32D4																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCE0_TCE2		USARTC0, USARTD0		
ATxmega32E5		ADC												EDMA				EVSYS												PORTA, PORTC, PORTD, PORTMUX, PORTR								TCC4, TCC5, TCD5		USARTC0, USARTD0		

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
ATxmega384C3																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCE0_TCE2, TCF0_TCF2		USARTC0, USARTD0, USARTE0		
ATxmega384D3																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCE0_TCE2, TCF0_TCF2		USARTC0, USARTD0, USARTE0, USARTF0		
ATxmega64A1																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTH, PORTJ, PORTK, PORTQ, PORTR										USARTC0, USARTC1, USARTD0, USARTD1, USARTE0, USARTE1, USARTF0, USARTF1		
ATxmega64A1U		ADC																EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTH, PORTJ, PORTK, PORTMUX, PORTQ, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCD1, TCE0_TCE2, TCE1, TCF0_TCF2, TCF1		USARTC0, USARTC1, USARTD0, USARTD1, USARTE0, USARTE1, USARTF0, USARTF1		
ATxmega64A3																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTR										USARTC0, USARTC1, USARTD0, USARTD1, USARTE0, USARTE1, USARTF0, USARTF1		
ATxmega64A3U		ADC																EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCD1, TCE0_TCE2, TCE1, TCF0_TCF2		USARTC0, USARTC1, USARTD0, USARTD1, USARTE0, USARTE1, USARTF0		
ATxmega64A4U		ADC																EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCD1, TCE0_TCE2		USARTC0, USARTC1, USARTD0, USARTD1, USARTE0		
ATxmega64B1																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTG, PORTM, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCE0_TCE2		USARTC0, USARTE0		
ATxmega64B3																		EVSYS												PORTB, PORTC, PORTD, PORTG, PORTM, PORTMUX, PORTR								TCC0_TCC2, TCC1		USARTC0		

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
ATxmega64C3																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCE0_TCE2, TCF0_TCF2		USARTC0, USARTD0, USARTE0		
ATxmega64D3																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCE0_TCE2, TCF0_TCF2		USARTC0, USARTD0, USARTE0		
ATxmega64D4																		EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTMUX, PORTR								TCC0_TCC2, TCC1, TCD0_TCD2, TCE0_TCE2		USARTC0, USARTD0		
ATxmega8E5		ADC												EDMA				EVSYS												PORTA, PORTC, PORTD, PORTMUX, PORTR								TCC4, TCC5, TCD5		USARTC0, USARTD0		
AVR128DA28		ADC																EVSYS												PORTA, PORTC, PORTD, PORTF								TCA0, TCB0, TCB1, TCB2, TCD		USART0, USART1, USART2		
AVR128DA32		ADC																EVSYS												PORTA, PORTC, PORTD, PORTF								TCA0, TCB0, TCB1, TCB2, TCD		USART0, USART1, USART2		
AVR128DA48		ADC																EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF								TCA0, TCA1, TCB0, TCB1, TCB2, TCB3, TCD		USART0, USART1, USART2, USART3, USART4		
AVR128DA64		ADC																EVSYS												PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG								TCA0, TCA1, TCB0, TCB1, TCB2, TCB3, TCB4, TCD		USART0, USART1, USART2, USART3, USART4, USART5		
CEC1712H_B2_SX																																					SYSTICK					
CEC1712H_S2_SX																																					SYSTICK					
MCV08A		ADC					COMP1															GPIO						OSC					PullUp					TMR0				WDT
MCV14A		ADC					COMP1, COMP2									EEFlash												OSC		PORTB, PORTC			PullUp					TMR0				WDT
MCV18A																												OSC		PORTA, PORTB								TMR0				WDT
MCV28A																												OSC		PORTA, PORTB, PORTC								TMR0				WDT
MEC1501H_B0_SZ																																					SYSTICK					
MEC1501H_B0_TF																																					SYSTICK					
MEC1501H_B0_Z2																																					SYSTICK					
MEC1503H_L1_3Y																																					SYSTICK					
MEC1503H_L1_SZ																																					SYSTICK					
MEC1507H_B0_SZ																																					SYSTICK					
MEC1507H_B0_TF																																					SYSTICK					
MEC1515H_D0_NB																																										
MEC1521H_B0_SZ																																					SYSTICK					
MEC1521H_B0_TF																																					SYSTICK					
MEC1521H_B0_Z2																																					SYSTICK					
MEC1523H_L1_3Y																																					SYSTICK					
MEC1523H_L1_SZ																																					SYSTICK					
MEC1527H_B0_SZ																																					SYSTICK					
MEC1721N_B0_LJ																																					SYSTICK					
MEC1721N_B0_SZ																																					SYSTICK					
MEC1723N_B0_LJ																																					SYSTICK					
MEC1723N_B0_SZ																																					SYSTICK					
MEC1723N_F0_SZ																																					SYSTICK					
MEC1723N_P0_XX																																					SYSTICK					
MEC1725N_B0_LJ																																					SYSTICK					
MGC3140								CoreTimer				DMA								INT					IC1, IC2	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD	PPS			RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1			WDT32
PIC10F200																						GPIO						OSC					PullUp					TMR0				WDT
PIC10F202																						GPIO						OSC					PullUp					TMR0				WDT
PIC10F204							COMP1															GPIO						OSC					PullUp					TMR0				WDT
PIC10F206							COMP1															GPIO						OSC					PullUp					TMR0				WDT
PIC10F220		ADC																				GPIO						OSC					PullUp					TMR0				WDT
PIC10F222		ADC																				GPIO						OSC					PullUp					TMR0				WDT
PIC10F320, PIC10LF320		ADC			CLC1					CWG1						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA		PWM1, PWM2	PullUp					TMR0, TMR2				WDT
PIC10F322, PIC10LF322		ADC			CLC1					CWG1						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA		PWM1, PWM2	PullUp					TMR0, TMR2				WDT
PIC12C508																						GPIO						OSC					PullUp					TMR0				WDT
PIC12C508A																						GPIO						OSC					PullUp					TMR0				WDT
PIC12C509																						GPIO						OSC					PullUp					TMR0				WDT
PIC12C509A																						GPIO						OSC					PullUp					TMR0				WDT
PIC12C671		ADC																		INT, IOC		GPIO						OSC					PullUp					TMR0				WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC12C672		ADC																		INT, IOC		GPIO						OSC					PullUp					TMR0				WDT
PIC12CE518																						GPIO						OSC					PullUp					TMR0				WDT
PIC12CE519																						GPIO						OSC					PullUp					TMR0				WDT
PIC12CE673		ADC																		INT, IOC		GPIO						OSC					PullUp					TMR0				WDT
PIC12CE674		ADC																		INT, IOC		GPIO						OSC					PullUp					TMR0				WDT
PIC12CR509A																						GPIO						OSC					PullUp					TMR0				WDT
PIC12F1501, PIC12LF1501		ADC			CLC1, CLC2		COMP1			CWG1						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA	PPS	PWM1, PWM2,	PullUp					TMR0, TMR1,				WDT
PIC12F1571, PIC12LF1571		ADC					COMP1			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA	PPS	PWM1, PWM2,	PullUp					TMR0, TMR1,				WDT
PIC12F1572, PIC12LF1572		ADC					COMP1			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA	PPS	PWM1, PWM2,	PullUp					TMR0, TMR1,	UART1			WDT
PIC12F1612, PIC12LF1612		ADC		CCP1, CCP2			COMP1			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA	PPS		PullUp			SMT1, SMT2		TMR0, TMR1,				WDT
PIC12F1822, PIC12LF1822		ADC		CCP1			COMP1						DSM			EEFlash				INT, IOC	FVR							OSC		PORTA	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC12F1840, PIC12LF1840		ADC		CCP1			COMP1						DSM			EEFlash				INT, IOC	FVR							OSC		PORTA	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC12F508																						GPIO						OSC					PullUp					TMR0				WDT
PIC12F509																						GPIO						OSC					PullUp					TMR0				WDT
PIC12F510		ADC					COMP1															GPIO						OSC					PullUp					TMR0				WDT
PIC12F519																EEFlash						GPIO						OSC					PullUp					TMR0				WDT
PIC12F529T39A																EEFlash												OSC		PORTB			PullUp					TMR0				WDT
PIC12F529T48A																EEFlash												OSC		PORTB			PullUp					TMR0				WDT
PIC12F609, PIC12HV609							COMP1, CVREF													INT, IOC	FVR	GPIO						OSC					PullUp					TMR0, TMR1				WDT
PIC12F615, PIC12HV615		ADC		CCP1			COMP1, CVREF													INT, IOC	FVR	GPIO						OSC			PPS		PullUp					TMR0, TMR1,				WDT
PIC12F617		ADC		CCP1			COMP1, CVREF									EEFlash				INT, IOC	FVR	GPIO						OSC			PPS		PullUp					TMR0, TMR1, TMR2				WDT
PIC12F629							COMP1, CVREF									EEFlash				INT, IOC	FVR	GPIO						OSC					PullUp					TMR0, TMR1				WDT
PIC12F635							COMP1, CVREF									EEFlash				INT, IOC	FVR	GPIO						OSC					PullUp					TMR0, TMR1				WDT
PIC12F675		ADC					COMP1, CVREF									EEFlash				INT, IOC	FVR	GPIO						OSC					PullUp					TMR0, TMR1				WDT
PIC12F683		ADC		CCP1			COMP1, CVREF									EEFlash				INT, IOC	FVR	GPIO						OSC					PullUp					TMR0, TMR1, TMR2				WDT
PIC12F752, PIC12HV752		ADC		CCP1		COG1	COMP1, COMP2									EEFlash				INT, IOC	FVR		HLT1					OSC		PORTA	PPS		PullUp					TMR0, TMR1,				WDT
PIC16C432							COMP1, COMP2, CVREF													INT, IOC	FVR							OSC		PORTA, PORTB			PullUp					TMR0				WDT
PIC16C433		ADC																		INT, IOC		GPIO						OSC					PullUp					TMR0				WDT
PIC16C505																												OSC		PORTB, PORTC			PullUp					TMR0				WDT
PIC16C54																												OSC		PORTA, PORTB								TMR0				WDT
PIC16C54C																												OSC		PORTA, PORTB								TMR0				WDT
PIC16C55																												OSC		PORTA, PORTB, PORTC								TMR0				WDT
PIC16C554																				INT, IOC								OSC		PORTA, PORTB			PullUp					TMR0				WDT
PIC16C557																				INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0				WDT
PIC16C558																				INT, IOC								OSC		PORTA, PORTB			PullUp					TMR0				WDT
PIC16C55A																												OSC		PORTA, PORTB, PORTC								TMR0				WDT
PIC16C56																												OSC		PORTA, PORTB								TMR0				WDT
PIC16C56A																												OSC		PORTA, PORTB								TMR0				WDT
PIC16C57																												OSC		PORTA, PORTB, PORTC								TMR0				WDT
PIC16C57C																												OSC		PORTA, PORTB, PORTC								TMR0				WDT
PIC16C58A																												OSC		PORTA, PORTB								TMR0				WDT
PIC16C58B																												OSC		PORTA, PORTB								TMR0				WDT
PIC16C620							COMP1, COMP2, CVREF													INT, IOC	FVR							OSC		PORTA, PORTB			PullUp					TMR0				WDT
PIC16C620A							COMP1, COMP2, CVREF													INT, IOC	FVR							OSC		PORTA, PORTB			PullUp					TMR0				WDT
PIC16C621							COMP1, COMP2, CVREF													INT, IOC	FVR							OSC		PORTA, PORTB			PullUp					TMR0				WDT
PIC16C621A							COMP1, COMP2, CVREF													INT, IOC	FVR							OSC		PORTA, PORTB			PullUp					TMR0				WDT
PIC16C622							COMP1, COMP2, CVREF													INT, IOC	FVR							OSC		PORTA, PORTB			PullUp					TMR0				WDT
PIC16C622A							COMP1, COMP2, CVREF													INT, IOC	FVR							OSC		PORTA, PORTB			PullUp					TMR0				WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC16C62A				CCP1																INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C62B				CCP1																INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C63				CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C63A				CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C642							COMP1, COMP2, CVREF													INT, IOC	FVR							OSC		PORTA, PORTB, PORTC			PullUp					TMR0				WDT
PIC16C64A				CCP1																INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C65A				CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C65B				CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C66				CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C662							COMP1, COMP2, CVREF													INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp					TMR0				WDT
PIC16C67				CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C71		ADC																		INT, IOC								OSC		PORTA, PORTB			PullUp					TMR0				WDT
PIC16C710		ADC																		INT, IOC								OSC		PORTA, PORTB			PullUp					TMR0				WDT
PIC16C711		ADC																		INT, IOC								OSC		PORTA, PORTB			PullUp					TMR0				WDT
PIC16C712		ADC		CCP1																INT, IOC								OSC		PORTA, PORTB, PORTP			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C715		ADC																		INT, IOC								OSC		PORTA, PORTB			PullUp					TMR0				WDT
PIC16C716		ADC		CCP1																INT, IOC								OSC		PORTA, PORTB, PORTP			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C717		ADC		CCP1												EEFlash				INT, IOC								OSC		PORTA, PORTB			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C72		ADC		CCP1																INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C72A		ADC		CCP1																INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C73A		ADC		CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C73B		ADC		CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C745		ADC		CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C74A		ADC		CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C74B		ADC		CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C76		ADC		CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C765		ADC		CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C77		ADC		CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C770		ADC		CCP1												EEFlash				INT, IOC								OSC		PORTA, PORTB			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C771		ADC		CCP1												EEFlash				INT, IOC								OSC		PORTA, PORTB			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C773		ADC		CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C774		ADC		CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C781		ADC					COMP1, COMP2									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB			PullUp					TMR0, TMR1				WDT
PIC16C782		ADC					COMP1, COMP2									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB			PullUp					TMR0, TMR1				WDT
PIC16C923				CCP1																INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp					TMR0, TMR1, TMR2				WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC16C924		ADC		CCP1																INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C925		ADC		CCP1												EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp					TMR0, TMR1, TMR2				WDT
PIC16C926		ADC		CCP1												EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp					TMR0, TMR1, TMR2				WDT
PIC16CE623							COMP1, COMP2, CVREF													INT, IOC	FVR							OSC		PORTA, PORTB			PullUp					TMR0				WDT
PIC16CE624							COMP1, COMP2, CVREF													INT, IOC	FVR							OSC		PORTA, PORTB			PullUp					TMR0				WDT
PIC16CE625							COMP1, COMP2, CVREF													INT, IOC	FVR							OSC		PORTA, PORTB			PullUp					TMR0				WDT
PIC16CR54																												OSC		PORTA, PORTB								TMR0				WDT
PIC16CR54A																												OSC		PORTA, PORTB								TMR0				WDT
PIC16CR54C																												OSC		PORTA, PORTB								TMR0				WDT
PIC16CR56A																												OSC		PORTA, PORTB								TMR0				WDT
PIC16CR57C																												OSC		PORTA, PORTB, PORTC								TMR0				WDT
PIC16CR58B																												OSC		PORTA, PORTB								TMR0				WDT
PIC16CR62				CCP1																INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1, TMR2				WDT
PIC16CR620A							COMP1, COMP2, CVREF													INT, IOC	FVR							OSC		PORTA, PORTB			PullUp					TMR0				WDT
PIC16CR63				CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1, TMR2				WDT
PIC16CR64				CCP1																INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp					TMR0, TMR1, TMR2				WDT
PIC16CR65				CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp					TMR0, TMR1, TMR2				WDT
PIC16CR72		ADC		CCP1																INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1, TMR2				WDT
PIC16CR73		ADC		CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1, TMR2				WDT
PIC16CR74		ADC		CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp					TMR0, TMR1, TMR2				WDT
PIC16CR76		ADC		CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1, TMR2				WDT
PIC16CR77		ADC		CCP1, CCP2																INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp					TMR0, TMR1, TMR2				WDT
PIC16CR83																EEFlash				INT, IOC								OSC		PORTA, PORTB			PullUp					TMR0				WDT
PIC16CR84																EEFlash				INT, IOC								OSC		PORTA, PORTB			PullUp					TMR0				WDT
PIC16CR926		ADC		CCP1												EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp					TMR0, TMR1, TMR2				WDT
PIC16F1454, PIC16LF1454																EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC	PPS	PWM1, PWM2	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1455, PIC16LF1455		ADC					COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC	PPS	PWM1, PWM2	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1459, PIC16LF1459		ADC					COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC	PPS	PWM1, PWM2	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1503, PIC16LF1503		ADC			CLC1, CLC2		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTC	PPS	PWM1, PWM2,	PullUp					TMR0, TMR1,				WDT
PIC16F1507, PIC16LF1507		ADC			CLC1, CLC2					CWG1						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC	PPS	PWM1, PWM2,	PullUp					TMR0, TMR1,				WDT
PIC16F1508, PIC16LF1508		ADC			CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC	PPS	PWM1, PWM2,	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1509, PIC16LF1509		ADC			CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC	PPS	PWM1, PWM2,	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1512, PIC16LF1512		ADC		CCP1, CCP2												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1513, PIC16LF1513		ADC		CCP1, CCP2												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1516, PIC16LF1516		ADC		CCP1, CCP2												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1517, PIC16LF1517		ADC		CCP1, CCP2												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1518, PIC16LF1518		ADC		CCP1, CCP2												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1519, PIC16LF1519		ADC		CCP1, CCP2												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F15225				CCP1, CCP2												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC	PPS, PPSLock	PWM3, PWM4	PullUp					TMR0, TMR1, TMR2				
PIC16F15245				CCP1, CCP2												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC	PPS, PPSLock	PWM3, PWM4	PullUp					TMR0, TMR1, TMR2				

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC16F1526, PIC16LF1526		ADC		CCP1, CCP10, CCP2, CCP3,												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,				WDT
PIC16F1527, PIC16LF1527		ADC		CCP1, CCP10, CCP2, CCP3,												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,				WDT
PIC16F15313, PIC16LF15313		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1			CWG1						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA	PPS, PPSLock	PWM3, PWM4,	PullUp					TMR0, TMR1,				WDT
PIC16F15323, PIC16LF15323		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTC	PPS, PPSLock	PWM3, PWM4,	PullUp					TMR0, TMR1,				WDT
PIC16F15324, PIC16LF15324		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTC	PPS, PPSLock	PWM3, PWM4,	PullUp					TMR0, TMR1,				WDT
PIC16F15325, PIC16LF15325		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTC	PPS, PPSLock	PWM3, PWM4,	PullUp					TMR0, TMR1,				WDT
PIC16F15344, PIC16LF15344		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC	PPS, PPSLock	PWM3, PWM4,	PullUp					TMR0, TMR1,				WDT
PIC16F15345, PIC16LF15345		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC	PPS, PPSLock	PWM3, PWM4,	PullUp					TMR0, TMR1,				WDT
PIC16F15354, PIC16LF15354		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC, PORTE	PPS, PPSLock	PWM3, PWM4,	PullUp					TMR0, TMR1,				WDT
PIC16F15355, PIC16LF15355		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC, PORTE	PPS, PPSLock	PWM3, PWM4,	PullUp					TMR0, TMR1,				WDT
PIC16F15356, PIC16LF15356		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC, PORTE	PPS, PPSLock	PWM3, PWM4,	PullUp					TMR0, TMR1,				WDT
PIC16F15375, PIC16LF15375		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC, PORTD,	PPS, PPSLock	PWM3, PWM4,	PullUp					TMR0, TMR1,				WDT
PIC16F15376, PIC16LF15376		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC, PORTD,	PPS, PPSLock	PWM3, PWM4,	PullUp					TMR0, TMR1,				WDT
PIC16F15385, PIC16LF15385		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC, PORTD,	PPS, PPSLock	PWM3, PWM4,	PullUp					TMR0, TMR1,				WDT
PIC16F15386, PIC16LF15386		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC, PORTD,	PPS, PPSLock	PWM3, PWM4,	PullUp					TMR0, TMR1,				WDT
PIC16F1574, PIC16LF1574		ADC					COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC	PPS, PPSLock	PWM1, PWM2,	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1575, PIC16LF1575		ADC					COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC	PPS, PPSLock	PWM1, PWM2,	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1578, PIC16LF1578		ADC					COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC	PPS, PPSLock	PWM1, PWM2,	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1579, PIC16LF1579		ADC					COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC	PPS, PPSLock	PWM1, PWM2,	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1613, PIC16LF1613		ADC		CCP1, CCP2			COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC	PPS		PullUp			SMT1, SMT2		TMR0, TMR1,				WDT
PIC16F1614, PIC16LF1614		ADC		CCP1, CCP2	CLC1, CLC2		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC	PPS, PPSLock	PWM3, PWM4	PullUp			SMT1, SMT2		TMR0, TMR1,	UART1			WDT
PIC16F1615, PIC16LF1615		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC	PPS, PPSLock	PWM3, PWM4	PullUp			SMT1, SMT2		TMR0, TMR1,	UART1			WDT
PIC16F1618, PIC16LF1618		ADC		CCP1, CCP2	CLC1, CLC2		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC	PPS, PPSLock	PWM3, PWM4	PullUp			SMT1, SMT2		TMR0, TMR1,	UART1			WDT
PIC16F1619, PIC16LF1619		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC	PPS, PPSLock	PWM3, PWM4	PullUp			SMT1, SMT2		TMR0, TMR1,	UART1			WDT
PIC16F1703, PIC16LF1703		ADC		CCP1, CCP2												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC	PPS, PPSLock		PullUp					TMR0, TMR1,				WDT
PIC16F1704, PIC16LF1704		ADC		CCP1, CCP2	CLC1, CLC2,	COG1	COMP1, COMP2									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC	PPS, PPSLock	PWM3, PWM4	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1705, PIC16LF1705		ADC		CCP1, CCP2	CLC1, CLC2,	COG1	COMP1, COMP2									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC	PPS, PPSLock	PWM3, PWM4	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1707, PIC16LF1707		ADC		CCP1, CCP2												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC	PPS, PPSLock		PullUp					TMR0, TMR1,				WDT
PIC16F1708, PIC16LF1708		ADC		CCP1, CCP2	CLC1, CLC2,	COG1	COMP1, COMP2									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC	PPS, PPSLock	PWM3, PWM4	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1709, PIC16LF1709		ADC		CCP1, CCP2	CLC1, CLC2,	COG1	COMP1, COMP2									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC	PPS, PPSLock	PWM3, PWM4	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1713, PIC16LF1713		ADC		CCP1, CCP2	CLC1, CLC2,	COG1	COMP1, COMP2									EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC, PORTE	PPS, PPSLock	PWM3, PWM4	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1716, PIC16LF1716		ADC		CCP1, CCP2	CLC1, CLC2,	COG1	COMP1, COMP2									EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC, PORTE	PPS, PPSLock	PWM3, PWM4	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1717, PIC16LF1717		ADC		CCP1, CCP2	CLC1, CLC2,	COG1	COMP1, COMP2									EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC, PORTD,	PPS, PPSLock	PWM3, PWM4	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1718, PIC16LF1718		ADC		CCP1, CCP2	CLC1, CLC2,	COG1	COMP1, COMP2									EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC, PORTE	PPS, PPSLock	PWM3, PWM4	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1719, PIC16LF1719		ADC		CCP1, CCP2	CLC1, CLC2,	COG1	COMP1, COMP2									EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC, PORTD,	PPS, PPSLock	PWM3, PWM4	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1764, PIC16LF1764		ADC		CCP1	CLC1, CLC2,	COG1	COMP1, COMP2									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC	PPS, PPSLock	PWM3, PWM5	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1765, PIC16LF1765		ADC		CCP1	CLC1, CLC2,	COG1	COMP1, COMP2									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC	PPS, PPSLock	PWM3, PWM5	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1768, PIC16LF1768		ADC		CCP1, CCP2	CLC1, CLC2,	COG1, COG2	COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC	PPS, PPSLock	PWM3, PWM4,	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1769, PIC16LF1769		ADC		CCP1, CCP2	CLC1, CLC2,	COG1, COG2	COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC	PPS, PPSLock	PWM3, PWM4,	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1773, PIC16LF1773		ADC		CCP1, CCP2, CCP7	CLC1, CLC2,	COG1, COG2,	COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS, PPSLock	PWM11, PWM3,	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1776, PIC16LF1776		ADC		CCP1, CCP2, CCP7	CLC1, CLC2,	COG1, COG2,	COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS, PPSLock	PWM11, PWM3,	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1777, PIC16LF1777		ADC		CCP1, CCP2, CCP7, CCP8	CLC1, CLC2,	COG1, COG2,	COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS, PPSLock	PWM11, PWM12,	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1778, PIC16LF1778		ADC		CCP1, CCP2, CCP7	CLC1, CLC2,	COG1, COG2,	COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS, PPSLock	PWM11, PWM3,	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1779, PIC16LF1779		ADC		CCP1, CCP2, CCP7, CCP8	CLC1, CLC2,	COG1, COG2,	COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS, PPSLock	PWM10, PWM11,	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1782, PIC16LF1782		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1783, PIC16LF1783		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1784, PIC16LF1784		ADC		CCP1, CCP2, CCP3			COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1786, PIC16LF1786		ADC		CCP1, CCP2, CCP3			COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1787, PIC16LF1787		ADC		CCP1, CCP2, CCP3			COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1788, PIC16LF1788		ADC		CCP1, CCP2, CCP3			COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1789, PIC16LF1789		ADC		CCP1, CCP2, CCP3			COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1823, PIC16LF1823		ADC		CCP1			COMP1, COMP2						DSM			EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC	PPS		PullUp					TMR0, TMR1,	UART1			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC16F1824, PIC16LF1824		ADC		CCP1, CCP2, CCP3, CCP4			COMP1, COMP2						DSM			EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1825, PIC16LF1825		ADC		CCP1, CCP2, CCP3, CCP4			COMP1, COMP2						DSM			EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1826, PIC16LF1826		ADC		CCP1			COMP1, COMP2						DSM			EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1827, PIC16LF1827		ADC		CCP1, CCP2, CCP3, CCP4			COMP1, COMP2						DSM			EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1828, PIC16LF1828		ADC		CCP1, CCP2, CCP3, CCP4			COMP1, COMP2						DSM			EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1829, PIC16LF1829		ADC		CCP1, CCP2, CCP3, CCP4			COMP1, COMP2						DSM			EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1829UN		ADC		CCP1, CCP2, CCP3, CCP4			COMP1, COMP2						DSM			EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1, TMR2, TMR4, TMR6	UART1			WDT
PIC16F18313, PIC16LF18313		ADC		CCP1, CCP2	CLC1, CLC2		COMP1			CWG1			DSM			EEFlash				INT, IOC	FVR							NCO, OSC		PORTA	PPS, PPSLock	PWM5, PWM6	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F18323, PIC16LF18323		ADC		CCP1, CCP2	CLC1, CLC2		COMP1, COMP2			CWG1			DSM			EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTC	PPS, PPSLock	PWM5, PWM6	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F18324, PIC16LF18324		ADC		CCP1, CCP2, CCP3, CCP4	CLC1, CLC2,		COMP1, COMP2			CWG1, CWG2			DSM			EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTC	PPS, PPSLock	PWM5, PWM6	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F18325, PIC16LF18325		ADC		CCP1, CCP2, CCP3, CCP4	CLC1, CLC2,		COMP1, COMP2			CWG1, CWG2			DSM			EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTC	PPS, PPSLock	PWM5, PWM6	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F18326, PIC16LF18326		ADC		CCP1, CCP2, CCP3, CCP4	CLC1, CLC2,		COMP1, COMP2			CWG1, CWG2			DSM			EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTC	PPS, PPSLock	PWM5, PWM6	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F18344, PIC16LF18344		ADC		CCP1, CCP2, CCP3, CCP4	CLC1, CLC2,		COMP1, COMP2			CWG1, CWG2			DSM			EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC	PPS, PPSLock	PWM5, PWM6	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F18345, PIC16LF18345		ADC		CCP1, CCP2, CCP3, CCP4	CLC1, CLC2,		COMP1, COMP2			CWG1, CWG2			DSM			EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC	PPS, PPSLock	PWM5, PWM6	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F18346, PIC16LF18346		ADC		CCP1, CCP2, CCP3, CCP4	CLC1, CLC2,		COMP1, COMP2			CWG1, CWG2			DSM			EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC	PPS, PPSLock	PWM5, PWM6	PullUp					TMR0, TMR1,	UART1			WDT
PIC16F18424, PIC16LF18424		ADC		CCP1, CCP2, CCP3, CCP4	CLC1, CLC2,		COMP1, COMP2			CWG1, CWG2						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTC	PPS, PPSLock	PWM6, PWM7	PullUp			SMT1		TMR0, TMR1,				WDT
PIC16F18425, PIC16LF18425		ADC		CCP1, CCP2, CCP3, CCP4	CLC1, CLC2,		COMP1, COMP2			CWG1, CWG2						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTC	PPS, PPSLock	PWM6, PWM7	PullUp			SMT1		TMR0, TMR1,				WDT
PIC16F18426, PIC16LF18426		ADC		CCP1, CCP2, CCP3, CCP4	CLC1, CLC2,		COMP1, COMP2			CWG1, CWG2						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTC	PPS, PPSLock	PWM6, PWM7	PullUp			SMT1		TMR0, TMR1,				WDT
PIC16F18444, PIC16LF18444		ADC		CCP1, CCP2, CCP3, CCP4	CLC1, CLC2,		COMP1, COMP2			CWG1, CWG2						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC	PPSLock	PWM6, PWM7	PullUp			SMT1		TMR0, TMR1,				WDT
PIC16F18445, PIC16LF18445		ADC		CCP1, CCP2, CCP3, CCP4	CLC1, CLC2,		COMP1, COMP2			CWG1, CWG2						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC	PPSLock	PWM6, PWM7	PullUp			SMT1		TMR0, TMR1,				WDT
PIC16F18446, PIC16LF18446		ADC		CCP1, CCP2, CCP3, CCP4	CLC1, CLC2,		COMP1, COMP2			CWG1, CWG2						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC	PPSLock	PWM6, PWM7	PullUp			SMT1		TMR0, TMR1,				WDT
PIC16F18455, PIC16LF18455		ADC		CCP1, CCP2, CCP3, CCP4,	CLC1, CLC2,		COMP1, COMP2			CWG1, CWG2,						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC, PORTE	PPSLock	PWM6, PWM7	PullUp			SMT1, SMT2		TMR0, TMR1,				WDT
PIC16F18456, PIC16LF18456		ADC		CCP1, CCP2, CCP3, CCP4,	CLC1, CLC2,		COMP1, COMP2			CWG1, CWG2,						EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC, PORTE	PPSLock	PWM6, PWM7	PullUp			SMT1, SMT2		TMR0, TMR1,				WDT
PIC16F1847, PIC16LF1847		ADC		CCP1, CCP2, CCP3, CCP4			COMP1, COMP2						DSM			EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F18854, PIC16LF18854		ADC		CCP1, CCP2, CCP3, CCP4,	CLC1, CLC2,		COMP1, COMP2			CWG1, CWG2,			DSM			EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC, PORTE	PPS, PPSLock	PWM6, PWM7	PullUp			SMT1, SMT2		TMR0, TMR1,	UART1			WDT
PIC16F18855, PIC16LF18855		ADC		CCP1, CCP2, CCP3, CCP4,	CLC1, CLC2,		COMP1, COMP2			CWG1, CWG2,			DSM			EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC, PORTE	PPS, PPSLock	PWM6, PWM7	PullUp			SMT1, SMT2		TMR0, TMR1,	UART1			WDT
PIC16F18856, PIC16LF18856		ADC		CCP1, CCP2, CCP3, CCP4,	CLC1, CLC2,		COMP1, COMP2			CWG1, CWG2,			DSM			EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC, PORTE	PPS, PPSLock	PWM6, PWM7	PullUp			SMT1, SMT2		TMR0, TMR1,	UART1			WDT
PIC16F18857, PIC16LF18857		ADC		CCP1, CCP2, CCP3, CCP4,	CLC1, CLC2,		COMP1, COMP2			CWG1, CWG2,			DSM			EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC, PORTE	PPS, PPSLock	PWM6, PWM7	PullUp			SMT1, SMT2		TMR0, TMR1,	UART1			WDT
PIC16F18875, PIC16LF18875		ADC		CCP1, CCP2, CCP3, CCP4,	CLC1, CLC2,		COMP1, COMP2			CWG1, CWG2,			DSM			EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC, PORTD,	PPS, PPSLock	PWM6, PWM7	PullUp			SMT1, SMT2		TMR0, TMR1,	UART1			WDT
PIC16F18876, PIC16LF18876		ADC		CCP1, CCP2, CCP3, CCP4,	CLC1, CLC2,		COMP1, COMP2			CWG1, CWG2,			DSM			EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC, PORTD,	PPS, PPSLock	PWM6, PWM7	PullUp			SMT1, SMT2		TMR0, TMR1,	UART1			WDT
PIC16F18877, PIC16LF18877		ADC		CCP1, CCP2, CCP3, CCP4,	CLC1, CLC2,		COMP1, COMP2			CWG1, CWG2,			DSM			EEFlash				INT, IOC	FVR							NCO, OSC		PORTA, PORTB, PORTC, PORTD,	PPS, PPSLock	PWM6, PWM7	PullUp			SMT1, SMT2		TMR0, TMR1,	UART1			WDT
PIC16F19155, PIC16LF19155		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS, PPSLock	PWM3, PWM4	PullUp			SMT1		TMR0, TMR1,				WDT
PIC16F19156, PIC16LF19156		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS, PPSLock	PWM3, PWM4	PullUp			SMT1		TMR0, TMR1,				WDT
PIC16F19175, PIC16LF19175		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS, PPSLock	PWM3, PWM4	PullUp			SMT1		TMR0, TMR1,				WDT
PIC16F19176, PIC16LF19176		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS, PPSLock	PWM3, PWM4	PullUp			SMT1		TMR0, TMR1,				WDT
PIC16F19185, PIC16LF19185		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS, PPSLock	PWM3, PWM4	PullUp			SMT1		TMR0, TMR1,				WDT
PIC16F19186, PIC16LF19186		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS, PPSLock	PWM3, PWM4	PullUp			SMT1		TMR0, TMR1,				WDT
PIC16F19195, PIC16LF19195		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS, PPSLock	PWM3, PWM4	PullUp			SMT1		TMR0, TMR1,				WDT
PIC16F19196, PIC16LF19196		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS, PPSLock	PWM3, PWM4	PullUp			SMT1		TMR0, TMR1,				WDT
PIC16F19197, PIC16LF19197		ADC		CCP1, CCP2	CLC1, CLC2,		COMP1, COMP2			CWG1						EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS, PPSLock	PWM3, PWM4	PullUp			SMT1		TMR0, TMR1,				WDT
PIC16F1933, PIC16LF1933		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1934, PIC16LF1934		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1936, PIC16LF1936		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1937, PIC16LF1937		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1938, PIC16LF1938		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1939, PIC16LF1939		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC16F1946, PIC16LF1946		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,				WDT
PIC16F1947, PIC16LF1947		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,				WDT
PIC16F505																												OSC		PORTB, PORTC			PullUp					TMR0				WDT
PIC16F506		ADC					COMP1, COMP2																					OSC		PORTB, PORTC			PullUp					TMR0				WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC16F526		ADC					COMP1, COMP2									EEFlash												OSC		PORTB, PORTC			PullUp					TMR0				WDT
PIC16F527		ADC					COMP1, COMP2									EEFlash				IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0				WDT
PIC16F54																												OSC		PORTA, PORTB								TMR0				WDT
PIC16F57																												OSC		PORTA, PORTB, PORTC								TMR0				WDT
PIC16F570		ADC					COMP1, COMP2									EEFlash				IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0				WDT
PIC16F59																												OSC		PORTA, PORTB, PORTC, PORTD, PORTE								TMR0				WDT
PIC16F610, PIC16HV610							COMP1, COMP2,													INT, IOC	FVR							OSC		PORTA, PORTC			PullUp					TMR0, TMR1				WDT
PIC16F616, PIC16HV616		ADC		CCP1			COMP1, COMP2,													INT, IOC	FVR							OSC		PORTA, PORTC			PullUp					TMR0, TMR1,				WDT
PIC16F627, PIC16LF627				CCP1			COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB			PullUp					TMR0, TMR1,				WDT
PIC16F627A, PIC16LF627A				CCP1			COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB			PullUp					TMR0, TMR1,				WDT
PIC16F628, PIC16LF628				CCP1			COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB			PullUp					TMR0, TMR1,				WDT
PIC16F628A, PIC16LF628A				CCP1			COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB			PullUp					TMR0, TMR1,				WDT
PIC16F630							COMP1, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC			PullUp					TMR0, TMR1				WDT
PIC16F631							COMP1, COMP2, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1				WDT
PIC16F636							COMP1, COMP2, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC			PullUp					TMR0, TMR1				WDT
PIC16F639							COMP1, COMP2, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC			PullUp					TMR0, TMR1				WDT
PIC16F648A, PIC16LF648A				CCP1			COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB			PullUp					TMR0, TMR1,				WDT
PIC16F676		ADC					COMP1, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC			PullUp					TMR0, TMR1				WDT
PIC16F677		ADC					COMP1, COMP2, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1				WDT
PIC16F684		ADC		CCP1			COMP1, COMP2, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC			PullUp					TMR0, TMR1, TMR2				WDT
PIC16F685		ADC		CCP1			COMP1, COMP2, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1, TMR2				WDT
PIC16F687		ADC					COMP1, COMP2, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1	UART1			WDT
PIC16F688		ADC					COMP1, COMP2, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTC			PullUp					TMR0, TMR1	UART1			WDT
PIC16F689		ADC					COMP1, COMP2, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1	UART1			WDT
PIC16F690		ADC		CCP1			COMP1, COMP2, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1, TMR2	UART1			WDT
PIC16F707, PIC16LF707		ADC		CCP1, CCP2												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,				WDT
PIC16F716		ADC		CCP1																INT, IOC								OSC		PORTA, PORTB			PullUp					TMR0, TMR1, TMR2				WDT
PIC16F72		ADC		CCP1												EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1, TMR2				WDT
PIC16F720, PIC16LF720		ADC		CCP1												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1,				WDT
PIC16F721, PIC16LF721		ADC		CCP1												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1,				WDT
PIC16F722, PIC16LF722		ADC		CCP1, CCP2												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,				WDT
PIC16F722A, PIC16LF722A		ADC		CCP1, CCP2												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,				WDT
PIC16F723, PIC16LF723		ADC		CCP1, CCP2												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,				WDT
PIC16F723A, PIC16LF723A		ADC		CCP1, CCP2												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,				WDT
PIC16F724, PIC16LF724		ADC		CCP1, CCP2												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,				WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC16F726, PIC16LF726		ADC		CCP1, CCP2												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,				WDT
PIC16F727, PIC16LF727		ADC		CCP1, CCP2												EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,				WDT
PIC16F73, PIC16LF73		ADC		CCP1, CCP2												EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1,				WDT
PIC16F737		ADC		CCP1, CCP2, CCP3			COMP1, COMP2, CVREF									EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC, PORTE			PullUp					TMR0, TMR1, TMR2				WDT
PIC16F74, PIC16LF74		ADC		CCP1, CCP2												EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD,			PullUp					TMR0, TMR1,				WDT
PIC16F747, PIC16LF747		ADC		CCP1, CCP2, CCP3			COMP1, COMP2,									EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD,			PullUp					TMR0, TMR1,				WDT
PIC16F753, PIC16HV753		ADC		CCP1		COG1	COMP1, COMP2									EEFlash				INT, IOC			HLT1, HLT2					OSC		PORTA, PORTC	PPS		PullUp					TMR0, TMR1,				WDT
PIC16F76, PIC16LF76		ADC		CCP1, CCP2												EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1,				WDT
PIC16F767, PIC16LF767		ADC		CCP1, CCP2, CCP3			COMP1, COMP2,									EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC, PORTE			PullUp					TMR0, TMR1,				WDT
PIC16F77, PIC16LF77		ADC		CCP1, CCP2												EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD,			PullUp					TMR0, TMR1,				WDT
PIC16F777, PIC16LF777		ADC		CCP1, CCP2, CCP3			COMP1, COMP2,									EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD,			PullUp					TMR0, TMR1,				WDT
PIC16F785, PIC16HV785		ADC		CCP1			COMP1, COMP2,									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC		PWM	PullUp					TMR0, TMR1,				WDT
PIC16F818, PIC16LF818		ADC		CCP1												EEFlash				INT, IOC								OSC		PORTA, PORTB			PullUp					TMR0, TMR1,				WDT
PIC16F819, PIC16LF819		ADC		CCP1												EEFlash				INT, IOC								OSC		PORTA, PORTB			PullUp					TMR0, TMR1,				WDT
PIC16F83, PIC16LF83																EEFlash				INT, IOC								OSC		PORTA, PORTB			PullUp					TMR0				WDT
PIC16F84, PIC16LF84																EEFlash				INT, IOC								OSC		PORTA, PORTB			PullUp					TMR0				WDT
PIC16F84A, PIC16LF84A																EEFlash				INT, IOC								OSC		PORTA, PORTB			PullUp					TMR0				WDT
PIC16F87, PIC16LF87				CCP1			COMP1, COMP2,									EEFlash				INT, IOC								OSC		PORTA, PORTB			PullUp					TMR0, TMR1,				WDT
PIC16F870, PIC16LF870		ADC		CCP1												EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1,				WDT
PIC16F871, PIC16LF871		ADC		CCP1												EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD,			PullUp					TMR0, TMR1,				WDT
PIC16F872, PIC16LF872		ADC		CCP1												EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1,				WDT
PIC16F873, PIC16LF873		ADC		CCP1, CCP2												EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1,				WDT
PIC16F873A, PIC16LF873A		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1,				WDT
PIC16F874, PIC16LF874		ADC		CCP1, CCP2												EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD,			PullUp					TMR0, TMR1,				WDT
PIC16F874A, PIC16LF874A		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD,			PullUp					TMR0, TMR1,				WDT
PIC16F876, PIC16LF876		ADC		CCP1, CCP2												EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1,				WDT
PIC16F876A, PIC16LF876A		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1,				WDT
PIC16F877A, PIC16LF877A		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD,			PullUp					TMR0, TMR1,				WDT
PIC16F88, PIC16LF88		ADC		CCP1			COMP1, COMP2,									EEFlash				INT, IOC								OSC		PORTA, PORTB			PullUp					TMR0, TMR1,				WDT
PIC16F882		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE			PullUp					TMR0, TMR1, TMR2	UART1			WDT
PIC16F883		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE			PullUp					TMR0, TMR1, TMR2	UART1			WDT
PIC16F884		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp					TMR0, TMR1, TMR2	UART1			WDT
PIC16F886		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE			PullUp					TMR0, TMR1, TMR2	UART1			WDT
PIC16F887		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp					TMR0, TMR1, TMR2	UART1			WDT
PIC16F913		ADC		CCP1			COMP1, COMP2, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE			PullUp					TMR0, TMR1, TMR2				WDT
PIC16F914		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp					TMR0, TMR1, TMR2				WDT
PIC16F916		ADC		CCP1			COMP1, COMP2, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE			PullUp					TMR0, TMR1, TMR2				WDT
PIC16F917		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp					TMR0, TMR1, TMR2				WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC16F946		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp					TMR0, TMR1, TMR2				WDT
PIC18C242		ADC		CCP1, CCP2																INT0, INT1, INT2, IOC								OSC		PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1			WDT
PIC18C252		ADC		CCP1, CCP2																INT0, INT1, INT2, IOC								OSC		PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1			WDT
PIC18C442		ADC		CCP1, CCP2																INT0, INT1, INT2, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1			WDT
PIC18C452		ADC		CCP1, CCP2																INT0, INT1, INT2, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1			WDT
PIC18C601		ADC		CCP1, CCP2																INT0, INT1, INT2, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp					TMR0, TMR1, TMR2, TMR3	UART1			WDT
PIC18C658		ADC		CCP1, CCP2			COMP1, COMP2													INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp					TMR0, TMR1, TMR2, TMR3	UART1			WDT
PIC18C801		ADC		CCP1, CCP2																INT0, INT1, INT2, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ			PullUp					TMR0, TMR1, TMR2, TMR3	UART1			WDT
PIC18C858		ADC		CCP1, CCP2			COMP1, COMP2													INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK			PullUp					TMR0, TMR1, TMR2, TMR3	UART1			WDT
PIC18F04Q41		ADC		CCP1			COMP1, COMP2			CWG1										INT0, INT1, INT2, IOC	FVR									PORTA, PORTC	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F05Q41		ADC		CCP1			COMP1, COMP2			CWG1										INT0, INT1, INT2, IOC	FVR									PORTA, PORTC	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F06Q40		ADC		CCP1			COMP1, COMP2			CWG1										INT0, INT1, INT2, IOC	FVR									PORTA, PORTC	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F06Q41		ADC		CCP1			COMP1, COMP2			CWG1										INT0, INT1, INT2, IOC	FVR									PORTA, PORTC	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F1220, PIC18LF1220		ADC		CCP1												EEFlash				INT0, INT1,								OSC		PORTA, PORTB			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F1230, PIC18LF1230		ADC					COMP0, COMP1,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB	PPS	PWM	PullUp					TMR0, TMR1	UART1			WDT
PIC18F1320, PIC18LF1320		ADC		CCP1												EEFlash				INT0, INT1,								OSC		PORTA, PORTB			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F1330, PIC18LF1330		ADC					COMP0, COMP1,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB	PPS	PWM	PullUp					TMR0, TMR1	UART1			WDT
PIC18F13K22, PIC18LF13K22		ADC		CCP1			COMP1, COMP2									EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F13K50, PIC18LF13K50		ADC		CCP1			COMP1, COMP2									EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F14K22, PIC18LF14K22		ADC		CCP1			COMP1, COMP2									EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F14K22LIN		ADC		CCP1			COMP1, COMP2									EEFlash				INT0, INT1, INT2, IOC	FVR							OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1, TMR2, TMR3	UART1			WDT
PIC18F14K50, PIC18LF14K50		ADC		CCP1			COMP1, COMP2									EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F14Q41		ADC		CCP1			COMP1, COMP2			CWG1										INT0, INT1, INT2, IOC	FVR									PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F15Q41		ADC		CCP1			COMP1, COMP2			CWG1										INT0, INT1, INT2, IOC	FVR									PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F16Q40		ADC		CCP1			COMP1, COMP2			CWG1										INT0, INT1, INT2, IOC	FVR									PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F16Q41		ADC		CCP1			COMP1, COMP2			CWG1										INT0, INT1, INT2, IOC	FVR									PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F2220, PIC18LF2220		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2221, PIC18LF2221		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2320, PIC18LF2320		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2321,							COMP1,													INT0,										PORTA, PORTB,								TMR0,				

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC18LF2321		ADC		CCP1, CCP2			COMP2,									EEFlash				INT1,								OSC		PORTC, PORTE	PPS		PullUp					TMR1,	UART1			WDT
PIC18F2331, PIC18LF2331		ADC		CCP1, CCP2												EEFlash				INT0, INT1,					IC1, IC2,			OSC		PORTA, PORTB, PORTC, PORTE		PWM	PullUp					TMR0, TMR1,	UART1			WDT
PIC18F23K20		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1			WDT
PIC18F23K22, PIC18LF23K22		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2									EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F2410, PIC18LF2410		ADC		CCP1, CCP2			COMP1, COMP2,													INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F242, PIC18LF242		ADC		CCP1, CCP2												EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2420, PIC18LF2420		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2423, PIC18LF2423		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2431, PIC18LF2431		ADC		CCP1, CCP2												EEFlash				INT0, INT1,					IC1, IC2,			OSC		PORTA, PORTB, PORTC, PORTE		PWM	PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2450, PIC18LF2450		ADC		CCP1												EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2455, PIC18LF2455		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2458, PIC18LF2458		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F248, PIC18LF248		ADC		CCP1												EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2480, PIC18LF2480		ADC		CCP1												EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F24J10, PIC18LF24J10		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F24J11, PIC18LF24J11		ADC		CCP1, CCP2			COMP1, COMP2,				DeepSleep, DSWDT					EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F24J50, PIC18LF24J50		ADC		CCP1, CCP2			COMP1, COMP2,				DeepSleep, DSWDT					EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F24K20		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1			WDT
PIC18F24K22, PIC18LF24K22		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2									EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18LF24K40, PIC18LF24K40		ADC		CCP1, CCP2			COMP1, COMP2			CWG1			DSM			EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS	PWM3, PWM4	PullUp					TMR0, TMR1,	UART1			WDT
PIC18F24K42, PIC18LF24K42		ADC		CCP1, CCP2, CCP3, CCP4			COMP1, COMP2			CWG1, CWG2,						EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS	PWM5, PWM6,	PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F24K50, PIC18LF24K50		ADC		CCP1, CCP2			COMP1, COMP2									EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F24Q10		ADC		CCP1, CCP2			COMP1, COMP2			CWG1			DSM			EEFlash				INT0, INT1, INT2, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS	PWM3, PWM4	PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1			WDT
PIC18F2510, PIC18LF2510		ADC		CCP1, CCP2			COMP1, COMP2,													INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2515, PIC18LF2515		ADC		CCP1, CCP2			COMP1, COMP2,													INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F252, PIC18LF252		ADC		CCP1, CCP2												EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2520, PIC18LF2520		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2523, PIC18LF2523		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2525, PIC18LF2525		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2550, PIC18LF2550		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2553, PIC18LF2553		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F258, PIC18LF258		ADC		CCP1												EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2580, PIC18LF2580		ADC		CCP1												EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2585, PIC18LF2585		ADC		CCP1												EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F25J10, PIC18LF25J10		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F25J11, PIC18LF25J11		ADC		CCP1, CCP2			COMP1, COMP2,				DeepSleep, DSWDT					EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F25J50, PIC18LF25J50		ADC		CCP1, CCP2			COMP1, COMP2,				DeepSleep, DSWDT					EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F25K20		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1			WDT
PIC18F25K22, PIC18LF25K22		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2									EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18LF25K40, PIC18LF25K40		ADC		CCP1, CCP2			COMP1, COMP2			CWG1			DSM			EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS	PWM3, PWM4	PullUp					TMR0, TMR1,	UART1			WDT
PIC18F25K42, PIC18LF25K42		ADC		CCP1, CCP2, CCP3, CCP4			COMP1, COMP2			CWG1, CWG2,						EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS	PWM5, PWM6,	PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F25K50, PIC18LF25K50		ADC		CCP1, CCP2			COMP1, COMP2									EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F25K80, PIC18LF25K80		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F25K83, PIC18LF25K83		ADC		CCP1, CCP2, CCP3, CCP4			COMP1, COMP2			CWG1, CWG2,						EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS	PWM5, PWM6,	PullUp					TMR0, TMR1,	UART1, UART2			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC18F25Q10		ADC		CCP1, CCP2			COMP1, COMP2			CWG1			DSM			EEFlash				INT0, INT1, INT2, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS	PWM3, PWM4	PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1			WDT
PIC18F25Q43		ADC		CCP1, CCP2, CCP3			COMP1, COMP2			CWG1, CWG2, CWG3										INT0, INT1, INT2, IOC	FVR									PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1, UART2			WDT
PIC18F2610, PIC18LF2610		ADC		CCP1, CCP2			COMP1, COMP2,													INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2620, PIC18LF2620		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2680, PIC18LF2680		ADC		CCP1												EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2682, PIC18LF2682		ADC		CCP1												EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F2685, PIC18LF2685		ADC		CCP1												EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F26J11, PIC18LF26J11		ADC		CCP1, CCP2			COMP1, COMP2,				DeepSleep, DSWDT					EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F26J13, PIC18LF26J13		ADC		CCP1, CCP10, CCP2, CCP3,			COMP1, COMP2,				DeepSleep, DSWDT					EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F26J50, PIC18LF26J50		ADC		CCP1, CCP2			COMP1, COMP2,				DeepSleep, DSWDT					EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F26J53, PIC18LF26J53		ADC		CCP1, CCP10, CCP2, CCP3,			COMP1, COMP2,				DeepSleep, DSWDT					EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F26K20		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1			WDT
PIC18F26K22, PIC18LF26K22		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2									EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F26K40, PIC18LF26K40		ADC		CCP1, CCP2			COMP1, COMP2			CWG1			DSM			EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS	PWM3, PWM4	PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F26K42, PIC18LF26K42		ADC		CCP1, CCP2, CCP3, CCP4			COMP1, COMP2			CWG1, CWG2,						EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS	PWM5, PWM6,	PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F26K80, PIC18LF26K80		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F26K83, PIC18LF26K83		ADC		CCP1, CCP2, CCP3, CCP4			COMP1, COMP2			CWG1, CWG2,						EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS	PWM5, PWM6,	PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F26Q10		ADC		CCP1, CCP2			COMP1, COMP2			CWG1			DSM			EEFlash				INT0, INT1, INT2, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS	PWM3, PWM4	PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1, UART2			WDT
PIC18F26Q43		ADC		CCP1, CCP2, CCP3			COMP1, COMP2			CWG1, CWG2, CWG3										INT0, INT1, INT2, IOC	FVR									PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1, UART2			WDT
PIC18F27J13, PIC18LF27J13		ADC		CCP1, CCP10, CCP2, CCP3,			COMP1, COMP2,				DeepSleep, DSWDT					EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F27J53, PIC18LF27J53		ADC		CCP1, CCP10, CCP2, CCP3,			COMP1, COMP2,				DeepSleep, DSWDT					EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F27K40, PIC18LF27K40		ADC		CCP1, CCP2			COMP1, COMP2			CWG1			DSM			EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS	PWM3, PWM4	PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F27K42, PIC18LF27K42		ADC		CCP1, CCP2, CCP3, CCP4			COMP1, COMP2			CWG1, CWG2,						EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS	PWM5, PWM6,	PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F27Q10		ADC		CCP1, CCP2			COMP1, COMP2			CWG1			DSM			EEFlash				INT0, INT1, INT2, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTE	PPS	PWM3, PWM4	PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1, UART2			WDT
PIC18F27Q43		ADC		CCP1, CCP2, CCP3			COMP1, COMP2			CWG1, CWG2, CWG3										INT0, INT1, INT2, IOC	FVR									PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1, UART2			WDT
PIC18F27Q83		ADC		CCP1, CCP2, CCP3			COMP1, COMP2			CWG1, CWG2, CWG3										INT0, INT1, INT2, IOC	FVR									PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1, UART2			WDT
PIC18F27Q84		ADC		CCP1, CCP2, CCP3			COMP1, COMP2			CWG1, CWG2, CWG3										INT0, INT1, INT2, IOC	FVR									PORTA, PORTB, PORTC, PORTE	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1, UART2			WDT
PIC18F4220, PIC18LF4220		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4221, PIC18LF4221		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4320, PIC18LF4320		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4321, PIC18LF4321		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4331,																				INT0,					IC1,					PORTA, PORTB,								TMR0,				

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC18LF4331		ADC		CCP1, CCP2												EEFlash				INT1,					IC2,			OSC		PORTC, PORTD,	PPS	PWM	PullUp					TMR1,	UART1			WDT
PIC18F43K20		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD, PORTE	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1			WDT
PIC18F43K22, PIC18LF43K22		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2									EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F4410, PIC18LF4410		ADC		CCP1, CCP2			COMP1, COMP2,													INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F442, PIC18LF442		ADC		CCP1, CCP2												EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4420, PIC18LF4420		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4423, PIC18LF4423		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4431, PIC18LF4431		ADC		CCP1, CCP2												EEFlash				INT0, INT1,					IC1, IC2,			OSC		PORTA, PORTB, PORTC, PORTD,	PPS	PWM	PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4450, PIC18LF4450		ADC		CCP1												EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4455, PIC18LF4455		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4458, PIC18LF4458		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F448, PIC18LF448		ADC		CCP1, ECCP1			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4480, PIC18LF4480		ADC		CCP1, ECCP1			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F44J10, PIC18LF44J10		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F44J11, PIC18LF44J11		ADC		CCP1, CCP2			COMP1, COMP2,				DeepSleep, DSWDT					EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F44J50, PIC18LF44J50		ADC		CCP1, CCP2			COMP1, COMP2,				DeepSleep, DSWDT					EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F44K20		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD, PORTE	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1			WDT
PIC18F44K22, PIC18LF44K22		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2									EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F4510, PIC18LF4510		ADC		CCP1, CCP2			COMP1, COMP2,													INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4515, PIC18LF4515		ADC		CCP1, CCP2			COMP1, COMP2,													INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F452, PIC18LF452		ADC		CCP1, CCP2												EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4520, PIC18LF4520		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4523, PIC18LF4523		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4525, PIC18LF4525		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4550, PIC18LF4550		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4553, PIC18LF4553		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F458, PIC18LF458		ADC		CCP1, ECCP1			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4580, PIC18LF4580		ADC		CCP1, ECCP1			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4585, PIC18LF4585		ADC		CCP1, ECCP1			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F45J10, PIC18LF45J10		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F45J11, PIC18LF45J11		ADC		CCP1, CCP2			COMP1, COMP2,				DeepSleep, DSWDT					EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F45J50, PIC18LF45J50		ADC		CCP1, CCP2			COMP1, COMP2,				DeepSleep, DSWDT					EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F45K20		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD, PORTE	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1			WDT
PIC18F45K22, PIC18LF45K22		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2									EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F45K40, PIC18LF45K40		ADC		CCP1, CCP2			COMP1, COMP2			CWG1			DSM			EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS	PWM3, PWM4	PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F45K42, PIC18LF45K42		ADC		CCP1, CCP2, CCP3, CCP4			COMP1, COMP2			CWG1, CWG2,						EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS	PWM5, PWM6,	PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F45K50, PIC18LF45K50		ADC		CCP1, CCP2			COMP1, COMP2									EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F45K80, PIC18LF45K80		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F45Q10		ADC		CCP1, CCP2						CWG1			DSM			EEFlash				INT0, INT1, INT2, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD, PORTE	PPS	PWM3, PWM4	PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1, UART2			WDT
PIC18F45Q43		ADC		CCP1, CCP2, CCP3						CWG1, CWG2, CWG3										INT0, INT1, INT2, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD, PORTE	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1, UART2			WDT
PIC18F4610, PIC18LF4610		ADC		CCP1, CCP2			COMP1, COMP2,													INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4620, PIC18LF4620		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4680, PIC18LF4680		ADC		CCP1, ECCP1			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F4682,							COMP1,													INT0,										PORTA, PORTB,								TMR0,				

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC18LF4682		ADC		CCP1, ECCP1			COMP2,									EEFlash				INT1,								OSC		PORTC, PORTD,			PullUp					TMR1,	UART1			WDT
PIC18F4685, PIC18LF4685		ADC		CCP1, ECCP1			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,			PullUp					TMR0, TMR1,	UART1			WDT
PIC18F46J11, PIC18LF46J11		ADC		CCP1, CCP2			COMP1, COMP2,				DeepSleep, DSWDT					EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F46J13, PIC18LF46J13		ADC		CCP1, CCP10, CCP2, CCP3,			COMP1, COMP2,				DeepSleep, DSWDT					EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F46J50, PIC18LF46J50		ADC		CCP1, CCP2			COMP1, COMP2,				DeepSleep, DSWDT					EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F46J53, PIC18LF46J53		ADC		CCP1, CCP10, CCP2, CCP3,			COMP1, COMP2,				DeepSleep, DSWDT					EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F46K20		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD, PORTE	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1			WDT
PIC18F46K22, PIC18LF46K22		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2									EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F46K40, PIC18LF46K40		ADC		CCP1, CCP2			COMP1, COMP2			CWG1			DSM			EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS	PWM3, PWM4	PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F46K42, PIC18LF46K42		ADC		CCP1, CCP2, CCP3, CCP4			COMP1, COMP2			CWG1, CWG2,						EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS	PWM5, PWM6,	PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F46K80, PIC18LF46K80		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F46Q10		ADC		CCP1, CCP2						CWG1			DSM			EEFlash				INT0, INT1, INT2, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD, PORTE	PPS	PWM3, PWM4	PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1, UART2			WDT
PIC18F46Q43		ADC		CCP1, CCP2, CCP3						CWG1, CWG2, CWG3										INT0, INT1, INT2, IOC	FVR									PORTA, PORTB, PORTC, PORTD, PORTE	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1, UART2			WDT
PIC18F47J13, PIC18LF47J13		ADC		CCP1, CCP10, CCP2, CCP3,			COMP1, COMP2,				DeepSleep, DSWDT					EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F47J53, PIC18LF47J53		ADC		CCP1, CCP10, CCP2, CCP3,			COMP1, COMP2,				DeepSleep, DSWDT					EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F47K40, PIC18LF47K40		ADC		CCP1, CCP2			COMP1, COMP2			CWG1			DSM			EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS	PWM3, PWM4	PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F47K42, PIC18LF47K42		ADC		CCP1, CCP2, CCP3, CCP4			COMP1, COMP2			CWG1, CWG2,						EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS	PWM5, PWM6,	PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F47Q10		ADC		CCP1, CCP2						CWG1			DSM			EEFlash				INT0, INT1, INT2, IOC	FVR							OSC		PORTA, PORTB, PORTC, PORTD, PORTE	PPS	PWM3, PWM4	PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1, UART2			WDT
PIC18F47Q43		ADC		CCP1, CCP2, CCP3						CWG1, CWG2, CWG3										INT0, INT1, INT2, IOC	FVR									PORTA, PORTB, PORTC, PORTD, PORTE	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1, UART2			WDT
PIC18F47Q83		ADC		CCP1, CCP2, CCP3			COMP1, COMP2			CWG1, CWG2, CWG3										INT0, INT1, INT2, IOC	FVR									PORTA, PORTB, PORTC, PORTD, PORTE	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1, UART2			WDT
PIC18F47Q84		ADC		CCP1, CCP2, CCP3			COMP1, COMP2			CWG1, CWG2, CWG3										INT0, INT1, INT2, IOC	FVR									PORTA, PORTB, PORTC, PORTD, PORTE	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1, UART2			WDT
PIC18F55K42, PIC18LF55K42		ADC		CCP1, CCP2, CCP3, CCP4			COMP1, COMP2			CWG1, CWG2,						EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS	PWM5, PWM6,	PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F55Q43		ADC		CCP1, CCP2, CCP3			COMP1, COMP2			CWG1, CWG2, CWG3										INT0, INT1, INT2, IOC	FVR									PORTA, PORTB, PORTC, PORTD, PORTE, PORTF	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1, UART2			WDT
PIC18F56K42, PIC18LF56K42		ADC		CCP1, CCP2, CCP3, CCP4			COMP1, COMP2			CWG1, CWG2,						EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS	PWM5, PWM6,	PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F56Q43		ADC		CCP1, CCP2, CCP3			COMP1, COMP2			CWG1, CWG2, CWG3										INT0, INT1, INT2, IOC	FVR									PORTA, PORTB, PORTC, PORTD, PORTE, PORTF	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1, UART2			WDT
PIC18F57K42, PIC18LF57K42		ADC		CCP1, CCP2, CCP3, CCP4			COMP1, COMP2			CWG1, CWG2,						EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS	PWM5, PWM6,	PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F57Q43		ADC		CCP1, CCP2, CCP3			COMP1, COMP2			CWG1, CWG2, CWG3										INT0, INT1, INT2, IOC	FVR									PORTA, PORTB, PORTC, PORTD, PORTE, PORTF	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1, UART2			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC18F57Q83		ADC		CCP1, CCP2, CCP3			COMP1, COMP2			CWG1, CWG2, CWG3										INT0, INT1, INT2, IOC	FVR									PORTA, PORTB, PORTC, PORTD, PORTE, PORTF	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1, UART2			WDT
PIC18F57Q84		ADC		CCP1, CCP2, CCP3			COMP1, COMP2			CWG1, CWG2, CWG3										INT0, INT1, INT2, IOC	FVR									PORTA, PORTB, PORTC, PORTD, PORTE, PORTF	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6	UART1, UART2			WDT
PIC18F6310, PIC18LF6310		ADC		CCP1, CCP2, CCP3			COMP1, COMP2,													INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F6390, PIC18LF6390		ADC		CCP1, CCP2			COMP1, COMP2,													INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F6393, PIC18LF6393		ADC		CCP1, CCP2			COMP1, COMP2,													INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F63J11		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT
PIC18F63J90		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT
PIC18F6410, PIC18LF6410		ADC		CCP1, CCP2, CCP3			COMP1, COMP2,													INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F6490, PIC18LF6490		ADC		CCP1, CCP2			COMP1, COMP2,													INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F6493, PIC18LF6493		ADC		CCP1, CCP2			COMP1, COMP2,													INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F64J11		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT
PIC18F64J90		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT
PIC18F6520, PIC18LF6520		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F6525, PIC18LF6525		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F6527, PIC18LF6527		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F6585, PIC18LF6585		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F65J10		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F65J11		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT
PIC18F65J15		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F65J50		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F65J90		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT
PIC18F65J94				CCP1, CCP10, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8, CCP9			COMP1, COMP2, COMP3, CVREF				DeepSleep, DSWDT		DSM			EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTVP	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR8	UART1, UART2			WDT
PIC18F65K22		ADC		CCP1, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8			COMP1, COMP2, COMP3, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR8	UART1, UART2			WDT
PIC18F65K40, PIC18LF65K40		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,			CWG1			DSM			EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS	PWM6, PWM7	PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F65K80, PIC18LF65K80		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,						DSM			EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F65K90		ADC		CCP1, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8			COMP1, COMP2, COMP3, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR8	UART1, UART2			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC18F6620, PIC18LF6620		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F6621, PIC18LF6621		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F6622, PIC18LF6622		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F6627, PIC18LF6627		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F6628, PIC18LF6628		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F6680, PIC18LF6680		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F66J10		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F66J11		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F66J15		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F66J16		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F66J50		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F66J55		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F66J60		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1			WDT
PIC18F66J65		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1			WDT
PIC18F66J90		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT
PIC18F66J93		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT
PIC18F66J94				CCP1, CCP10, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8, CCP9			COMP1, COMP2, COMP3, CVREF				DeepSleep, DSWDT		DSM			EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTVP	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR8	UART1, UART2			WDT
PIC18F66J99				CCP1, CCP10, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8, CCP9			COMP1, COMP2, COMP3, CVREF				DeepSleep, DSWDT		DSM			EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTVP	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR8	UART1, UART2			WDT
PIC18F66K22		ADC		CCP1, CCP10, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8, CCP9			COMP1, COMP2, COMP3, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR10, TMR12, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8	UART1, UART2			WDT
PIC18F66K40, PIC18LF66K40		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,			CWG1			DSM			EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS	PWM6, PWM7	PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F66K80, PIC18LF66K80		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,						DSM			EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F66K90		ADC		CCP1, CCP10, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8, CCP9			COMP1, COMP2, COMP3, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR10, TMR12, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8	UART1, UART2			WDT
PIC18F6720, PIC18LF6720		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F6722,				CCP1, CCP2,			COMP1,													INT0,										PORTA, PORTB,								TMR0,	UART1,			

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC18LF6722		ADC		CCP3, CCP4,			COMP2,									EEFlash				INT1,								OSC		PORTC, PORTD,	PPS		PullUp					TMR1,	UART2			WDT
PIC18F6723, PIC18LF6723		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F67J10		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F67J11		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F67J50		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F67J60		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1			WDT
PIC18F67J90		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT
PIC18F67J93		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT
PIC18F67J94				CCP1, CCP10, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8, CCP9			COMP1, COMP2, COMP3, CVREF				DeepSleep, DSWDT		DSM			EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTVP	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR8	UART1, UART2			WDT
PIC18F67K22		ADC		CCP1, CCP10, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8, CCP9			COMP1, COMP2, COMP3, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR10, TMR12, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8	UART1, UART2			WDT
PIC18F67K40, PIC18LF67K40		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,			CWG1			DSM			EEFlash				INT0, INT1,	FVR							OSC		PORTA, PORTB, PORTC, PORTD,	PPS	PWM6, PWM7	PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F67K90		ADC		CCP1, CCP10, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8, CCP9			COMP1, COMP2, COMP3, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR10, TMR12, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8	UART1, UART2			WDT
PIC18F8310, PIC18LF8310		ADC		CCP1, CCP2, CCP3			COMP1, COMP2,													INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F8390, PIC18LF8390		ADC		CCP1, CCP2			COMP1, COMP2,													INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F8393, PIC18LF8393		ADC		CCP1, CCP2			COMP1, COMP2,													INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F83J11		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT
PIC18F83J90		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT
PIC18F8410, PIC18LF8410		ADC		CCP1, CCP2, CCP3			COMP1, COMP2,													INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F8490, PIC18LF8490		ADC		CCP1, CCP2			COMP1, COMP2,													INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F8493, PIC18LF8493		ADC		CCP1, CCP2			COMP1, COMP2,													INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F84J11		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT
PIC18F84J90		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT
PIC18F8520, PIC18LF8520		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F8525, PIC18LF8525		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F8527, PIC18LF8527		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F8585, PIC18LF8585		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC18F85J10		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F85J11		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT
PIC18F85J15		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F85J50		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F85J90		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT
PIC18F85J94				CCP1, CCP10, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8, CCP9			COMP1, COMP2, COMP3, CVREF				DeepSleep, DSWDT		DSM			EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTVP	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR8	UART1, UART2			WDT
PIC18F85K22		ADC		CCP1, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8			COMP1, COMP2, COMP3, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR8	UART1, UART2			WDT
PIC18F85K90		ADC		CCP1, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8			COMP1, COMP2, COMP3, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR8	UART1, UART2			WDT
PIC18F8620, PIC18LF8620		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F8621, PIC18LF8621		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F8622, PIC18LF8622		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F8627, PIC18LF8627		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F8628, PIC18LF8628		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F8680, PIC18LF8680		ADC		CCP1, CCP2			COMP1, COMP2,									EEFlash				INT0, INT1,								OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1			WDT
PIC18F86J10		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F86J11		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F86J15		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F86J16		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F86J50		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F86J55		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F86J60		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F86J65		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F86J72		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC18F86J90		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT
PIC18F86J93		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT
PIC18F86J94				CCP1, CCP10, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8, CCP9			COMP1, COMP2, COMP3, CVREF				DeepSleep, DSWDT		DSM			EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTVP	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR8	UART1, UART2			WDT
PIC18F86J99				CCP1, CCP10, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8, CCP9			COMP1, COMP2, COMP3, CVREF				DeepSleep, DSWDT		DSM			EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTVP	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR8	UART1, UART2			WDT
PIC18F86K22		ADC		CCP1, CCP10, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8, CCP9			COMP1, COMP2, COMP3, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR10, TMR12, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8	UART1, UART2			WDT
PIC18F86K90		ADC		CCP1, CCP10, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8, CCP9			COMP1, COMP2, COMP3, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR10, TMR12, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8	UART1, UART2			WDT
PIC18F8720, PIC18LF8720		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F8722, PIC18LF8722		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F8723, PIC18LF8723		ADC		CCP1, CCP2, CCP3, CCP4,			COMP1, COMP2,									EEFlash				INT0, INT1,							OSC		PORTA, PORTB, PORTC, PORTD,	PPS		PullUp					TMR0, TMR1,	UART1, UART2			WDT
PIC18F87J10		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F87J11		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F87J50		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F87J60		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F87J72		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT
PIC18F87J90		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT
PIC18F87J93		ADC		CCP1, CCP2			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3	UART1, UART2			WDT
PIC18F87J94				CCP1, CCP10, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8, CCP9			COMP1, COMP2, COMP3, CVREF				DeepSleep, DSWDT		DSM			EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTVP	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR8	UART1, UART2			WDT
PIC18F87K22		ADC		CCP1, CCP10, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8, CCP9			COMP1, COMP2, COMP3, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR10, TMR12, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8	UART1, UART2			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC18F87K90		ADC		CCP1, CCP10, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8, CCP9			COMP1, COMP2, COMP3, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR10, TMR12, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8	UART1, UART2			WDT
PIC18F95J94				CCP1, CCP10, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8, CCP9			COMP1, COMP2, COMP3, CVREF				DeepSleep, DSWDT		DSM			EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK, PORTL, PORTVP	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR8	UART1, UART2			WDT
PIC18F96J60		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F96J65		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F96J94				CCP1, CCP10, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8, CCP9			COMP1, COMP2, COMP3, CVREF				DeepSleep, DSWDT		DSM			EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK, PORTL, PORTVP	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR8	UART1, UART2			WDT
PIC18F96J99				CCP1, CCP10, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8, CCP9			COMP1, COMP2, COMP3, CVREF				DeepSleep, DSWDT		DSM			EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK, PORTL, PORTVP	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR8	UART1, UART2			WDT
PIC18F97J60		ADC		CCP1, CCP2, CCP3, CCP4, CCP5			COMP1, COMP2, CVREF									EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4	UART1, UART2			WDT
PIC18F97J94				CCP1, CCP10, CCP2, CCP3, CCP4, CCP5, CCP6, CCP7, CCP8, CCP9			COMP1, COMP2, COMP3, CVREF				DeepSleep, DSWDT		DSM			EEFlash				INT0, INT1, INT2, INT3, IOC							OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK, PORTL, PORTVP	PPS		PullUp					TMR0, TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR8	UART1, UART2			WDT
PIC24EP128GP202		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP128GP204		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP128GP206		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP128MC202		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP128MC204		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP128MC206		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP256GP202		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC24EP256GP204		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP256GP206		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP256GU810		ADC1, ADC2					COMP1, COMP2, COMP3		CRC			DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
PIC24EP256GU814		ADC1, ADC2					COMP1, COMP2, COMP3		CRC			DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
PIC24EP256MC202		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP256MC204		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP256MC206		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP32GP202		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP32GP203		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP32GP204		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP32MC202		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP32MC203		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC24EP32MC204		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP512GP202		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP512GP204		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP512GP206		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP512GP806		ADC1, ADC2					COMP1, COMP2, COMP3		CRC			DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
PIC24EP512GU810		ADC1, ADC2					COMP1, COMP2, COMP3		CRC			DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
PIC24EP512GU814		ADC1, ADC2					COMP1, COMP2, COMP3		CRC			DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
PIC24EP512MC202		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP512MC204		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP512MC206		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP64GP202		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC24EP64GP203		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP64GP204		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP64GP206		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP64MC202		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP64MC203		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP64MC204		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24EP64MC206		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24F04KA200		ADC1					COMP1, COMP2													INT, IOC					IC1	OC1		OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3	UART1		VREF	WDT
PIC24F04KA201		ADC1					COMP1, COMP2													INT, IOC					IC1	OC1		OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3	UART1		VREF	WDT
PIC24F04KL100				CCP1/ECCP1, CCP2			COMP1													INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3	UART1		VREF	WDT
PIC24F04KL101				CCP1/ECCP1, CCP2			COMP1													INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3	UART1		VREF	WDT
PIC24F08KA101		ADC1					COMP1, COMP2		CRC											INT, IOC					IC1	OC1		OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2		VREF	WDT
PIC24F08KA102		ADC1					COMP1, COMP2		CRC											INT, IOC					IC1	OC1		OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2		VREF	WDT
PIC24F08KL200		ADC1		CCP1/ECCP1, CCP2			COMP1													INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3	UART1		VREF	WDT
PIC24F08KL201		ADC1		CCP1/ECCP1, CCP2			COMP1													INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3	UART1		VREF	WDT
PIC24F08KL301				CCP1/ECCP1, CCP2, CCP3			COMP1, COMP2													INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4	UART1, UART2		VREF	WDT
PIC24F08KL302				CCP1/ECCP1, CCP2, CCP3			COMP1, COMP2													INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4	UART1, UART2		VREF	WDT
PIC24F08KL401		ADC1		CCP1/ECCP1, CCP2, CCP3			COMP1, COMP2													INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4	UART1, UART2		VREF	WDT
PIC24F08KL402		ADC1		CCP1/ECCP1, CCP2, CCP3			COMP1, COMP2													INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4	UART1, UART2		VREF	WDT
PIC24F08KM101		ADC1		MCCP1/SCCP1, MCCP2/SCCP2			COMP1													INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1		VREF	WDT
PIC24F08KM102		ADC1		MCCP1/SCCP1, MCCP2/SCCP2			COMP1													INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1		VREF	WDT
PIC24F08KM202		ADC1		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5			COMP1, COMP2, COMP3													INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1, UART2		VREF	WDT
PIC24F08KM204		ADC1		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5			COMP1, COMP2, COMP3													INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1, UART2		VREF	WDT
PIC24F16KA101		ADC1					COMP1, COMP2		CRC											INT, IOC					IC1	OC1		OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC24F16KA102		ADC1					COMP1, COMP2		CRC											INT, IOC					IC1	OC1		OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3,	UART1, UART2		VREF	WDT
PIC24F16KA301		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3	OC1, OC2, OC3		OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24F16KA302		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3	OC1, OC2, OC3		OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24F16KA304		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3	OC1, OC2, OC3		OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24F16KL401		ADC1		CCP1/ECCP1, CCP2, CCP3			COMP1, COMP2													INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4	UART1, UART2		VREF	WDT
PIC24F16KL402		ADC1		CCP1/ECCP1, CCP2, CCP3			COMP1, COMP2													INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4	UART1, UART2		VREF	WDT
PIC24F16KM102		ADC1		MCCP1/SCCP1, MCCP2/SCCP2			COMP1													INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1		VREF	WDT
PIC24F16KM104		ADC1		MCCP1/SCCP1, MCCP2/SCCP2			COMP1													INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1		VREF	WDT
PIC24F16KM202		ADC1		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5			COMP1, COMP2, COMP3													INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1, UART2		VREF	WDT
PIC24F16KM204		ADC1		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5			COMP1, COMP2, COMP3													INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1, UART2		VREF	WDT
PIC24F32KA301		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3	OC1, OC2, OC3		OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24F32KA302		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3	OC1, OC2, OC3		OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24F32KA304		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3	OC1, OC2, OC3		OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ1024GA606		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ1024GA610		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ1024GB606		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ1024GB610		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128DA106		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128DA110		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC24FJ128DA206		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128DA210		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GA006		ADC1					COMP		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ128GA008		ADC1					COMP		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ128GA010		ADC1					COMP		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ128GA106		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GA108		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GA110		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GA202		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT	DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont	DSM							INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GA204		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT	DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont	DSM							INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GA306		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT	DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont	DSM							INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7	OC1, OC2, OC3, OC4, OC5, OC6, OC7		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GA308		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT	DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont	DSM							INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7	OC1, OC2, OC3, OC4, OC5, OC6, OC7		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GA310		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT	DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont	DSM							INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7	OC1, OC2, OC3, OC4, OC5, OC6, OC7		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GA406		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC24FJ128GA410		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GA412		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GA606		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GA610		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GA702		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3	OC1, OC2, OC3		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2		VREF	WDT
PIC24FJ128GA704		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3	OC1, OC2, OC3		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2		VREF	WDT
PIC24FJ128GA705		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3	OC1, OC2, OC3		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2		VREF	WDT
PIC24FJ128GB106		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GB108		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GB110		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GB202		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT	DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont	DSM							INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GB204		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT	DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont	DSM							INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GB206		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GB210		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC24FJ128GB406		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GB410		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GB412		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GB606		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GB610		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GC006							COMP1, COMP2, COMP3		CRC		DSWDT	DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont	DSM							INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GC010							COMP1, COMP2, COMP3		CRC		DSWDT	DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont	DSM							INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GL302		ADC1		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTB, PORTC, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GL303		ADC1		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GL305		ADC1		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GL306		ADC1		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GL405		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GL406		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GL408		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC24FJ128GL410		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GU405		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GU406		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GU408		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ128GU410		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ16GA002		ADC1					COMP		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ16GA004		ADC1					COMP		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ16MC101		ADC1					COMP1, COMP2, COMP3													INT, IOC					IC1, IC2, IC3	OC1, OC2		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3	UART1		VREF	WDT
PIC24FJ16MC102		ADC1					COMP1, COMP2, COMP3													INT, IOC					IC1, IC2, IC3	OC1, OC2		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3	UART1		VREF	WDT
PIC24FJ192GA106		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ192GA108		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ192GA110		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ192GB106		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ192GB108		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC24FJ192GB110		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256DA106		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256DA110		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256DA206		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256DA210		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GA106		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GA108		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GA110		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GA406		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GA410		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GA412		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GA606		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GA610		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC24FJ256GA702		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont									INT, IOC					IC1, IC2, IC3	OC1, OC2, OC3		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2		VREF	WDT
PIC24FJ256GA704		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont									INT, IOC					IC1, IC2, IC3	OC1, OC2, OC3		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2		VREF	WDT
PIC24FJ256GA705		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont									INT, IOC					IC1, IC2, IC3	OC1, OC2, OC3		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2		VREF	WDT
PIC24FJ256GB106		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GB108		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GB110		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GB206		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GB210		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GB406		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5,									INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GB410		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont									INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GB412		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont									INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GB606		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont									INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GB610		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont									INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GL405		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont									INT, IOC								OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC24FJ256GL406		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GL408		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GL410		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GU405		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GU406		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GU408		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ256GU410		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ32GA002		ADC1					COMP		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ32GA004		ADC1					COMP		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ32GA102		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT									INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ32GA104		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT									INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ32GB002		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT									INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ32GB004		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT									INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ32MC101		ADC1					COMP1, COMP2, COMP3													INT, IOC					IC1, IC2, IC3	OC1, OC2		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1		VREF	WDT
PIC24FJ32MC102		ADC1					COMP1, COMP2, COMP3													INT, IOC					IC1, IC2, IC3	OC1, OC2		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1		VREF	WDT
PIC24FJ32MC104		ADC1					COMP1, COMP2, COMP3													INT, IOC					IC1, IC2, IC3	OC1, OC2		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1		VREF	WDT
PIC24FJ48GA002		ADC1					COMP		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ48GA004		ADC1					COMP		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC24FJ512GA606		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont									INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ512GA610		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont									INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ512GB606		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont									INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ512GB610		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont									INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ512GL405		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont									INT, IOC								OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ512GL406		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont									INT, IOC								OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ512GL408		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont									INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ512GL410		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont									INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ512GU405		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont									INT, IOC								OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ512GU406		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont									INT, IOC								OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ512GU408		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont									INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ512GU410		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont									INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GA002		ADC1					COMP		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ64GA004		ADC1					COMP		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ64GA006		ADC1					COMP		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ64GA008		ADC1					COMP		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC24FJ64GA010		ADC1					COMP		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ64GA102		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT									INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ64GA104		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT									INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ64GA106		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GA108		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GA110		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GA202		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT	DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont	DSM							INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GA204		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT	DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont	DSM							INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GA306		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT	DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont	DSM							INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7	OC1, OC2, OC3, OC4, OC5, OC6, OC7		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GA308		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT	DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont	DSM							INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7	OC1, OC2, OC3, OC4, OC5, OC6, OC7		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GA310		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT	DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont	DSM							INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7	OC1, OC2, OC3, OC4, OC5, OC6, OC7		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GA406		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GA410		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GA412		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GA702		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3	OC1, OC2, OC3		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC24FJ64GA704		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3	OC1, OC2, OC3		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2		VREF	WDT
PIC24FJ64GA705		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3	OC1, OC2, OC3		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2		VREF	WDT
PIC24FJ64GB002		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT									INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ64GB004		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT									INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ64GB106		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GB108		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GB110		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GB202		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT	DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont	DSM							INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GB204		ADC1					COMP1, COMP2, COMP3		CRC		DSWDT	DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont	DSM							INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GB406		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GB410		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GB412		ADC1	BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6	OC1, OC2, OC3, OC4, OC5, OC6		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GC006							COMP1, COMP2, COMP3		CRC		DSWDT	DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont	DSM							INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GC010							COMP1, COMP2, COMP3		CRC		DSWDT	DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont	DSM							INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5			VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC24FJ64GL302		ADC1		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTB, PORTC, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GL303		ADC1		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GL305		ADC1		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ64GL306		ADC1		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5			COMP1, COMP2, COMP3		CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4		VREF	WDT
PIC24FJ96GA006		ADC1					COMP		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ96GA008		ADC1					COMP		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FJ96GA010		ADC1					COMP		CRC											INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FV08KM101		ADC1		MCCP1/SCCP1, MCCP2/SCCP2			COMP1													INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1		VREF	WDT
PIC24FV08KM102		ADC1		MCCP1/SCCP1, MCCP2/SCCP2			COMP1													INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1		VREF	WDT
PIC24FV08KM202		ADC1		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5			COMP1, COMP2, COMP3													INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1, UART2		VREF	WDT
PIC24FV08KM204		ADC1		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5			COMP1, COMP2, COMP3													INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1, UART2		VREF	WDT
PIC24FV16KA301		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3	OC1, OC2, OC3		OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FV16KA302		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3	OC1, OC2, OC3		OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FV16KA304		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3	OC1, OC2, OC3		OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FV16KM102		ADC1		MCCP1/SCCP1, MCCP2/SCCP2			COMP1													INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1		VREF	WDT
PIC24FV16KM104		ADC1		MCCP1/SCCP1, MCCP2/SCCP2			COMP1													INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1		VREF	WDT
PIC24FV16KM202		ADC1		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5			COMP1, COMP2, COMP3													INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1, UART2		VREF	WDT
PIC24FV16KM204		ADC1		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5			COMP1, COMP2, COMP3													INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1, UART2		VREF	WDT
PIC24FV32KA301		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3	OC1, OC2, OC3		OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FV32KA302		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3	OC1, OC2, OC3		OSC		PORTA, PORTB			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24FV32KA304		ADC1					COMP1, COMP2, COMP3		CRC											INT, IOC					IC1, IC2, IC3	OC1, OC2, OC3		OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24HJ128GP202		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC24HJ128GP204		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24HJ128GP206		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ128GP206A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ128GP210		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ128GP210A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ128GP306		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ128GP306A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ128GP310		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ128GP310A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ128GP502		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24HJ128GP504		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24HJ128GP506		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ128GP506A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC24HJ128GP510		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ128GP510A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ12GP201		ADC1																		INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
PIC24HJ12GP202		ADC1																		INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
PIC24HJ16GP304		ADC1																		INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
PIC24HJ256GP206		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ256GP206A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ256GP210		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ256GP210A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ256GP610		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ256GP610A		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ32GP202		ADC1																		INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
PIC24HJ32GP204		ADC1																		INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
PIC24HJ32GP302		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24HJ32GP304		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24HJ64GP202		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC24HJ64GP204		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24HJ64GP206		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ64GP206A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ64GP210		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ64GP210A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ64GP502		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24HJ64GP504		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
PIC24HJ64GP506		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ64GP506A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ64GP510		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC24HJ64GP510A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
PIC32CX0525G12084																																					SYSTICK					
PIC32CX0525G12144																																					SYSTICK					
PIC32MK0256GPG048							COMP1, COMP4	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT32
PIC32MK0256GPG064							COMP1, COMP2, COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MK0256MCJ048							COMP1, COMP4	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT32
PIC32MK0256MCJ064							COMP1, COMP2, COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT32
PIC32MK0512GPD064							COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MK0512GPD100							COMP1, COMP2, COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MK0512GPE064							COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MK0512GPE100							COMP1, COMP2, COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MK0512GPG048							COMP1, COMP4	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT32
PIC32MK0512GPG064							COMP1, COMP2, COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MK0512GPK064							COMP1, COMP2, COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MK0512GPK100							COMP1, COMP2, COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MK0512MCF064							COMP1, COMP2, COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MK0512MCF100							COMP1, COMP2, COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MK0512MCJ048							COMP1, COMP4	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT32
PIC32MK0512MCJ064							COMP1, COMP2, COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT32
PIC32MK0512MCM064							COMP1, COMP2, COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MK0512MCM100							COMP1, COMP2, COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MK1024GPD064							COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MK1024GPD100							COMP1, COMP2, COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MK1024GPE064							COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MK1024GPE100							COMP1, COMP2, COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MK1024GPK064							COMP1, COMP2, COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MK1024GPK100							COMP1, COMP2, COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MK1024MCF064							COMP1, COMP2, COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MK1024MCF100							COMP1, COMP2, COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MK1024MCM064							COMP1, COMP2, COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MK1024MCM100							COMP1, COMP2, COMP3, COMP4, COMP5	CoreTimer				DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MM0016GPL020		ADC		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3			COMP1, COMP2	CoreTimer												INT, IOC								OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1	UART1, UART2			WDT32
PIC32MM0016GPL028		ADC		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3			COMP1, COMP2	CoreTimer												INT, IOC								OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1	UART1, UART2			WDT32
PIC32MM0016GPL036		ADC		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3			COMP1, COMP2	CoreTimer												INT, IOC								OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1	UART1, UART2			WDT32
PIC32MM0032GPL020		ADC		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3			COMP1, COMP2	CoreTimer												INT, IOC								OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1	UART1, UART2			WDT32
PIC32MM0032GPL028		ADC		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3			COMP1, COMP2	CoreTimer												INT, IOC								OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1	UART1, UART2			WDT32
PIC32MM0032GPL036		ADC		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3			COMP1, COMP2	CoreTimer												INT, IOC								OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1	UART1, UART2			WDT32
PIC32MM0064GPL020		ADC		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3			COMP1, COMP2	CoreTimer												INT, IOC								OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1	UART1, UART2			WDT32
PIC32MM0064GPL028		ADC		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3			COMP1, COMP2	CoreTimer												INT, IOC								OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1	UART1, UART2			WDT32
PIC32MM0064GPL036		ADC		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3			COMP1, COMP2	CoreTimer												INT, IOC								OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1	UART1, UART2			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MM0064GPM028		ADC		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8, SCCP9			COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC								OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2, UART3			WDT32
PIC32MM0064GPM036		ADC		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8, SCCP9			COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC								OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2, UART3			WDT32
PIC32MM0064GPM048		ADC		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8, SCCP9			COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2, UART3			WDT32
PIC32MM0064GPM064		ADC		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8, SCCP9			COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2, UART3			WDT32
PIC32MM0128GPM028		ADC		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8, SCCP9			COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC								OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2, UART3			WDT32
PIC32MM0128GPM036		ADC		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8, SCCP9			COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC								OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2, UART3			WDT32
PIC32MM0128GPM048		ADC		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8, SCCP9			COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2, UART3			WDT32
PIC32MM0128GPM064		ADC		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8, SCCP9			COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2, UART3			WDT32
PIC32MM0256GPM028		ADC		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8, SCCP9			COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC								OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2, UART3			WDT32
PIC32MM0256GPM036		ADC		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8, SCCP9			COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC								OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2, UART3			WDT32
PIC32MM0256GPM048		ADC		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8, SCCP9			COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2, UART3			WDT32
PIC32MM0256GPM064		ADC		MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8, SCCP9			COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2, UART3			WDT32
PIC32MX110F016B		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX110F016C		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX110F016D		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX120F032B		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX120F032C		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX120F032D		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX120F064H		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MX130F064B		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX130F064C		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX130F064D		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX130F128H		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4			WDT32
PIC32MX130F128L		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5			WDT32
PIC32MX130F256B		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX130F256D		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX150F128B		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX150F128C		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX150F128D		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX150F256H		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4			WDT32
PIC32MX150F256L		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5			WDT32
PIC32MX154F128B		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX154F128D		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX170F256B		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX170F256D		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX170F512H		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4			WDT32
PIC32MX170F512L		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5			WDT32
PIC32MX174F256B		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX174F256D		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX210F016B		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MX210F016C		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX210F016D		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX220F032B		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX220F032C		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX220F032D		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX230F064B		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX230F064C		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX230F064D		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX230F128H		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4			WDT32
PIC32MX230F128L		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5			WDT32
PIC32MX230F256B		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX230F256D		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX250F128B		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX250F128C		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX250F128D		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX250F256H		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4			WDT32
PIC32MX250F256L		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5			WDT32
PIC32MX254F128B		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX254F128D		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX270F256B		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX270F256D		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MX270F512H		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4			WDT32
PIC32MX270F512L		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5			WDT32
PIC32MX274F256B		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX274F256D		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX320F032H		ADC					COMP1, COMP2	CoreTimer												INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX320F064H		ADC					COMP1, COMP2	CoreTimer												INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX320F128H		ADC					COMP1, COMP2	CoreTimer												INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX320F128L		ADC					COMP1, COMP2	CoreTimer												INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX330F064H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4			WDT32
PIC32MX330F064L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5			WDT32
PIC32MX340F128H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX340F128L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX340F256H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX340F512H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX350F128H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4			WDT32
PIC32MX350F128L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5			WDT32
PIC32MX350F256H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4			WDT32
PIC32MX350F256L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5			WDT32
PIC32MX360F256L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX360F512L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX370F512H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MX370F512L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5			WDT32
PIC32MX420F032H		ADC					COMP1, COMP2	CoreTimer												INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX430F064H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4			WDT32
PIC32MX430F064L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5			WDT32
PIC32MX440F128H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX440F128L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX440F256H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX440F512H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX450F128H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4			WDT32
PIC32MX450F128L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5			WDT32
PIC32MX450F256H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4			WDT32
PIC32MX450F256L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5			WDT32
PIC32MX460F256L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX460F512L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT32
PIC32MX470F512H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4			WDT32
PIC32MX470F512L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5			WDT32
PIC32MX530F128H		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4			WDT32
PIC32MX530F128L		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5			WDT32
PIC32MX534F064H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX534F064L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX550F256H		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MX550F256L		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5			WDT32
PIC32MX564F064H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX564F064L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX564F128H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX564F128L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX570F512H		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4			WDT32
PIC32MX570F512L		ADC					COMP1, COMP2, COMP3	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5			WDT32
PIC32MX575F256H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX575F256L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX575F512H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX575F512L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX664F064H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX664F064L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX664F128H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX664F128L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX675F256H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX675F256L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX675F512H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MX675F512L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX695F512H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX695F512L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX764F128H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX764F128L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX775F256H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX775F256L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX775F512H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX775F512L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX795F512H		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MX795F512L		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5	OC1, OC2, OC3, OC4, OC5		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ0512EFE064							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ0512EFE100							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ0512EFE124							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ0512EFE144							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MZ0512EFF064							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ0512EFF100							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ0512EFF124							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ0512EFF144							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ0512EFK064							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ0512EFK100							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ0512EFK124							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ0512EFK144							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024ECG064		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024ECG100		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024ECG124		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024ECG144		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MZ1024ECH064		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024ECH100		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024ECH124		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024ECH144		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024ECM064		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024ECM100		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024ECM124		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024ECM144		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFE064							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFE100							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFE124							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFE144							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MZ1024EFF064							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFF100							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFF124							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFF144							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFG064							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFG100							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFG124							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFG144							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFH064							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFH100							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFH124							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFH144							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MZ1024EFK064							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFK100							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFK124							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFK144							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFM064							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFM100							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFM124							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1024EFM144							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1025DAA169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1025DAA176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1025DAA288							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1025DAB169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MZ1025DAB176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1025DAB288							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1025DAG169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1025DAG176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1025DAH169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1025DAH176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1025DAK169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1025DAK176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1025DAL169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1025DAL176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1025DAR169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1025DAR176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MZ1025DA5169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1025DA5176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1025W104132								CoreTimer				DMA								INT, IOC										PORTA, PORTB, PORTC, PORTK	PPS		PullUp	RTSP				TMR2, TMR3, TMR4, TMR5, TMR6, TMR7	UART1			
PIC32MZ1064DAA169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1064DAA176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1064DAA288							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1064DAB169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1064DAB176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1064DAB288							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1064DAG169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1064DAG176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1064DAH169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MZ1064DAH176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1064DAK169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1064DAK176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1064DAL169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1064DAL176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1064DAR169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1064DAR176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1064DAS169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ1064DAS176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2025DAA169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2025DAA176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2025DAA288							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MZ2025DAB169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2025DAB176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2025DAB288							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2025DAG169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2025DAG176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2025DAH169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2025DAH176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2025DAK169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2025DAK176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2025DAL169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2025DAL176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2025DAR169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MZ2025DAR176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2025DAS169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2025DAS176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048ECG064		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048ECG100		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048ECG124		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048ECG144		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048ECH064		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048ECH100		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048ECH124		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048ECH144		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048ECM064		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MZ2048ECM100		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048ECM124		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048ECM144		ADC					COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048EFG064							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048EFG100							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048EFG124							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048EFG144							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048EFH064							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048EFH100							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048EFH124							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048EFH144							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048EFM064							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MZ2048EFM100							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048EFM124							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2048EFM144							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2064DAA169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2064DAA176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2064DAA288							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2064DAB169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2064DAB176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2064DAB288							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2064DAG169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2064DAG176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2064DAH169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
PIC32MZ2064DAH176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2064DAK169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2064DAK176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2064DAL169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2064DAL176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2064DAR169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2064DAR176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2064DAS169							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32MZ2064DAS176							COMP1, COMP2	CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4, UART5, UART6			WDT32
PIC32WK2057GPD132								CoreTimer				DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4				PORTA, PORTB, PORTC, PORTK	PPS		PullUp					TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7	UART1, UART2			
dsPIC30F1010		ADC1					COMP1, COMP2													INT, IOC						OC1		OSC		PORTA, PORTB, PORTD, PORTE, PORTF		PWM	PullUp	RTSP				TMR1, TMR2	UART1			WDT
dsPIC30F2010		ADC1																		INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2		OSC		PORTB, PORTC, PORTD, PORTE, PORTF		PWM	PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
dsPIC30F2011		ADC1																		INT, IOC					IC1, IC2	OC1, OC2		OSC		PORTB, PORTC, PORTD			PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
dsPIC30F2012		ADC1																		INT, IOC					IC1, IC2	OC1, OC2		OSC		PORTB, PORTC, PORTD, PORTF			PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
dsPIC30F2020		ADC1					COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1	OC1, OC2		OSC		PORTA, PORTB, PORTD, PORTE, PORTF		PWM	PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC30F2023		ADC1					COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1	OC1, OC2		OSC		PORTA, PORTB, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
dsPIC30F3010		ADC1																		INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2		OSC		PORTB, PORTC, PORTD, PORTE, PORTF		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1			WDT
dsPIC30F3011		ADC1																		INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTB, PORTC, PORTD, PORTE, PORTF		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC30F3012		ADC1																		INT, IOC					IC1, IC2	OC1, OC2		OSC		PORTB, PORTC, PORTD			PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
dsPIC30F3013		ADC1																		INT, IOC					IC1, IC2	OC1, OC2		OSC		PORTB, PORTC, PORTD, PORTF			PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2			WDT
dsPIC30F3014		ADC1																		INT, IOC					IC1, IC2	OC1, OC2		OSC		PORTA, PORTB, PORTC, PORTD, PORTF			PullUp	RTSP				TMR1, TMR2, TMR3	UART1, UART2			WDT
dsPIC30F4011		ADC1																		INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTB, PORTC, PORTD, PORTE, PORTF		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC30F4012		ADC1																		INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2		OSC		PORTB, PORTC, PORTD, PORTE, PORTF		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1			WDT
dsPIC30F4013		ADC1																		INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTF			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC30F5011		ADC1																		INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC30F5013		ADC1																		INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC30F5015		ADC1																		INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1			WDT
dsPIC30F5016		ADC1																		INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1			WDT
dsPIC30F6010		ADC1																		INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC30F6010A		ADC1																		INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC30F6011		ADC1																		INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC30F6011A		ADC1																		INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC30F6012		ADC1																		INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC30F6012A		ADC1																		INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC30F6013		ADC1																		INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC30F6013A		ADC1																		INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC30F6014		ADC1																		INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC30F6014A		ADC1																		INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC30F6015		ADC1																		INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33CH128MP202				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH128MP202S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB			PullUp	RTSP				TMR1	UART1			
dsPIC33CH128MP203				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH128MP203S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1			
dsPIC33CH128MP205				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH128MP205S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1			
dsPIC33CH128MP206				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH128MP206S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1			
dsPIC33CH128MP208				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH128MP208S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1			

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33CH128MP502				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH128MP502S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB			PullUp	RTSP				TMR1	UART1			
dsPIC33CH128MP503				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH128MP503S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1			
dsPIC33CH128MP505				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH128MP505S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1			
dsPIC33CH128MP506				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH128MP506S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1			
dsPIC33CH128MP508				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH128MP508S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1			
dsPIC33CH256MP205			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH256MP205S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1			
dsPIC33CH256MP206			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH256MP206S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1			
dsPIC33CH256MP208			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH256MP208S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1			
dsPIC33CH256MP505			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH256MP505S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1			
dsPIC33CH256MP506			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33CH256MP506S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1			
dsPIC33CH256MP508			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH256MP508S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1			
dsPIC33CH512MP205			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH512MP205S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1			
dsPIC33CH512MP206			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH512MP206S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1			
dsPIC33CH512MP208			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH512MP208S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1			
dsPIC33CH512MP505			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH512MP505S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1			
dsPIC33CH512MP506			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH512MP506S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1			
dsPIC33CH512MP508			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH512MP508S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1			
dsPIC33CH64MP202				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH64MP202S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB			PullUp	RTSP				TMR1	UART1			
dsPIC33CH64MP203				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH64MP203S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1			

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33CH64MP205				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH64MP205S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1			
dsPIC33CH64MP206				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH64MP206S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1			
dsPIC33CH64MP208				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH64MP208S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1			
dsPIC33CH64MP502				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH64MP502S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB			PullUp	RTSP				TMR1	UART1			
dsPIC33CH64MP503				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH64MP503S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1			
dsPIC33CH64MP505				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH64MP505S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1			
dsPIC33CH64MP506				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH64MP506S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1			
dsPIC33CH64MP508				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMA24FCHANNEL4, DMA24FCHANNEL5, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1, UART2			WDT
dsPIC33CH64MP508S1			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4								DMA24FCHANNEL0, DMA24FCHANNEL1, DMACont								INT, IOC										PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1			
dsPIC33CK128MP202			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK128MP203			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK128MP205			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33CK128MP206			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK128MP208			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK128MP502			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK128MP503			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK128MP505			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK128MP506			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK128MP508			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK256MP202			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK256MP203			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK256MP205			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK256MP206			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK256MP208			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK256MP502			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK256MP503			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK256MP505			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK256MP506			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK256MP508			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK32MC102				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33CK32MC103				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK32MC105				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK32MP102				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK32MP103				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK32MP105				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK32MP202			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK32MP203			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK32MP205			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK32MP206			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK32MP502			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK32MP503			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK32MP505			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK32MP506			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK64MC102				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK64MC103				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK64MC105				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK64MP102				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK64MP103				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK64MP105				MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33CK64MP202			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK64MP203			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK64MP205			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK64MP206			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK64MP208			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK64MP502			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK64MP503			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK64MP505			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK64MP506			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33CK64MP508			BootSwap	MCCP1/SCCP1, MCCP2/SCCP2, MCCP3/SCCP3, SCCP4, SCCP5, SCCP6, SCCP7, SCCP8					CRC			DMA24FCHANNEL0, DMA24FCHANNEL1, DMA24FCHANNEL2, DMA24FCHANNEL3, DMACont								INT, IOC								OSC		PORTA, PORTB, PORTC, PORTD, PORTE			PullUp	RTSP				TMR1	UART1, UART2, UART3			WDT
dsPIC33EDV64MC205		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC						IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4			OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP128GM304		ADC1, ADC2					COMP1, COMP2, COMP3, COMP4, COMP5		CRC			DMA								INT, IOC						IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8			OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
dsPIC33EP128GM306		ADC1, ADC2					COMP1, COMP2, COMP3, COMP4, COMP5		CRC			DMA								INT, IOC						IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8			OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
dsPIC33EP128GM310		ADC1, ADC2					COMP1, COMP2, COMP3, COMP4, COMP5		CRC			DMA								INT, IOC						IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8			OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
dsPIC33EP128GM604		ADC1, ADC2					COMP1, COMP2, COMP3, COMP4, COMP5		CRC			DMA								INT, IOC						IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8			OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33EP128GM706		ADC1, ADC2					COMP1, COMP2, COMP3, COMP4, COMP5		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
dsPIC33EP128GM710		ADC1, ADC2					COMP1, COMP2, COMP3, COMP4, COMP5		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
dsPIC33EP128GP502		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP128GP504		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP128GP506		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP128GS702		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP128GS704		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP128GS705		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP128GS706		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP128GS708		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP128GS804		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP128GS805		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP128GS806		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP128GS808		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33EP128MC202		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP128MC204		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP128MC206		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP128MC502		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP128MC504		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP128MC506		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP16GS202		ADC1					COMP1, COMP2													INT, IOC					IC1	OC1		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
dsPIC33EP16GS502		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP16GS504		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP16GS505		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP16GS506		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP256GM304		ADC1, ADC2					COMP1, COMP2, COMP3, COMP4, COMP5		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
dsPIC33EP256GM306		ADC1, ADC2					COMP1, COMP2, COMP3, COMP4, COMP5		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
dsPIC33EP256GM310		ADC1, ADC2					COMP1, COMP2, COMP3, COMP4, COMP5		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33EP256GM604		ADC1, ADC2					COMP1, COMP2, COMP3, COMP4, COMP5		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
dsPIC33EP256GM706		ADC1, ADC2					COMP1, COMP2, COMP3, COMP4, COMP5		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
dsPIC33EP256GM710		ADC1, ADC2					COMP1, COMP2, COMP3, COMP4, COMP5		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
dsPIC33EP256GP502		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP256GP504		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP256GP506		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP256MC202		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP256MC204		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP256MC206		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP256MC502		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP256MC504		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP256MC506		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP256MU806		ADC1, ADC2					COMP1, COMP2, COMP3		CRC			DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33EP256MU810		ADC1, ADC2					COMP1, COMP2, COMP3		CRC			DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
dsPIC33EP256MU814		ADC1, ADC2					COMP1, COMP2, COMP3		CRC			DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
dsPIC33EP32GP502		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP32GP503		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP32GP504		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP32GS202		ADC1					COMP1, COMP2													INT, IOC					IC1	OC1		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
dsPIC33EP32GS502		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP32GS504		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP32GS505		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP32GS506		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP32MC202		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP32MC203		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP32MC204		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33EP32MC502		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP32MC503		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP32MC504		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP512GM304		ADC1, ADC2					COMP1, COMP2, COMP3, COMP4, COMP5		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
dsPIC33EP512GM306		ADC1, ADC2					COMP1, COMP2, COMP3, COMP4, COMP5		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
dsPIC33EP512GM310		ADC1, ADC2					COMP1, COMP2, COMP3, COMP4, COMP5		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
dsPIC33EP512GM604		ADC1, ADC2					COMP1, COMP2, COMP3, COMP4, COMP5		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
dsPIC33EP512GM706		ADC1, ADC2					COMP1, COMP2, COMP3, COMP4, COMP5		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
dsPIC33EP512GM710		ADC1, ADC2					COMP1, COMP2, COMP3, COMP4, COMP5		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
dsPIC33EP512GP502		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP512GP504		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP512GP506		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33EP512GP806		ADC1, ADC2					COMP1, COMP2, COMP3		CRC			DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
dsPIC33EP512MC202		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP512MC204		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP512MC206		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP512MC502		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP512MC504		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP512MC506		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP512MC806		ADC1, ADC2					COMP1, COMP2, COMP3		CRC			DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
dsPIC33EP512MU810		ADC1, ADC2					COMP1, COMP2, COMP3		CRC			DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT
dsPIC33EP512MU814		ADC1, ADC2					COMP1, COMP2, COMP3		CRC			DMA								INT, IOC					IC10, IC11, IC12, IC13, IC14, IC15, IC16, IC2, IC3, IC4, IC5, IC6, IC7, IC8, IC9	OC10, OC11, OC12, OC13, OC14, OC15, OC16, OC2, OC3, OC4, OC5, OC6, OC7, OC8, OC9		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG, PORTH, PORTJ, PORTK	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2, UART3, UART4		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33EP64GP502		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP64GP503		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP64GP504		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP64GP506		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP64GS502		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP64GS504		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP64GS505		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP64GS506		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP64GS708		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP64GS804		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP64GS805		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP64GS806		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP64GS808		ADC1	BootSwap				COMP1, COMP2, COMP3, COMP4					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33EP64MC202		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP64MC203		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33EP64MC204		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP64MC206		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP64MC502		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP64MC503		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP64MC504		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EP64MC506		ADC1					COMP1, COMP2, COMP3, COMP4		CRC			DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV128GM002		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV128GM003		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV128GM004		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV128GM006		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV128GM102		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV128GM103		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV128GM104		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33EV128GM106		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV256GM002		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV256GM003		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV256GM004		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV256GM006		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV256GM102		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV256GM103		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV256GM104		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV256GM106		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC; PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV32GM002		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV32GM003		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV32GM004		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33EV32GM006		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV32GM102		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV32GM103		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV32GM104		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV32GM106		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV64GM002		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV64GM003		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV64GM004		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV64GM006		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC; PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV64GM102		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV64GM103		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33EV64GM104		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33EV64GM106		ADC1					COMP1, COMP2, COMP3, COMP4, COMP5					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33FJ06GS001		ADC1					COMP1, COMP2													INT, IOC								OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2				WDT
dsPIC33FJ06GS101		ADC1																		INT, IOC						OC1		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2	UART1			WDT
dsPIC33FJ06GS101A		ADC1																		INT, IOC						OC1		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2	UART1			WDT
dsPIC33FJ06GS102		ADC1																		INT, IOC						OC1		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2	UART1			WDT
dsPIC33FJ06GS102A		ADC1																		INT, IOC						OC1		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2	UART1			WDT
dsPIC33FJ06GS202		ADC1					COMP1, COMP2													INT, IOC					IC1	OC1		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2	UART1			WDT
dsPIC33FJ06GS202A		ADC1					COMP1, COMP2													INT, IOC					IC1	OC1		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2	UART1			WDT
dsPIC33FJ09GS302		ADC1					COMP1, COMP2													INT, IOC					IC1	OC1		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2	UART1			WDT
dsPIC33FJ128GP202		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33FJ128GP204		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33FJ128GP206		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ128GP206A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ128GP306		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ128GP306A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ128GP310		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ128GP310A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ128GP706		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33FJ128GP706A		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ128GP708		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ128GP708A		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ128GP710		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ128GP710A		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ128GP802		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33FJ128GP804		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33FJ128MC202		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33FJ128MC204		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33FJ128MC506		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ128MC506A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ128MC510		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ128MC510A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33FJ128MC706		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ128MC706A		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ128MC708		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ128MC708A		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ128MC710		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ128MC710A		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ128MC802		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33FJ128MC804		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33FJ12GP201		ADC1																		INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
dsPIC33FJ12GP202		ADC1																		INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
dsPIC33FJ12MC201		ADC1																		INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
dsPIC33FJ12MC202		ADC1																		INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
dsPIC33FJ16GP101		ADC1					COMP1, COMP2, COMP3													INT, IOC					IC1, IC2, IC3	OC1, OC2		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1		VREF	WDT
dsPIC33FJ16GP102		ADC1					COMP1, COMP2, COMP3													INT, IOC					IC1, IC2, IC3	OC1, OC2		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1		VREF	WDT
dsPIC33FJ16GP304		ADC1																		INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
dsPIC33FJ16GS402		ADC1																		INT, IOC					IC1, IC2	OC1, OC2		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
dsPIC33FJ16GS404		ADC1																		INT, IOC					IC1, IC2	OC1, OC2		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
dsPIC33FJ16GS502		ADC1					COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2	OC1, OC2		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33FJ16GS504		ADC1					COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2	OC1, OC2		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
dsPIC33FJ16MC101		ADC1					COMP1, COMP2, COMP3													INT, IOC					IC1, IC2, IC3	OC1, OC2		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3	UART1		VREF	WDT
dsPIC33FJ16MC102		ADC1					COMP1, COMP2, COMP3													INT, IOC					IC1, IC2, IC3	OC1, OC2		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3	UART1		VREF	WDT
dsPIC33FJ16MC304		ADC1																		INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
dsPIC33FJ256GP506		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ256GP506A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ256GP510		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ256GP510A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ256GP710		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ256GP710A		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ256MC510		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ256MC510A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ256MC710		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33FJ256MC710A		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ32GP101		ADC1					COMP1, COMP2, COMP3													INT, IOC					IC1, IC2, IC3	OC1, OC2		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1		VREF	WDT
dsPIC33FJ32GP102		ADC1					COMP1, COMP2, COMP3													INT, IOC					IC1, IC2, IC3	OC1, OC2		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1		VREF	WDT
dsPIC33FJ32GP104		ADC1					COMP1, COMP2, COMP3													INT, IOC					IC1, IC2, IC3	OC1, OC2		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1		VREF	WDT
dsPIC33FJ32GP202		ADC1																		INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
dsPIC33FJ32GP204		ADC1																		INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
dsPIC33FJ32GP302		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33FJ32GP304		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33FJ32GS406		ADC1																		INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33FJ32GS606		ADC1					COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33FJ32GS608		ADC1					COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33FJ32GS610		ADC1					COMP1, COMP2, COMP3, COMP4													INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33FJ32MC101		ADC1					COMP1, COMP2, COMP3													INT, IOC					IC1, IC2, IC3	OC1, OC2		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1		VREF	WDT
dsPIC33FJ32MC102		ADC1					COMP1, COMP2, COMP3													INT, IOC					IC1, IC2, IC3	OC1, OC2		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1		VREF	WDT
dsPIC33FJ32MC104		ADC1					COMP1, COMP2, COMP3													INT, IOC					IC1, IC2, IC3	OC1, OC2		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1		VREF	WDT
dsPIC33FJ32MC202		ADC1																		INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
dsPIC33FJ32MC204		ADC1																		INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3	UART1			WDT
dsPIC33FJ32MC302		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33FJ32MC304		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33FJ64GP202		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33FJ64GP204		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33FJ64GP206		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ64GP206A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ64GP306		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ64GP306A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ64GP310		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC; PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ64GP310A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ64GP706		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ64GP706A		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ64GP708		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ64GP708A		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ64GP710		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33FJ64GP710A		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG			PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ64GP802		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33FJ64GP804		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS		PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33FJ64GS406		ADC1																		INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33FJ64GS606		ADC1					COMP1, COMP2, COMP3, COMP4					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33FJ64GS608		ADC1					COMP1, COMP2, COMP3, COMP4					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33FJ64GS610		ADC1					COMP1, COMP2, COMP3, COMP4					DMA								INT, IOC					IC1, IC2, IC3, IC4	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2			WDT
dsPIC33FJ64MC202		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33FJ64MC204		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33FJ64MC506		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ64MC506A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ64MC508		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ64MC508A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ64MC510		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT

Device	AC	ADC	Bootswap	CCP	CLC	COG	Comp	CoreTimer	CRC	CWG	DeepSleep	DMA	DSM	EDMA	EEFC	EEFlash	EIC	EVSYS	ExternalInterrupt	INT	FVR	GPIO	HLT	IDAU	IC	OC	MPU	Osc	PIO	Ports	PPS	PWM	PullUp	RTSP	RTT	SMT	SYSTICK	TMR/C	UART	USART	VREF	WDT
dsPIC33FJ64MC510A		ADC1										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ64MC706		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ64MC706A		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ64MC710		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ64MC710A		ADC1, ADC2										DMA								INT, IOC					IC1, IC2, IC3, IC4, IC5, IC6, IC7, IC8	OC1, OC2, OC3, OC4, OC5, OC6, OC7, OC8		OSC		PORTA, PORTB, PORTC, PORTD, PORTE, PORTF, PORTG		PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5, TMR6, TMR7, TMR8, TMR9	UART1, UART2			WDT
dsPIC33FJ64MC802		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
dsPIC33FJ64MC804		ADC1					COMP		CRC			DMA								INT, IOC					IC1, IC2, IC7, IC8	OC1, OC2, OC3, OC4		OSC		PORTA, PORTB, PORTC	PPS	PWM	PullUp	RTSP				TMR1, TMR2, TMR3, TMR4, TMR5	UART1, UART2		VREF	WDT
rfPIC12C509AF																						GPIO						OSC					PullUp					TMR0				WDT
rfPIC12C509AG																						GPIO						OSC					PullUp					TMR0				WDT
rfPIC12F675F		ADC					COMP1, CVREF									EEFlash				INT, IOC	FVR	GPIO						OSC					PullUp					TMR0, TMR1				WDT
rfPIC12F675H		ADC					COMP1, CVREF									EEFlash				INT, IOC	FVR	GPIO						OSC					PullUp					TMR0, TMR1				WDT
rfPIC12F675K		ADC					COMP1, CVREF									EEFlash				INT, IOC	FVR	GPIO						OSC					PullUp					TMR0, TMR1				WDT

5/26/2020 13:56

Simulator Peripheral Support by Device - Table Heading Descriptions

See your device documentation or family reference manual for details on each peripheral.

Peripheral Heading	Simulator Peripheral Module*
AC	AC = Analog Comparator. ACC = Analog Comparator Controller.
ADC	ADC*n* = Analog-to-Digital Converter module.
Bootswap	Boot and Program Flash memory regions can be swapped during run-time.
CCP	CCP*n* = Capture/Compare/PWM module. ECCP*n* = Enhanced Capture/Compare/PWM module. MCCP*n* = Multiple Capture/Compare/PWM module. SCCP*n* = Single Capture/Compare/PWM module.
CLC	CLC*n* = Configurable Logic Cell.
COG	COG*n* = Complementary Output Generator module. Used with the Complementary Waveform Generator (CWG).
Comp	COMP*n* = Comparitor module. CVREF = Comparitor Voltage Reference.
CoreTimer	PIC32 Core timer.
CRC	Cyclic Redundancy Code module. Also CRC/Scan.
CWG	CWG*n* = Complementary Waveform Generator module. Used with the Complementary Output Generator (COG).
DeepSleep	Deep Sleep. DSWDT = Deep Sleep Watchdog Timer.
DMA	DMA, DMACont = Direct Memory Access controller. DMA24FCHANNEL0*n* = PIC24 DMA channel.
DSM	Data Signal Modulator module.
EEFC	Enhanced Embedded Flash Controller.
EEFlash	EE Flash program memory.
EVSYS	Environmental System - Temperature Sensor.
ExternalInterrupt	ExternalInterrupt = External Interrupt on INT[6,3:0] pins. PinChangeInterrupt = External Interrupt on PCINT[7:0] pins.
INT	INT or INT*n* = External Interupt pins. IOC = Interrupt on Change pin.
FVR	Fixed Voltage Reference (FVR) module. Optionally used by the ADC, DAC, Comparator, and Temperature sensor modules.
GPIO	General Purpose Input/Output.
HLT	HLT*n* = Hardware Limit Timer.
IC	IC*n* = Input Capture module.
OC	OC*n* = Output Compare module.
MPU	Memory Protection Unit.
Osc	OSC = Oscillator module. NCO = Numerically Controlled Oscillator module.
PIO	PIO*a* = PIO*a* module. Peripheral I/O controllers.
Ports	PORT*a* = Port*a* module. PBADEN = Port B ADC enable configuration bit.
PPS	PPS = Peripheral Pin Select without lock. PPSLock = Peripheral Pin Select with lock.
PWM	PWM*n* = Pulse Width Modulation module.
PullUp	Pullup circuitry on pins.

Peripheral Heading	Simulator Peripheral Module*
RTSP	Run-Time Self-Programming feature.
RTT	Run-Time Timer.
SMT	SMT*n* = Signal Measurement Timer.
SYSTICK	The Cortex-M7 SysTick external clock.
TMR/CNTR	TC*x* = Timer/Counter. TMR*n* = Timer module.
UART	UART*n* = Universal Asynchronous Receive/Transmit module.
VREF	Voltage Reference module.
WDT	WDT = Watchdog Timer. WDT32 = 32-bit Watchdog Timer.
* If there is more than one module: *n* represents the module number, or *a* represents the module letter, or *x* represents either the module number or letter.	