

SAM 4S Series Family Silicon Errata and Data Sheet Clarification

The SAM 4S Series family of devices that you have received conform functionally to the current Device Data Sheet (11100K-ATARM-SAM4S-Datasheet_09-Jun-15), except for the anomalies described in this document.

New Silicon Errata Issues

Note: This document provides information on new errata issues for the SAM 4S Series of devices. Please refer to the current device data sheet for all pre-existing silicon errata issues.

1. Module: Voltage Regulator

The embedded voltage regulator does not work under the temperature below +25°C when VDDIN is supplied below 2.8V.

Work around

VDDIN must be supplied at 2.8V minimum to guarantee embedded voltage regulator start-up down to -40°C.

Affected Silicon Revisions

A	B						
X							

Note: The voltage regulator errata is not applicable to ATSAM4S2 and ATSAM4S4 derivatives.

2. Module: ADC

The ADC does not start when using under these conditions: VDDANA < 2.4V or ADVREF < 2.4V, and temperature T° < 0°C.

Work around

Use reserved value of the IBCTL field in the ADC Analog Control Register (ADC_ACR) IBCTL= 11b to ensure a correct startup of the ADC with a higher bias current (Typically, +50% higher than the standard configuration). This setup can be kept for standard analog conversions. If current consumption is critical, the IBCTL field setting must be kept to 11b at least during 20 µs before being changed to its nominal value.

Affected Silicon Revisions

A	B						
X	X						

SAM 4S SERIES

Data Sheet Clarifications

1. Module: Ordering Information

In the current device data sheet, the SAM4S Ordering Codes table (Table 47-1) is incorrect. The correct information is provided in the following table.

TABLE 47-1: SAM4S ORDERING CODES TABLE

Ordering Code	MRL	Flash (Kbytes)	SRAM (Kbytes)	Package	Carrier Type	Operating Temperature Range
ATSAM4SD32CA-CU	A	2*1024	160	TFBGA100	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4SD32CB-CN	B					Industrial (-40°C to +105°C)
ATSAM4SD32CA-CFU	A	2*1024	160	VFBGA100	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4SD32CB-CFN	B					Industrial (-40°C to +105°C)
ATSAM4SD32CA-AU	A	2*1024	160	LQFP100	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4SD32CB-AN	B					Industrial (-40°C to +105°C)
ATSAM4SD32BA-MU	A	2*1024	160	QFN64	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4SD32BB-MN	B					Industrial (-40°C to +105°C)
ATSAM4SD32BA-AU	A	2*1024	160	LQFP64	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4SD32BB-AN	B					Industrial (-40°C to +105°C)
ATSAM4SD32BA-UUR	A	2*1024	160	WLCSP64	Tape and Reel	Industrial (-40°C to +85°C)
ATSAM4SD32BB-UUR	B					
ATSAM4SD16CA-CU	A	2*1024	160	TFBGA100	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4SD16CB-CN	B					Industrial (-40°C to +105°C)
ATSAM4SD16CA-CFU	A	2*512	160	VFBGA100	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4SD16CB-CFN	B					Industrial (-40°C to +105°C)
ATSAM4SD16CA-AU	A	2*512	160	LQFP100	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4SD16CB-AN	B					Industrial (-40°C to +105°C)
ATSAM4SD16BA-MU	A	2*512	160	QFN64	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4SD16BB-MN	B					Industrial (-40°C to +105°C)
ATSAM4SD16BA-AU	A	2*512	160	LQFP64	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4SD16BB-AN	B					Industrial (-40°C to +105°C)
ATSAM4SD16BA-UUR	A	2*512	160	WLCSP64	Tape and Reel	Industrial (-40°C to +85°C)
ATSAM4SD16BB-UUR	B					
ATSAM4SA16CA-CU	A	1024	160	TFBGA100	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4SA16CB-CN	B					Industrial (-40°C to +105°C)
ATSAM4SA16CA-CFU	A	1024	160	VFBGA100	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4SA16CB-CFN	B					Industrial (-40°C to +105°C)
ATSAM4SA16CA-AU	A	1024	160	LQFP100	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4SA16CB-AN	B					Industrial (-40°C to +105°C)
ATSAM4SA16BA-MU	A	1024	160	QFN64	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4SA16BB-MN	B					Industrial (-40°C to +105°C)
ATSAM4SA16BA-AU	A	1024	160	LQFP64	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4SA16BB-AN	B					Industrial (-40°C to +105°C)
ATSAM4S16CA-CU	A	1024	128	TFBGA100	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S16CB-CN	B					Industrial (-40°C to +105°C)
ATSAM4S16CA-AU	A	1024	128	LQFP100	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S16CB-AN	B					Industrial (-40°C to +105°C)

SAM 4S SERIES

Ordering Code	MRL	Flash (Kbytes)	SRAM (Kbytes)	Package	Carrier Type	Operating Temperature Range
ATSAM4S16CA-CFU	A	1024	128	VFPGA100	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S16CB-CFN	B					Industrial (-40°C to +105°C)
ATSAM4S16BA-AU	A	1024	128	LQFP64	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S16BB-AN	B					Industrial (-40°C to +105°C)
ATSAM4S16BA-MU	A	1024	128	LQFP64	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S16BB-MN	B					Industrial (-40°C to +105°C)
ATSAM4S16BA-UUR	A	1024	128	WLCSP64	Tape and Reel	Industrial (-40°C to +85°C)
ATSAM4S16BB-UUR	B					
ATSAM4S8CA-CU	A	512	128	TFBGA100	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S8CB-CN	B					Industrial (-40°C to +105°C)
ATSAM4S8CA-CFU	A	1024	128	VFPGA100	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S8CB-CFN	B					Industrial (-40°C to +105°C)
ATSAM4S8CA-AU	A	1024	128	LQFP100	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S8CB-AN	B					Industrial (-40°C to +105°C)
ATSAM4S8BA-MU	A	1024	128	QFN64	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S8BB-MN	B					Industrial (-40°C to +105°C)
ATSAM4S8BA-UUR	A	512	128	WLCSP64	Tape and Reel	Industrial (-40°C to +85°C)
ATSAM4S8BB-UUR	B					
ATSAM4S8BA-AU	A	512	128	LQFP64	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S8BB-AN	B					Industrial (-40°C to +105°C)
ATSAM4S4CA-CU	A	256	64	TFBGA100	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S4CB-CN	B					Industrial (-40°C to +105°C)
ATSAM4S4CA-CFU	A	256	64	VFPGA100	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S4CB-CFN	B					Industrial (-40°C to +105°C)
ATSAM4S4CA-AU	A	256	64	LQFP100	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S4CB-AN	B					Industrial (-40°C to +105°C)
ATSAM4S4BA-MU	A	256	64	QFN64	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S4BB-MN	B					Industrial (-40°C to +105°C)
ATSAM4S4BA-UUR	A	256	64	WLCSP64	Tape and Reel	Industrial (-40°C to +85°C)
ATSAM4S4BB-UUR	B					
ATSAM4S4BA-AU	A	256	64	LQFP64	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S4BB-AN	B					Industrial (-40°C to +105°C)
ATSAM4S4AA-MU	A	256	64	QFN48	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S4AB-MN	B					Industrial (-40°C to +105°C)
ATSAM4S4AA-AU	A	256	64	LQFP48	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S4AB-AN	B					Industrial (-40°C to +105°C)
ATSAM4S2CA-CU	A	256	64	TFBGA100	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S2CB-CN	B					Industrial (-40°C to +105°C)
ATSAM4S2CA-CFU	A	256	64	VFPGA100	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S2CB-CFN	B					Industrial (-40°C to +105°C)
ATSAM4S2CA-AU	A	256	64	LQFP100	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S2CB-AN	B					Industrial (-40°C to +105°C)
ATSAM4S2BA-MU	A	256	64	QFN64	Tray, Tape and Reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S2BB-MN	B					Industrial (-40°C to +105°C)

SAM 4S SERIES

Ordering Code	MRL	Flash (Kbytes)	SRAM (Kbytes)	Package	Carrier Type	Operating Temperature Range
ATSAM4S2BA-UUR	A	128	64	WLCSP64	Tape and Reel	Industrial (-40°C to +85°C)
ATSAM4S2BB-UUR	B					
ATSAM4S2BA-AU	A	128	64	LQFP64	Tray, Tape and reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S2BB-AN	B					Industrial (-40°C to +105°C)
ATSAM4S2AA-MU	A	256	64	QFN48	Tray, Tape and reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S2AB-MN	B					Industrial (-40°C to +105°C)
ATSAM4S2AA-AU	A	256	64	LQFP48	Tray, Tape and reel (add R to ordering code)	Industrial (-40°C to +85°C)
ATSAM4S2AB-AN	B					Industrial (-40°C to +105°C)

2. Module: CHIP ID

Table 30-1. "SAM 4S Chip ID Registers" is updated with Chip ID information. The newly added information is shown in **BOLD**.

TABLE 30-1: SAM 4S CHIP ID REGISTERS

Chip Name	CHIPID_CIDR	CHIPID_EXID
SAM4SD32C (Rev A)	0x29A7_0EE0	0x0
SAM4SD32C (Rev B)	0x29A7_0EE1	0x0
SAM4SD32B (Rev A)	0x2997_0EE0	0x0
SAM4SD32B (Rev B)	0x2997_0EE1	0x0
SAM4SD16C (Rev A)	0x29A7_0CE0	0x0
SAM4SD16C (Rev B)	0x29A7_0CE1	0x0
SAM4SD16B (Rev A)	0x2997_0CE0	0x0
SAM4SD16B (Rev B)	0x2997_0CE1	0x0
SAM4SA16C (Rev A)	0x28A7_0CE0	0x0
SAM4SA16C (Rev B)	0x28A7_0CE1	0x0
SAM4SA16B (Rev A)	0x2897_0CE0	0x0
SAM4SA16B (Rev B)	0x2897_0CE1	0x0
SAM4S16B (Rev A)	0x289C_0CE0	0x0
SAM4S16B (Rev B)	0x289C_0CE1	0x0
SAM4S16C (Rev A)	0x28AC_0CE0	0x0
SAM4S16C (Rev B)	0x28AC_0CE1	0x0
SAM4S8B (Rev A)	0x289C_0AE0	0x0
SAM4S8B (Rev B)	0x289C_0AE1	0x0
SAM4S8C (Rev A)	0x28AC_0AE0	0x0
SAM4S8C (Rev B)	0x28AC_0AE1	0x0
SAM4S4C (Rev A)	0x28AB_09E0/ 0x28AB_09E1	0x0
SAM4S4C (Rev B)	0x28AB_09E1	0x0

SAM 4S SERIES

TABLE 30-1: SAM 4S CHIP ID REGISTERS

SAM4S4B (Rev A)	0x289B_09E0/ 0x289B_09E1	0x0
SAM4S4B (Rev B)	0x289B_09E1	0x0
SAM4S4A (Rev A)	0x288B_09E0/ 0x288B_09E1	0x0
SAM4S4A (Rev B)	0x288B_09E1	0x0
SAM4S2C (Rev A)	0x28AB_07E0/ 0x28AB_07E1	0x0
SAM4S2C (Rev B)	0x28AB_07E1	0x0
SAM4S2B (Rev A)	0x289B_07E0/ 0x289B_07E1	0x0
SAM4S2B (Rev B)	0x289B_07E1	0x0
SAM4S2A (Rev A)	0x288B_07E0/ 0x288B_07E1	0x0
SAM4S2A (Rev B)	0x288B_07E1	0x0

3. Module: Errata

Table 48-3. “Errata SAM 4S4/S2 Rev A Parts” is updated with Chip ID information. The newly added information is shown in **BOLD**.

TABLE 48-3: ERRATA SAM 4S4/S2 REV A PARTS

Device Name	Revision	Chip ID
SAM4S4C	A	0x28AB_09E0/ 0x28AB_09E1
SAM4S4B	A	0x289B_09E0/ 0x289B_09E1
SAM4S4A	A	0x288B_09E0/ 0x288B_09E1
SAM4S2C	A	0x28AB_07E0/ 0x28AB_07E1
SAM4S2B	A	0x289B_07E0/ 0x289B_07E1
SAM4S2A	A	0x288B_07E0/ 0x288B_07E1

SAM 4S SERIES

APPENDIX A: REVISION HISTORY

Rev A Document (3/2018)

This is the initial released version of this document.

Rev B Document (5/2019)

The following Data Sheet Clarifications were added:

- **2. Module: “CHIP ID”**
- **3. Module: “Errata”**

Rev C Document 10/2020

The packages for the following Ordering Codes were updated in **TABLE 47-1: “SAM4S Ordering Codes Table”**:

- ATSAM4S4AA-MU
- ATSAM4S4AB-MN

Note the following details of the code protection feature on Microchip devices:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods being used in attempts to breach the code protection features of the Microchip devices. We believe that these methods require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Attempts to breach these code protection features, most likely, cannot be accomplished without violating Microchip's intellectual property rights.
- Microchip is willing to work with any customer who is concerned about the integrity of its code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not mean that we are guaranteeing the product is "unbreakable." Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication is provided for the sole purpose of designing with and using Microchip products. Information regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDIRECT, SPECIAL, PUNITIVE, INCIDENTAL OR CONSEQUENTIAL LOSS, DAMAGE, COST OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Trademarks

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, chipKIT, chipKIT logo, CryptoMemory, CryptoRF, dsPIC, FlashFlex, flexPWR, HELDO, IGLoo, JukeBlox, KeeLoq, Klear, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PackeTime, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, FlashTec, Hyper Speed Control, HyperLight Load, IntelliMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimePictra, TimeProvider, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, Augmented Switching, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, IdealBridge, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, Inter-Chip Connectivity, JitterBlocker, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O, simpleMAP, SimpliPHY, SmartBuffer, SMART-I.S., storClad, SQI, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, TSHARC, USBCheck, VariSense, VectorBlox, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2018-2020, Microchip Technology Incorporated, All Rights Reserved.

ISBN:978-1-5224-6950-6

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.



MICROCHIP

Worldwide Sales and Service

AMERICAS

Corporate Office
2355 West Chandler Blvd.
Chandler, AZ 85224-6199
Tel: 480-792-7200
Fax: 480-792-7277
Technical Support:
<http://www.microchip.com/support>
Web Address:
www.microchip.com

Atlanta

Duluth, GA
Tel: 678-957-9614
Fax: 678-957-1455

Austin, TX

Tel: 512-257-3370

Boston

Westborough, MA
Tel: 774-760-0087
Fax: 774-760-0088

Chicago

Itasca, IL
Tel: 630-285-0071
Fax: 630-285-0075

Dallas

Addison, TX
Tel: 972-818-7423
Fax: 972-818-2924

Detroit

Novi, MI
Tel: 248-848-4000

Houston, TX

Tel: 281-894-5983

Indianapolis

Noblesville, IN
Tel: 317-773-8323
Fax: 317-773-5453
Tel: 317-536-2380

Los Angeles

Mission Viejo, CA
Tel: 949-462-9523
Fax: 949-462-9608
Tel: 951-273-7800

Raleigh, NC

Tel: 919-844-7510

New York, NY

Tel: 631-435-6000

San Jose, CA

Tel: 408-735-9110
Tel: 408-436-4270

Canada - Toronto

Tel: 905-695-1980
Fax: 905-695-2078

ASIA/PACIFIC

Australia - Sydney
Tel: 61-2-9868-6733

China - Beijing
Tel: 86-10-8569-7000

China - Chengdu
Tel: 86-28-8665-5511

China - Chongqing
Tel: 86-23-8980-9588

China - Dongguan
Tel: 86-769-8702-9880

China - Guangzhou
Tel: 86-20-8755-8029

China - Hangzhou
Tel: 86-571-8792-8115

China - Hong Kong SAR
Tel: 852-2943-5100

China - Nanjing
Tel: 86-25-8473-2460

China - Qingdao
Tel: 86-532-8502-7355

China - Shanghai
Tel: 86-21-3326-8000

China - Shenyang
Tel: 86-24-2334-2829

China - Shenzhen
Tel: 86-755-8864-2200

China - Suzhou
Tel: 86-186-6233-1526

China - Wuhan
Tel: 86-27-5980-5300

China - Xian
Tel: 86-29-8833-7252

China - Xiamen
Tel: 86-592-2388138

China - Zhuhai
Tel: 86-756-3210040

ASIA/PACIFIC

India - Bangalore
Tel: 91-80-3090-4444

India - New Delhi
Tel: 91-11-4160-8631

India - Pune
Tel: 91-20-4121-0141

Japan - Osaka
Tel: 81-6-6152-7160

Japan - Tokyo
Tel: 81-3-6880-3770

Korea - Daegu
Tel: 82-53-744-4301

Korea - Seoul
Tel: 82-2-554-7200

Malaysia - Kuala Lumpur
Tel: 60-3-7651-7906

Malaysia - Penang
Tel: 60-4-227-8870

Philippines - Manila
Tel: 63-2-634-9065

Singapore
Tel: 65-6334-8870

Taiwan - Hsin Chu
Tel: 886-3-577-8366

Taiwan - Kaohsiung
Tel: 886-7-213-7830

Taiwan - Taipei
Tel: 886-2-2508-8600

Thailand - Bangkok
Tel: 66-2-694-1351

Vietnam - Ho Chi Minh
Tel: 84-28-5448-2100

EUROPE

Austria - Wels
Tel: 43-7242-2244-39
Fax: 43-7242-2244-393

Denmark - Copenhagen
Tel: 45-4485-5910
Fax: 45-4485-2829

Finland - Espoo
Tel: 358-9-4520-820

France - Paris
Tel: 33-1-69-53-63-20
Fax: 33-1-69-30-90-79

Germany - Garching
Tel: 49-8931-9700

Germany - Haan
Tel: 49-2129-3766400

Germany - Heilbronn
Tel: 49-7131-72400

Germany - Karlsruhe
Tel: 49-721-625370

Germany - Munich
Tel: 49-89-627-144-0
Fax: 49-89-627-144-44

Germany - Rosenheim
Tel: 49-8031-354-560

Israel - Ra'anana
Tel: 972-9-744-7705

Italy - Milan
Tel: 39-0331-742611
Fax: 39-0331-466781

Italy - Padova
Tel: 39-049-7625286

Netherlands - Drunen
Tel: 31-416-690399
Fax: 31-416-690340

Norway - Trondheim
Tel: 47-7288-4388

Poland - Warsaw
Tel: 48-22-3325737

Romania - Bucharest
Tel: 40-21-407-87-50

Spain - Madrid
Tel: 34-91-708-08-90
Fax: 34-91-708-08-91

Sweden - Gothenberg
Tel: 46-31-704-60-40

Sweden - Stockholm
Tel: 46-8-5090-4654

UK - Wokingham
Tel: 44-118-921-5800
Fax: 44-118-921-5820