
**AT08946: 915MHz Printed Folded Monopole Antenna
Reference Design**

Atmel Wireless

Features

- Compact PCB antenna for 915MHz ISM band
- Return Loss, gain, and efficiency measurement results
- Easy to integrate Altium® design files and Gerber files
- Guidelines to integrate antenna board with RF board

Description

Scope of this application note is to guide customers to design applications using ATEVK-900-ANT-FM Printed Folded Monopole antenna for 915MHz ISM band based on AT86RF212B transceiver.

This application note contains the physical dimensions of the antenna, RF measurement results, and a brief design note. It describes the methods to integrate this antenna with a 915MHz wireless board for quick prototyping.

Table of Contents

1	Introduction	3
2	Printed Folded Monopole Antenna.....	3
2.1	Antenna Structure	3
2.2	Return Loss Measurement.....	5
2.3	Radiation Pattern, Gain, and Efficiency Measurement.....	6
2.4	Guidelines for Antenna Integration with Transceiver.....	9
3	Abbreviations and Acronyms	9
4	Reference	9
5	Revision History	10

1 Introduction

This application note guides in designing a new 915MHz band Printed Folded Monopole Antenna based on system requirements, board size, and layer stack up.

This antenna reference design can be integrated with any 915MHz ISM band transceiver to verify their prototypes quickly and it acts as a better reference for designing an application using antenna.


2 Printed Folded Monopole Antenna

2.1 Antenna Structure

The 915MHz ISM band (902MHz ~ 928MHz) is commonly used unlicensed band in the United States of America for industrial, scientific, and medical applications. Demand for compact antennas operating in this frequency band is increasing day by day. A standard $\lambda/4$ Printed Monopole Antenna (λ = wavelength) is widely used in many applications due to its small size and better radiation characteristics. It can be used for this application. The operation of monopole is similar to dipole. The ground plane of the monopole acts as the second arm to perform a dipole operation [1]. Any modifications to the size of the ground plane, affects the performance of antenna. So, the designer must be careful about the ground plane size during the design and it must be fixed to the actual board size of the application.

Using folded structure, the size of the monopole can be reduced to fit the available board size with a small degradation in antenna efficiency and radiation pattern when compared with standard antenna. Folded structure actually requires longer trace (in multiple hair-pin bends) than $\lambda/4$ for its operation. However, it occupies lesser space. The structure of the proposed Printed Folded Monopole is shown in Figure 2-1 and the dimension of the antenna is shown in Figure 2-2.

Figure 2-1. 915MHz ISM Band Printed Folded Monopole Antenna with SMA Connector



Using Agilent's ADS tool Return Loss, Gain, Directivity, Efficiency, and Far-Filed Pattern Cuts were tuned in simulation before creating the prototype. PCB parameters are specified in Table 2-1 PCB Layer stackup is shown in Figure 2-3. Feed line is a 50 Ω "CPW with Ground Plane" structure with trace width $W=1.6\text{mm}$ and Trace-Ground gap of 0.4mm on either side. An edge mount SMA connector foot print is placed in the board to assemble SMA connector for measurement and integration purposes.

Table 2-1. PCB Characteristic

PCB Material – Parameter	Value
PCB substrate	FR-4
Dielectric constant (ϵ_r)	4.4
Loss tangent ($\tan\delta$)	0.02
Substrate thickness	1.6mm
Cu thickness	35 μ m

Figure 2-2. Dimension of 915MHz ISM Band Printed Folded Monopole Antenna





Figure 2-3. PCB Layer Stack Up

Layer stackup



NOTE 1A: FR4

2A: SURFACE PROTECTION: Chemical Gold

3: PCB Thickness to be calculated based on Stack up
THE BOARD MUST BE RoHS COMPLIANT

If a standard printed monopole is used for the PCB layer stack up, it requires a $\lambda_g/4$ length of 45mm without including ground plane size. Also, the length of the ground plane must be $\geq \lambda_g/4$ for standard monopole.

$$\lambda_g = \frac{C}{\sqrt{\epsilon_r}f}$$

Where,

- λ_g = Guided wavelength
- C = Velocity of light
- f = Frequency of operation
- ϵ_r = Relative permittivity of dielectric material


The size of the Printed Meander antenna including ground plane is 33.3mm x 23.3mm.

2.2 Return Loss Measurement

Return Loss (S11) is directly measured in a Calibrated Vector Network Analyzer. The measured Return Loss is shown in Figure 2-4. The antenna achieved Return Loss < -10dB for 868MHz to 928MHz.

The antenna can be tuned in prototype in the following manner to operate in the desired band: Increasing the length (trace perpendicular to ground plane) will reduce the resonant frequency of the antenna and decreasing the length will increase the resonant frequency. Length can be increased using copper foil. Increasing the width of the line will improve the bandwidth.

Figure 2-4. Measured Return Loss Plot



2.3 Radiation Pattern, Gain, and Efficiency Measurement

Figure 2-5, Figure 2-6, and Figure 2-7 show Azimuth and Elevation pattern-cuts of the antenna. All these patterns are not normalized with respect to peak value. Antenna was configured in receive mode for all these measurements. The plots represent measured power density by placing the receiving antenna in different orientations. From the results, the pattern is fairly omni-directional in both Azimuth and Elevation planes.

Figure 2-5. Azimuth Radiation Pattern ($\theta=90^\circ$)




Figure 2-6. Elevation Radiation Pattern ($\phi=0^\circ$)




Figure 2-7. Elevation Radiation Pattern ($\phi=90^\circ$)




Figure 2-8. 3D – Radiation Pattern: Front View




Figure 2-9. 3D – Radiation Pattern: Top View





Figure 2-10. 3D – Radiation Pattern: Side View



The measured peak gain of the antenna for 915MHz is -1.26dB and the efficiency is 19%. Efficiency of printed antennas is based on antenna type and ground plane size. This reference design has a very small ground plane and hence the efficiency might be less. If the ground plane is large enough in the final application board, the efficiency might be higher.

2.4 Guidelines for Antenna Integration with Transceiver

- Although, the discussed reference board contains only two layers, this reference design can be used for multilayer application. In multilayer application, antenna can be placed either on top layer or bottom layer based on the available space. Any change in dielectric constant or tangent loss of the PCB material or PCB thickness will shift the resonant frequency and change radiation characteristics. These factors must be considered while designing the application.
- It is usually a better practice to have transceiver and antenna on the same layer without having any via-hole in RF path. Via holes create discontinuity and loss of signal which will require proper impedance matching to reduce loss.
- Copper clearance must be provided in all layers beneath the antenna. Because, conductor will reflect RF signal and change the radiation characteristics of the antenna.
- RF trace connecting Transceiver output (Balun output for Differential output Transceivers) and Antenna Feed point must be 50Ω controlled impedance line. It is highly preferred to have a provision for Pi-pad matching network to improve matching between Transceiver output and antenna input. It will avoid board re-spin during mismatched circumstances. Many combinations of lumped element matching methods are available [2].
- Mechanical enclosure of the product must not have any conductive material. Plastic enclosure is preferred; but, it might also detune the antenna from the desired band. So, tuning the antenna with lumped components must be performed by placing it within the enclosure.
- RF and antenna board can be placed separately. If space is not a constraint, SMA cables can be used to connect RF board with antenna board. Insertion loss of a standard 20cm SMA-Male to SMA-Male cable varies from 0.11dB ~ 0.4dB at 915MHz (depending on the manufacturer). Most ISM band applications are designed on small sized boards. A small board mount RF connector such as U.FL and mating flexible RF cables can be used to connect RF board with antenna board.

3 Abbreviations and Acronyms

BW	:	Bandwidth
CPW	:	Coplanar Waveguide
GND	:	Ground
GHz	:	Giga Hertz
ISM	:	Industrial, Scientific and Medical
MHz	:	Mega Hertz
mm	:	Millimeter
PCB	:	Printed Circuit Board
RF	:	Radio Frequency
Rx	:	Receiver
SMA	:	Sub-Miniature Version A
Tx	:	Transmitter
μm	:	micro-meter

4 Reference

- [1] “Antenna Theory: Analysis and Design”, Third Edition, Constantine A. Balanis
- [2] “Microwave Engineering”, Fourth Edition, David M. Pozar

5 Revision History

Doc Rev.	Date	Comments
42289A	07/2014	Initial document release.



Atmel Corporation 1600 Technology Drive, San Jose, CA 95110 USA T: (+1)(408) 441.0311 F: (+1)(408) 436.4200 | www.atmel.com

© 2014 Atmel Corporation. / Rev.:Atmel-42289A-915MHz-Printed-Folded-Monopole-Antenna-Reference-Design_ApplicationNote_072014.

Atmel®, Atmel logo and combinations thereof, Enabling Unlimited Possibilities®, and others are registered trademarks or trademarks of Atmel Corporation in U.S. and other countries. Altium® is a registered trademark of Altium Limited. Other terms and product names may be trademarks of others.

DISCLAIMER: The information in this document is provided in connection with Atmel products. No license, express or implied, by estoppel or otherwise, to any intellectual property right is granted by this document or in connection with the sale of Atmel products. EXCEPT AS SET FORTH IN THE ATMEL TERMS AND CONDITIONS OF SALES LOCATED ON THE ATMEL WEBSITE, ATMEL ASSUMES NO LIABILITY WHATSOEVER AND DISCLAIMS ANY EXPRESS, IMPLIED OR STATUTORY WARRANTY RELATING TO ITS PRODUCTS INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTY OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT. IN NO EVENT SHALL ATMEL BE LIABLE FOR ANY DIRECT, INDIRECT, CONSEQUENTIAL, PUNITIVE, SPECIAL OR INCIDENTAL DAMAGES (INCLUDING, WITHOUT LIMITATION, DAMAGES FOR LOSS AND PROFITS, BUSINESS INTERRUPTION, OR LOSS OF INFORMATION) ARISING OUT OF THE USE OR INABILITY TO USE THIS DOCUMENT, EVEN IF ATMEL HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES. Atmel makes no representations or warranties with respect to the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and products descriptions at any time without notice. Atmel does not make any commitment to update the information contained herein. Unless specifically provided otherwise, Atmel products are not suitable for, and shall not be used in, automotive applications. Atmel products are not intended, authorized, or warranted for use as components in applications intended to support or sustain life.

SAFETY-CRITICAL, MILITARY, AND AUTOMOTIVE APPLICATIONS DISCLAIMER: Atmel products are not designed for and will not be used in connection with any applications where the failure of such products would reasonably be expected to result in significant personal injury or death ("Safety-Critical Applications") without an Atmel officer's specific written consent. Safety-Critical Applications include, without limitation, life support devices and systems, equipment or systems for the operation of nuclear facilities and weapons systems. Atmel products are not designed nor intended for use in military or aerospace applications or environments unless specifically designated by Atmel as military-grade. Atmel products are not designed nor intended for use in automotive applications unless specifically designated by Atmel as automotive-grade.