

OptoLyzer® MOCCA compact V3.1



ISBN: 978-1-62077-921-7

Copyright © 2013 - 2014 K2L GmbH & Co. KG ("K2L"). All rights reserved.

Please make sure that all information within a document marked as 'Confidential' or 'Restricted Access' is handled solely in accordance with the agreement pursuant to which it is provided, and is not reproduced or disclosed to others without the prior written consent of K2L. The confidential ranking of a document can be found in the footer of every page. This document supersedes and replaces all information previously supplied. The technical information in this document loses its validity with the next edition. Although the information is believed to be accurate, no responsibility is assumed for inaccuracies. Specifications and other documents mentioned in this document are subject to change without notice. K2L reserves the right to make changes to this document and to the products at any time without notice. Neither the provision of this information nor the sale of the described products conveys any licenses under any patent rights or other intellectual property rights of K2L or others. The products may contain design defects or errors known as anomalies, including but not necessarily limited to any which may be identified in this document, which may cause the product to deviate from published descriptions. Anomalies are described in errata sheets available upon request. K2L products are not designed, intended, authorized or warranted for use in any life support or other application where product failure could cause or contribute to personal injury or severe property damage. Any and all such uses without prior written approval of an officer of K2L will be fully at your own risk. The K2L logo is a trademark of K2L. Other names mentioned may be trademarks of their respective holders.

K2L disclaims and excludes any and all warranties, including without limitation any and all implied warranties of merchantability, fitness for a particular purpose, title, and against infringement and the like, and any and all warranties arising from any course of dealing or usage of trade. In no event shall K2L be liable for any direct, incidental, indirect, special, punitive, or consequential damages; or for lost data, profits, savings or revenues of any kind; regardless of the form of action, whether based on contract; tort; negligence of K2L or others; strict liability; breach of warranty; or otherwise; whether or not any remedy of buyer is held to have failed of its essential purpose, and whether or not K2L has been advised of the possibility of such damages.

Table of Contents

Chapter 1 Preface	6
1.1 Intended Use	6
1.2 Scope of Delivery	6
1.3 Definitions of Terms	7
1.4 References	8
Chapter 2 Safety Instructions	9
2.1 Supply and Synchronization	9
2.2 Relay	9
2.3 Restrictions in Operation	9
Chapter 3 Definitions Limit Class	10
3.1 Emission	10
Chapter 4 Introduction	11
4.1 Feature Summary	11
4.2 Block Diagram	12
4.3 Properties of Supported Bus Systems	12
4.3.1 CAN	12
4.3.1.1 High Speed Transceiver	12
4.3.1.2 Low Speed Transceiver	12
4.3.1.3 Single Wire Transceiver	13
4.3.2 FlexRay	13
4.3.3 LIN	13
4.3.4 MOST	14
4.3.4.1 MOST50	14
4.3.4.2 MOST150	14
4.3.4.3 SpyNIC for MOST	14
4.3.4.4 StressNIC for MOST	14
4.3.5 Ethernet	15
4.3.6 Sleep Mode	15
Chapter 5 Hardware Description	16
5.1 Front Panel	16
5.2 Rear Panel	20
Chapter 6 Pin Assignment of the Connectors	22
6.1 High Speed CAN	22
6.2 LIN / FlexRay	23
6.3 LIN / Low Speed CAN and Single Wire CAN 2 / 6	24
6.4 Synchronization and Power	24
6.5 Digital Audio In/Out (S/PDIF)	25
6.6 Analog Audio In/Out	25
6.7 USB	25
6.8 Relay	26
6.9 ECL	26
6.10 MOST Connector	27
6.10.1 MOST50 Electrical Connector	27

6.10.2 MOST150 Optical Connector	27
6.10.3 MOST150 Coaxial Connector	27
6.10.3.1 Simplex Use Case	28
6.10.3.2 Duplex Use Case.....	28
6.10.3.3 Duplex Endpoint Use Case	29
<hr/>	
Chapter 7 Technical Specifications	30
<hr/>	
Chapter 8 Maintenance	32
<hr/>	
Chapter 9 Revision History	33

List of Figures

Figure 4.1	Block Diagram	12
Figure 4.2	Order of Chips inside the OptoLyzer MOCCA compact.	14
Figure 5.1	Front Panel (MOST150 oPHY and MOST150 cPHY Variant)	16
Figure 5.2	Rear Panel (Variant with S/PDIF Interfaces)	20
Figure 6.1	DE-9 Connector	22
Figure 6.2	Pin Assignment of the Sync and Power Connector	24
Figure 6.3	Pin Assignment of the S/PDIF Connector	25
Figure 6.4	Pin Assignment of the Analog Audio In/Out Connector	25
Figure 6.5	PIN Assignment of the MOST50 Connector	27
Figure 6.6	Simplex Use Case	28
Figure 6.7	Duplex Use Case	28
Figure 6.8	Duplex Endpoint Use Case	29
Figure 8.1	How To Release cPHY Connector.	32

List of Tables

Table 1.1	Definitions of Terms	7
Table 5.1	Connectors on the Front Panel	17
Table 5.2	LEDs	19
Table 5.3	Connectors on the Rear Panel	20
Table 6.1	Pin Assignment of Connector High Speed CAN 1/3/5	22
Table 6.2	Pin Assignment of Connector High Speed CAN 2/4/6	23
Table 6.3	Pin Assignment of Connector LIN / FlexRay A/B	23
Table 6.4	Pin Assignment of Connector LIN / Low Speed CAN	24
Table 6.5	Pinning of the Sync and Power Connector	24
Table 6.6	Pin Assignment of the Relay Connector	26
Table 6.7	Technical Values	26
Table 6.8	Pin Assignment of the MOST50 Connector	27
Table 7.1	Device and Bus Characteristics	30
Table 7.2	Mechanical Characteristics	30
Table 7.3	Electrical Characteristics	31
Table 9.1	Customer Revision History	33

Chapter 1 Preface

1.1 Intended Use

The OptoLyzer MOCCA compact is intended to be used for developing, testing, or analyzing CAN[®], FlexRay[™], LIN[®], or MOST[®] based automotive products and systems by persons with experience in developing automotive devices.

1.2 Scope of Delivery

The OptoLyzer MOCCA compact is the hardware part of the following K2L products (e.g.):

- ATS
- OptoLyzer MOCCA compact Bundle
(including OptoLyzer Suite support for MOST50 and MOST150)

The delivery covers the following:

- OptoLyzer MOCCA compact
- Power cable
- MOST cable (optional)
- USB cable
- USB stick (license dongle)
- CAN termination resistors (optional)
- Sync and power cable (optional)
- Adaptation Kit (optional)

Check your shipment for completeness. If you have any complaints direct them to sales@K2L.com. Providing the delivery note number eases the handling.

1.3 Definitions of Terms

For better understanding of the following chapters, this section provides explanation to special terms, used in the description of the OptoLyzer MOCCA compact user manual.

Table 1.1 Definitions of Terms

TERM / ABBREVIATION	DESCRIPTION
ATS	Automotive Test System
CAN	Controller Area Network
cPHY	Coaxial electrical physical layer; used e.g., in OptoLyzer MOCCA compact 150c variant
D	Depth
DUT	Device Under Test
ECL	Electrical Control Line, a method to wake up ECUs in MOST networks.
ECU	Electronic Control Unit
ePHY	Electrical physical layer; used e.g., in OptoLyzer MOCCA compact 50e variant
FlexRay	Automotive network communications bus system
H	Height
LIN	Local Interconnect Network
Low speed CAN Transceiver	Fault tolerant CAN Transceiver
MDIX	Medium Dependent Interface Crossover
MediaLB [®]	Media Local Bus
MOST [®]	Media Oriented Systems Transport
oPHY	Optical physical layer; used e.g., in OptoLyzer MOCCA compact 150o variant
RCA	Type of electrical connector used for transmitting audio and video signals (also known as cinch, introduced from Radio Corporation of America).
Sync	Synchronization
S/PDIF	Sony/Philips Digital Interconnect Format
USB	Universal Serial Bus
W	Width

1.4 References

- [1] Electrical Physical Layer Specification Version 2.0
Refer to FlexRay Consortium.
- [2] International Organization for Standardization
<http://www.iso.org>
- [3] Telecommunications Industry Association
<http://www.tiaonline.org>
- [4] International Electrotechnical Commission
<http://www.iec.ch>

Chapter 2 Safety Instructions

2.1 Supply and Synchronization

The OptoLyzer MOCCA compact devices could be cascaded via Sync/Power connector. One of the two Sync/Power connectors is intended to be used for the power supply and the other for cascading the OptoLyzer MOCCA compact by using an optional sync cable.

During cascading, caution has to be taken, since the first device in the chain can take the maximum current of 3 A. Do not cascade more than eight devices in chain.

For all setups either a fuse of max. 4 A in the supply cable to the first device or the use of the current limitation of the laboratory power supply is mandatory.

2.2 Relay

The Relay feature of the device is designed to switch other 12 V powered devices. The capability is limited to 5 A at 16 V maximum. Always use core cable ends of appropriate length and diameter to prevent unintended connections.

2.3 Restrictions in Operation

The OptoLyzer MOCCA compact integrates temperature sensitive components. Therefore do not cover the device with any objects. Covering disables the passive cooling. Make sure to allow enough airflow to the OptoLyzer MOCCA compact, when the device is assembled. Do never place the running OptoLyzer MOCCA compact in a closed case or box. Do not stack any OptoLyzer MOCCA compact devices.

Chapter 3 Definitions Limit Class

3.1 Emission

The OptoLyzer MOCCA compact has passed the requirements according to the standard EN 55022:2010, class A.

Warning

The OptoLyzer MOCCA compact is a class A product. In a domestic environment this product may cause radio interference in which case the user may be required to take adequate measures.

Chapter 4 Introduction

The OptoLyzer MOCCA compact is an out of the box automotive bus interface, combining most of the current automotive field buses. The device can be used e.g., as an automotive bus interface featuring simulation via PC or as an analyzing device for the different automotive bus systems.

Due to its PC compatible connections including USB 2.0 and 10/100 Mbit/s Ethernet, it is easily possible to control the embedded OptoLyzer MOCCA compact software from the PC including monitoring, tracing, and logging of data exchange over the different field bus systems. The OptoLyzer MOCCA compact provides comfortable spy and stress functionalities for MOST.

The OptoLyzer MOCCA compact is available as different hardware variants optimized for dedicated use cases (e.g., with or without MOST connector (oPHY, ePHY, and cPHY variants), different MOST speed grades).

4.1 Feature Summary

The following list covers the key features of the hardware platform. Some of the options may not be available in specific configurations.

- 6 high speed CAN interfaces, two of them selectable either as high- or low-speed transceiver or single wire CAN
- 1 FlexRay connector
- 6 LIN interfaces
- MOST150 (cPHY or oPHY), MOST50 (ePHY) or without MOST
- USB 2.0 port supporting high speed with 480 Mbit/s and full speed with 12 Mbit/s
- Ethernet connection with 10/100 Mbit/s
- S/PDIF coaxial input and output for audio streaming over MOST
- Analog audio input and output for audio streaming over MOST
- MOST ECL support or generic trigger in-/output
- Relay to switch external loads of up to 5 A
- Time stamp synchronization with cascaded OptoLyzer MOCCA compact devices over power cables.
- SpyNIC for MOST on-board
- StressNIC for MOST on-board
- Simplex, duplex and duplex endpoint use case support in cPHY variant of MOST150.

4.2 Block Diagram

A block diagram shows the features available for the OptoLyzer MOCCA compact V3.1. In order to minimize crossing lines in Figure 4.1 below the FPGA was split into two blocks.




Figure 4.1 Block Diagram

4.3 Properties of Supported Bus Systems

The OptoLyzer MOCCA compact is intended to be used as stimulation, test and analysis device for automotive field buses with DUTs connected to them. Therefore the design is constrained to ensure the behavior to be as passive as possible.

4.3.1 CAN

The accuracy of CAN time stamps is 500 µs.

4.3.1.1 High Speed Transceiver

High speed CAN bus systems according to ISO 11898-2 [2] are terminated with 120 Ω at each end. Therefore the OptoLyzer MOCCA compact does not terminate the bus. The transmission speed ranges from 33 kbits/s to 1 Mbits/s.

4.3.1.2 Low Speed Transceiver

Low speed CAN bus systems usually have a distributed termination. The value of the termination in each node depends on the number of nodes in the network. To avoid effects on the total impedance of the network the OptoLyzer MOCCA compact has a weak termination of 5.6 kΩ. A communication via the low speed transceivers ranges up to a speed of 125 kbits/s.

4.3.1.3 Single Wire Transceiver

The single wire CAN is terminated with 9.1 k Ω . The transmission speeds for single wire CAN are 33 kbits/s (on-board communication) and 83 kbits/s (off-board communication).

4.3.2 FlexRay

The termination of a FlexRay bus depends on the bus topology. Two terminations are mandatory in each active branch. The OptoLyzer MOCCA compact can be installed in various topologies. Therefore a termination is not implemented in the device. Thus the terminations have to be realized in a different way. In addition, the OptoLyzer MOCCA compact does not act as a bus guardian.

The OptoLyzer MOCCA compact provides one FlexRay interface and is able to switch from sleep mode to wake-up mode stimulated by the FlexRay bus. The bus is capable of transmitting up to 10 Mbit/s (brutto) as per "Electrical Physical Layer Specification Version 2.0". The accuracy of FlexRay time stamps is 500 μ s for the static part of the schedule.

4.3.3 LIN

Both LIN master and LIN slave functionality are supported. The accuracy of LIN time stamps is 1 μ s. The OptoLyzer MOCCA compact supports a maximum transmission speed of 20 kbit/s (brutto).

4.3.4 MOST

The OptoLyzer MOCCA compact variant supporting MOST50 is able to switch the clock mode of the embedded OS81082 INIC and thus supports a 44.1 kHz as well as a 48 kHz network whereas the OptoLyzer MOCCA compact variant designed for a MOST150 network has a fixed clock mode of 48 kHz. OptoLyzer MOCCA compact variants of any speed grade have an INIC, a SpyNIC for MOST and a StressNIC for MOST on-board. The StressNIC for MOST can be connected if desired via software. The accuracy of INIC MOST time stamps is 500 μ s.

When analyzing data e.g., when interpreting an acknowledged code, it is important to know how the chips (INIC, SpyNIC for MOST, StressNIC for MOST) are arranged inside the OptoLyzer MOCCA compact.




Figure 4.2 Order of Chips inside the OptoLyzer MOCCA compact

The MOST feature is optional for OptoLyzer MOCCA compact variants i.e., there are OptoLyzer MOCCA compact variants supporting MOST (MOST50 or MOST150) or variants without MOST.¹

4.3.4.1 MOST50

Data exchange between the OptoLyzer MOCCA compact and the embedded OS81082 INIC is realized by MediaLB 3-Pin with 512Fs.

4.3.4.2 MOST150

Data exchange between the OptoLyzer MOCCA compact and the embedded OS81110 INIC is realized by MediaLB 6-Pin with 2048Fs.

4.3.4.3 SpyNIC for MOST

Each speed grade of an OptoLyzer MOCCA compact has also an appropriate SpyNIC for MOST on-board. Both speed grade variants of the SpyNIC are spying control, packet, and allocation messages. A node is realized at the same time. The accuracy of SpyNIC time stamps is 1 μ s.

4.3.4.4 StressNIC for MOST

Each speed grade of an OptoLyzer MOCCA compact has also an appropriate StressNIC for MOST on-board. Both speed grade variants of the StressNIC are supporting dedicated use cases for simulating some common network error situations (e.g., light (activity)²/lock stress, buffer full

1. An optical MOST25 interface is provided by the former hardware version MOCCA compact V2.3.

2. Light relates to the OptoLyzer MOCCA 150o variant, activity relates to the OptoLyzer MOCCA 50e and OptoLyzer MOCCA 150c variants.

simulation, etc.). By default the StressNIC for MOST is electrically bypassed but can be enabled by appropriate software (e.g., ATS) (see [Figure 4.2 on page 14](#)).

4.3.5 Ethernet

Auto MDIX is supported, therefore the LAN interface can connect via straight and crossed patch cables. The physical layer 100BASE-TX is supported. Thereby the MAC address of the Ethernet controller has a unique address. The accuracy of Ethernet time stamps is 500 μ s.

4.3.6 Sleep Mode

The OptoLyzer MOCCA compact is able to scan the six CAN buses in sleep mode and if stimulated to switch from sleep mode into wake-up mode. In addition, the OptoLyzer MOCCA compact can be waked-up via FlexRay, LIN or ECL. For controlling the sleep mode software is needed to be developed by the customer.

Chapter 5 Hardware Description

5.1 Front Panel

Different hardware variants are available for the OptoLyzer MOCCA compact. [Figure 5.1](#) depicts a variant supporting the MOST150 oPHY variant (top) and the MOST150 cPHY variant (bottom).




Figure 5.1 Front Panel (MOST150 oPHY and MOST150 cPHY Variant)

All components of the front panel are described below:

- [Table 5.1](#) describes the connectors from left to right and top to down.
- [Table 5.2](#) describes the LEDs.

Table 5.1 Connectors on the Front Panel














INTERFACE	SYMBOL	DESCRIPTION
Analog Audio Out		<p>These interfaces are only available on variants that are supporting MOST. The OptoLyzer MOCCA compact provides one stereo headphone output. It has a 3.5 mm jack plug. Output Power: $P_{o, Max, Rms} = 1.4 \text{ mW}$ (at $R = 16 \Omega$, $V_{out} = 150 \text{ mV}_{RMS}$)</p>
ECL or Trigger	 	<p>OptoLyzer MOCCA compact variants supporting MOST:</p> <ul style="list-style-type: none"> ECL can be used to wake-up the OptoLyzer MOCCA compact according to different ECL implementations. <p>OptoLyzer MOCCA compact variants without MOST:</p> <ul style="list-style-type: none"> The trigger can be used to wake-up the OptoLyzer MOCCA compact. <p>Both trigger variants are realized using a LIN transceiver. For the pin out refer to Section 6.9, "ECL," on page 26.</p>
MOST (ePHY variant oPHY variant cPHY variant)	 	<p>These interfaces are only available on variants that are supporting MOST^a. The MOST50 connector bases on an electrical physical layer (ePHY) whereas the MOST150 connectors base either on an optical physical layer (oPHY) or a coaxial electrical physical layer (cPHY) described separately below. For the pin out refer to Section 6.10, "MOST Connector," on page 27.</p>
MOST (cPHY variant Rx connector)		<p>The icon refers to the bottom part in Figure 5.1. This interface is only available on variants that are supporting the coaxial variant of MOST. The MOST150c connectors base on a coaxial electrical physical layer (cPHY). This connector provides an Rx interface. It is used</p> <ul style="list-style-type: none"> in simplex use cases as Rx (indicated by the single-headed arrow). <p>For more details refer to Section 6.10, "MOST Connector," on page 27.</p>
MOST (cPHY variant Rx/Tx connector)		<p>The icon refers to the bottom part in Figure 5.1. This interface is only available on variants that are supporting the coaxial variant of MOST. The MOST150c connectors base on a coaxial electrical physical layer (cPHY). This connector provides a duplex interface (Rx/Tx connection). It is used</p> <ul style="list-style-type: none"> in duplex use cases as Rx/Tx (indicated by the double-headed arrow). <p>For more details refer to Section 6.10, "MOST Connector," on page 27.</p>
MOST (cPHY variant Tx and Rx/Tx connector)		<p>The icon refers to the bottom part in Figure 5.1. This interface is only available on variants that are supporting the coaxial variant of MOST. The MOST150c connectors base on a coaxial electrical physical layer (cPHY). This connector provides a Tx or a duplex interface (Rx/Tx connection). It is used</p> <ul style="list-style-type: none"> in simplex use cases as Tx (indicated by the single-headed arrow) and in duplex use cases as Rx/Tx (indicated by the double-headed arrow) and in duplex endpoint use cases (indicated by the double-headed arrow). <p>For more details refer to Section 6.10, "MOST Connector," on page 27.</p>

Table 5.1 Connectors on the Front Panel

INTERFACE	SYMBOL	DESCRIPTION
Program Reset		<p>The device can be reset by the push button. If the button is pressed for less than 1 s, the device is reset. The same button is used for switching into the flashing mode if it is pressed for more than 2 seconds. For details see the “K2L Flasher Online Help” that is part of the shipment.</p>
Analog Line IN		<p>These interfaces are only available on variants that are supporting MOST. The OptoLyzer MOCCA compact provides one analog audio Line IN. The analog Line IN input impedance is 10 kΩ. The analog input is converted into a digital stream with resolutions of 8, 16 or 24 bits / channel, both mono or stereo. It has a 3.5 mm jack plug.</p>
Relay		<p>The relay is able to switch 5 A as a potential free shutter. For safety purposes refer to Chapter 2, "Safety Instructions," on page 9. For the pin out refer to Section 6.8, "Relay," on page 26.</p>
USB		<p>The USB port is a standard USB B-type receptacle.</p>
LAN		<p>The LAN connector is an RJ45 receptacle according to TIA-568 [3].</p>

a.Each OptoLyzer MOCCA compact has either one MOST150 oPHY, three MOST150 cPHY or one MOST50 ePHY connector.

The OptoLyzer MOCCA compact offers up to seven LEDs. All LEDs except the Power LED are tri-colors.

Table 5.2 LEDs

INTERFACE	SYMBOL	DESCRIPTION	COLOR	DESCRIPTION
Active	Active	This LED indicates any activity.	Red	Reserved
			Green	Reserved
			Blue (Twinkling)	Slowly: Firmware running Fast: Flash mode
Operation	Op.	This LED indicates different states dependent on the installed firmware (e.g., for ATS etc.).	Red	Depending on firmware
			Green	Depending on firmware
			Blue	Depending on firmware
CAN	CAN	This LED indicates the bus state of the CAN bus.	Red	Error
			Green	Operational
			White (Twinkling)	Bus activity
MOST	MOST	This LED indicates the bus state of the MOST network. The LED is only available for variants that are supporting MOST.	Red	Error
			Green	Net on
			White (Twinkling)	Bus activity
FlexRay	FR	This LED indicates the bus state of the FlexRay bus.	Red	Error
			Green	Synced
			White (Twinkling)	Bus activity
LIN	LIN	This LED indicates the bus state of the LIN bus.	Red	Error
			Green	Operational
			White (Twinkling)	Bus activity
Power	PWR	This LED indicates a powered device.	Green	Powered device

5.2 Rear Panel

Different hardware variants and software configurations are available for the OptoLyzer MOCCA compact. As a result some connectors might not be available for a specific variant of the OptoLyzer MOCCA compact.



Figure 5.2 Rear Panel (Variant with S/PDIF Interfaces)

All components of the rear panel are described below. [Table 5.3](#) describes the connectors from top to bottom and left to right.

Table 5.3 Connectors on the Rear Panel

INTERFACE	DESCRIPTION
High Speed CAN 1/3/5 2/4/6	These two connectors offer six high speed CAN instances with baud rates from 40 kbit/s to 1 Mbit/s depending on the cable length. The CAN instances 1, 3, 4 and 5 are hard specified as high speed CAN interfaces whereas the CAN instances 2 and 6 can also be used as low speed or as single wire CAN interfaces. The CAN interfaces can be controlled by a customer application. Details about the CAN bus properties are described in Section 4.3.1, "CAN," on page 12 . For the pin out refer to Section 6.1, "High Speed CAN," on page 22 .
LIN / FlexRay	This DE-9 socket combines pins assigned to the FlexRay bus and pins assigned to the LIN channels 3, 4, 5 and 6. For the pin out refer to Section 6.2, "LIN / FlexRay," on page 23 .
LIN / Low Speed CAN Single Wire CAN 2 / 6	This DE-9 socket combines two low speed and two single wire CAN interfaces (CAN instances 2 and 6) as well as two LIN channels (1 and 2). These CAN instances can be used either as high speed CAN interfaces or as low speed CAN interfaces or as single wire CAN interfaces. These CAN interfaces can be controlled by a customer application. For the pin out refer to Section 6.3, "LIN / Low Speed CAN and Single Wire CAN 2 / 6," on page 24 .
Sync / Power	The Synchronization (Sync) and the Power connector have the identical pin assignment i.e., each socket can be used either for synchronization or power purposes. Restrictions are described in Section Chapter 2, "Safety Instructions," on page 9 . The OptoLyzer MOCCA compact is intended to be powered by the (optional available) wall power supply or by any other power supply which is capable to deliver 12 V and 1 A. If the wall power supply is not used, the included power cable has to be used to connect the 12 V supply to the OptoLyzer MOCCA compact. For the pin out refer to Section 6.4, "Synchronization and Power," on page 24 .

Table 5.3 Connectors on the Rear Panel

INTERFACE	DESCRIPTION		
S/PDIF IN / OUT	<p>These interfaces are only available on variants that are supporting MOST. The output is compliant to the specification IEC 60958 [4] with 75 Ω and 0.5 Vpp (+ / -20%). The output is short circuit proof. The input circuit expects an unbalanced input and has an impedance of 75 Ω. Input sample rates from 32 to 96 kHz are accepted. For the pin out refer to Section 6.5, "Digital Audio In/Out (S/PDIF)," on page 25. The OptoLyzer MOCCA compact offers the bidirectional transfer of audio streams between the MOST synchronous channel and the S/PDIF connectors. An audio stream on a MOST synchronous channel can be routed to the S/PDIF output of the device. It is also possible to route a digital audio stream from S/PDIF input of the device to the MOST synchronous channel at the same time. The following tables describe which S/PDIF formats are supported by the OptoLyzer MOCCA compact.</p>		
	<p>Direction S/PDIF (IN) to MOST: S/PDIF data from an external S/PDIF source routed to the MOST network. The S/PDIF (IN) is routed through a sample rate converter. The signal can be either a mono or stereo signal.</p>		
	IN	MOST	Supported Framerates
	8 bit / channel	8 bit / channel	32 - 96 kHz
	16 bit / channel	16 bit / channel	
	24 bit / channel	24 bit / channel	
	<p>Direction MOST to S/PDIF (OUT): S/PDIF data from the MOST network routed to an external S/PDIF sink. The signal can be either a mono or stereo signal.</p>		
MOST	OUT	Supported Framerates	
8 bit / channel	8 bit / channel	32 - 96 kHz	
16 bit / channel	16 bit / channel		
24 bit / channel	24 bit / channel		

Chapter 6 Pin Assignment of the Connectors

6.1 High Speed CAN

Connector type for both High Speed CAN connectors: DE-9

Figure 6.1 shows the connector pin assignment as it is visible on the rear panel.




Figure 6.1 DE-9 Connector

The provided GND pins must not be used unless there is no other GND connection. These pins must not be used for supply purpose.

Table 6.1 Pin Assignment of Connector High Speed CAN 1/3/5

PIN NO.	SIGNAL	DESCRIPTION
1	CAN5-Low	Low-level CAN bus line
2	CAN1-Low	Low-level CAN bus line
3	GND	Signal ground
4	CAN3-Low	Low-level CAN bus line
5		Not connected
6		Not connected
7	CAN1-High	High-level CAN bus line
8	CAN5-High	High-level CAN bus line
9	CAN3-High	High-level CAN bus line

The provided GND pins must not be used unless there is no other GND connection. These pins must not be used for supply purpose.

Table 6.2 Pin Assignment of Connector High Speed CAN 2/4/6

PIN NO.	SIGNAL	DESCRIPTION
1	CAN6-Low	Low-level CAN bus line
2	CAN2-Low	Low-level CAN bus line
3	GND	Signal ground
4	CAN4-Low	Low-level CAN bus line
5		Not connected
6		Not connected
7	CAN2-High	High-level CAN bus line
8	CAN6-High	High-level CAN bus line
9	CAN4-High	High-level CAN bus line

6.2 LIN / FlexRay

Connector type (see [Figure 6.1](#)): DE-9

The provided GND pin must not be used unless there is no other GND connection. This pin must not be used for supply purpose.

Table 6.3 Pin Assignment of Connector LIN / FlexRay A/B

PIN NO.	SIGNAL	DESCRIPTION
1	LIN3	3 rd LIN channel
2	Channel B BP	Positive bus line
3	GND	Signal ground
4	Channel A BM	Negative bus line
5	LIN4	4 th LIN channel
6	LIN5	5 th LIN channel
7	Channel B BM	Negative bus line
8	Channel A BP	Positive bus line
9	LIN6	6 th LIN channel

6.3 LIN / Low Speed CAN and Single Wire CAN 2 / 6

Connector type (see [Figure 6.1](#)): DE-9

The provided GND pin must not be used unless there is no other GND connection. This pin must not be used for supply purpose.

Table 6.4 Pin Assignment of Connector LIN / Low Speed CAN

PIN NO.	SIGNAL	DESCRIPTION
1	CAN2-SW	High-level CAN2 bus line (single wire)
2	CAN2-Low	Low-level CAN2 bus line (low speed)
3	GND	Signal ground
4	CAN6-Low	Low-level CAN6 bus line (low speed)
5	LIN1	1 st LIN channel
6	LIN2	2 nd LIN channel
7	CAN2-High	High-level CAN2 bus line (low speed)
8	CAN6-SW	High-level CAN6 bus line (single wire)
9	CAN6-High	High-level CAN6 bus line (low speed)

6.4 Synchronization and Power

There are two connectors for synchronization and power. [Figure 6.2](#) shows the pin assignment as it is visible on the rear panel for these connectors. For more details about synchronization and power refer to [Section 2.1, "Supply and Synchronization,"](#) on page 9.




Figure 6.2 Pin Assignment of the Sync and Power Connector

Table 6.5 Pinning of the Sync and Power Connector

PIN NO.	SIGNAL	DESCRIPTION
1	12 V	Power supply
2	Sync	Synchronization line
3	GND	System ground

6.5 Digital Audio In/Out (S/PDIF)

Both digital connectors (S/PDIF In/Out) interface to a RCA phono socket.




Figure 6.3 Pin Assignment of the S/PDIF Connector

The input circuit expects an unbalanced input and has an impedance of 75 Ω . The shield connects to system ground.

6.6 Analog Audio In/Out

Both the stereo line-in and the stereo headphone output interface to an audio phone connector.




Figure 6.4 Pin Assignment of the Analog Audio In/Out Connector

6.7 USB

The USB port is a standard USB B-type receptacle.

6.8 Relay

The relay is able to switch 5 A as a potential free shutter. Please refer also to [Chapter 2, "Safety Instructions,"](#) on page 9.

Relay type:

- assembled connector type: RIA 31182102
- connector type to be plugged: RIA 31169102

The pin assignment below is described as it is visible on the front panel.

Table 6.6 Pin Assignment of the Relay Connector

PIN NUMBER	DESCRIPTION
1 (left pin)	Shutter input
2 (right pin)	Shutter output

6.9 ECL

This connector provides two pins: The upper pin is for connecting the ECL/Trigger signal, the lower pin for connecting GND.

Connector type:

- assembled connector type: Molex 43045-0201
- connector type to be plugged: Molex 43025-0200

Table 6.7 Technical Values

PARAMETER	VALUE
Frequency	0..20 kHz
V_{Out}	7..18 V
R_{out}	20..60 k Ω
$V_{In, Low, Max}$	0.4 V_{Bat}
$V_{I, High, Min}$	0.6 V_{Bat}
V_{In} Hysteresis	0.05 V_{Bat}

6.10 MOST Connector

6.10.1 MOST50 Electrical Connector

Connector type: AMP 1376350-1

Figure 6.5 shows the pin assignment as it is visible on the front panel.




Figure 6.5 PIN Assignment of the MOST50 Connector

Table 6.8 Pin Assignment of the MOST50 Connector

PIN NUMBER	DESCRIPTION
1, 4, 5, 8	Not connected
2	ETXP
3	ETXN
6	ERXN
7	ERXP

6.10.2 MOST150 Optical Connector

Connector type: Tyco Micro FOT (2+0).

The orientation of the Rx and Tx path is printed on the panel.

The MOST150 connector is designated for a 2+0 optical header cable. The direction is visible on the cable:

- Tx: Optical output for MOST network
- Rx: Optical input for MOST network

6.10.3 MOST150 Coaxial Connector

Connector type: 59S20X-40ML5-Z FAKRA

Three different use cases are supported. They are shown together with the appropriate connection diagrams in the following sections. Each use case presents logically a ring, even if the devices are physically connected by one cable (e.g., duplex endpoint use case). For more details about the coaxial interfaces refer to [Table 5.1 on page 17](#).

6.10.3.1 Simplex Use Case




Figure 6.6 Simplex Use Case

In this use case the OptoLyzer MOCCA compact 150c observes and participates in a simplex ring. Data is transmitted in one direction. Thereby the single-headed arrow shows the direction. The OptoLyzer MOCCA compact 150c can appear as an extra node in the ring.

6.10.3.2 Duplex Use Case




Figure 6.7 Duplex Use Case

In this use case the OptoLyzer MOCCA compact 150c observes and participates in a duplex ring e.g., between a head unit and a camera. Data is transmitted in both directions indicated by double-headed arrows. The OptoLyzer MOCCA compact 150c can appear as an extra node in the ring.

6.10.3.3 Duplex Endpoint Use Case




Figure 6.8 Duplex Endpoint Use Case

In this use case the OptoLyzer MOCCA compact 150c observes and participates at one end in a duplex ring e.g., is acting either as a head unit or a camera. Data is transmitted in both directions indicated by a double-headed arrow. The OptoLyzer MOCCA compact 150c can appear as an extra node in the ring.

Chapter 7 Technical Specifications

The table below covers characteristics of the OptoLyzer MOCCA compact and its bus interfaces.

Table 7.1 Device and Bus Characteristics

PARAMETER		VALUE
RAM		512 kB external / 240 kB internal
Flash Memory		2 MB internal
Controllers		
µController		Renesas V850E2/FL4-H@160 MHz
CAN Transceivers		
	Low Speed CAN Transceiver	NXP TJA 1055
	High Speed CAN Transceiver	NXP TJA 1041
	Single wire CAN Transceiver	On Semiconductor® NCV7356
FlexRay Transceiver		NXP TJA 1080
LAN Transceiver		Microchip LAN89218
LIN Transceiver		SN65HVDA195
MOST Controllers		
	MOST25 (optical)	Microchip OS81050
	MOST50 (electrical)	Microchip OS81082
	MOST150 (optical/coaxial)	Microchip OS81110
S/PDIF		I/O electrical via 2 x cinch, input sample rate 32 - 96 kHz
USB		Cypress EZ-USB 2.0

The table below covers mechanical characteristics of the OptoLyzer MOCCA compact.

Table 7.2 Mechanical Characteristics

PARAMETER	VALUE	UNIT
Dimensions (H x W x D)	45 x 112 x 116	mm
Weight	360	g
Ambient Temperature Range	-40..+70	°C

The table below covers electrical characteristics of the OptoLyzer MOCCA compact.

Table 7.3 Electrical Characteristics

PARAMETER	MIN	TYP	MAX	UNIT	COMMENT
Operating Voltage Range	7		16	V	
Current Consumption (operation)		500		mA	
Current Consumption (sleep)		< 1		mA	
Relay for external load (potential free shutter)			5	A	@ 12 V DC

Chapter 8 Maintenance

Figure 8.1 shows how a cPHY connector of the OptoLyzer MOCCA compact 150c can be released or exchanged.




Figure 8.1 How To Release cPHY Connector

Follow these steps:

1. Depress the locking tab of the snap-on coupling.
2. Pull the jack away from the device while still pressing the locking tab.

Chapter 9 Revision History

Table 9.1 Customer Revision History

REVISION LEVEL	SECTION/FIGURE/ ENTRY	CORRECTION
DS60001258B	Section 4.2, "Block Diagram," on page 12	Figure 4.1: LIN Transceiver corrected: SN65HVDA195
DS60001258A	All	New: OptoLyzer compact 150c variant. DS number replaces version number. ISBN number inserted (cover page). General improvement of wording.
	Section 1.3, "Definitions of Terms," on page 7	New terms added: cPHY, ePHY and oPHY
	Section 2.3, "Restrictions in Operation," on page 9	New section
	Section 4.1, "Feature Summary," on page 11	MOST feature adapted, new feature added: support of simplex, duplex and duplex endpoint use cases
	Section 4.2, "Block Diagram," on page 12	cPHY added for MOST connector
	Section 4.3.4, "MOST," on page 14	Description improved (StressNIC for MOST can be connected optionally), Figure 4.2 modified.
	Section 4.3.4.1, "MOST50," on page 14	Currently 512Fs are used (1024Fs removed).
	Section 4.3.4.4, "StressNIC for MOST," on page 14	Description improved: light/lock stress -> light (activity)/lock stress
	Section 4.3.5, "Ethernet," on page 15	Description improved (relating to MAC address).
	Section 4.3.6, "Sleep Mode," on page 15	Description improved (hint added that software is needed to control sleep mode).
	Section 5.1, "Front Panel," on page 16	Figure 5.1: cPHY variant of MOST150 added. Table 5.1: new cPHY interfaces added. Description of "Program Reset" button extended. Table 5.2: power icon replaced by 'Pwr.'
	Section 6.10.3, "MOST150 Coaxial Connector," on page 27	New section
	Chapter 7, "Technical Specifications," on page 30	Low Speed CAN Transceiver changed from NXP TJA 1054 to NXP TJA 1055
Chapter 8, "Maintenance," on page 32	New chapter	
Rev. 1.0 (04-29-13)	Initial Version	

Further Information

For more information on K2L automotive products, including integrated circuits, software, and MOST® development tools and modules, visit our web site: <http://www.K2L.de>. Direct contact information is available at: <http://www.K2L.de/contact>.

K2L GmbH & Co. KG
Bannwaldallee 48
D-76185 Karlsruhe
Germany

Technical Support

Contact information for technical support is available at: <http://www.K2L.de/contact>.