

# OptoLyzer® Studio


The Universal Multi-Bus User Interface Software



The development cycle of automotive distributed devices and systems is complex and time consuming. The more important is it to have a tool at hand that makes this work easier. K2L's OptoLyzer Studio is a software that supports you in device-and system development and helps shorten time-to-market. It offers you a comprehensive and easy-to-use tool chain that supports you in conducting all development tasks starting from early test- and simulation phases up to and including final analysis and verification. Over all leading-edge automotive networks, OptoLyzer Studio is the solution to make your projects successful.

#### **Product Benefits**

- State of the art GUI based on .NET technology
- Support of many popular automotive networking technologies
- Extensive catalog and trace file support
- Security functionality
- · Device- and system simulation
- Comprehensive hardware interface support



# Ordering Information

Entry Edition:

■ OptoLyzer Studio Entry Order No. B10443

Foundation Edition:

- OptoLyzer Studio Foundation CL Order No. B10444
- OptoLyzer Studio Foundation

Order No. B10445

OptoLyzer Studio Foundation LAN

Order No. B10469

OptoLyzer Studio Foundation compact

Order No. B10446

Runtime Edition:

OptoLyzer Studio Runtime
Order No. B10470

Professional Edition:

OptoLyzer Studio Professional compact

Order No. B10471



## **OptoLyzer Studio Graphical User Interface**


The GUI design is based on an intuitive ribbon concept that facilitates easy access to the available functions of the OptoLyzer Studio. Dockable windows add clarity and tidiness; steep learning curves are a thing of the past. The Trace View including the Graph View, the Activity View, the Filter View, the Hex and Bit Dump, the Disassembly View, the Tiles View as well as the Analysis Framework View are the centerpieces of OptoLyzer Studio.

#### **Bus System Support**

OptoLyzer Studio supports a wide variety of automotive bus systems, including Ethernet/Internet, CAN, CAN FD, LIN, FlexRay®, MOST® as well as INICnet<sup>™</sup> technology based networks. In addition to protocol decoding capabilities, several technology-specific features are available: LDF editor for LIN, CAN replay functionality as well as DBC viewer and UDP/TCP send/receive, just to mention a few.

### Catalog Formats

The picture below shows the Catalog import dialogue with supported formats.



#### **Trace File Formats**

To give you the best flexibility for importing and exporting files from/to other software tools, OptoLyzer Studio supports OLSLOG, PCAP/ PCAPNG, ASC, BLF and other trace file formats.

#### Security

With authentication messages send/receive and freshness value as well as MAC analysis, OptoLyzer Studio offers the functionality needed to examine authentication measures in security-hardened CAN networks.

# **Supported Hardware Devices**

- OptoLyzer MOCCA Family
- Espresso T1S™ Device
- Network Adapter (via Win10Pcap)
- Kvaser Leaf Light/Pro HS V2
- CAN Bus Analyzer and LIN Serial Analyzer from Microchip
- Protocol Analyzers: Totalphase Beagle™ USB 480 and Totalphase Beagle I<sup>2</sup>C/SPI





K2L is committed to working toward a sustainable environment. We endeavor to make continual improvements in natural resource conservation through efficient product design and global operations thereby reducing greenhouse gas emissions generated by our products and facilities. Our environmental life cycle process seeks to reduce our carbon footprint through product life and recyclability and efficient use of materials, energy and transportation. We remain committed to promoting smart energy policies across our global organization.

Although the information in this document has been checked and is believed to be accurate, no responsibility is assumed for inaccuracies. K2L reserves the right to make changes to product descriptions and specifications at any time without notice. Contact your local K2L sales office to obtain the latest product descriptions and specifications before placing your product order. The provision of this information does not convey any licenses under any patent rights or other intellectual property rights of K2L or others. All sales are expressly conditional on your agreement to the terms and conditions of the most recently dated version of K2L's standard Terms of Sale Agreement dated before the date of your order. Products may contain design defects or errors which may cause a product's functions to deviate from published product specifications. Errata, listing these design defects or errors are available

upon request. K2L products are not designed, intended, authorized or warranted for use in any life support or other application where product failure could cause or contribute to personal injury or severe property damage. Any and all such uses without prior written approval of an Officer of K2L and further testing and/or modification will be fully at the risk of the customer. Copies of this document or other K2L literature, as well as the Terms of Sale Agreement, may be obtained by visiting K2L's website at http://www.K2L.de. The K2L logo is a trademark of K2L. Other names mentioned may be trademarks of their respective holders. All claims made herein speak as of the date of this material. The company does not undertake to update such statements. (05/19) Copyright © 2019 K2L GmbH ("K2L"). All rights reserved.

DS00003068A WEEE-Reg.-Nr. DE 79600900